







SPECIFICATIONS:

1. Material:

(1). Body: PA46

(2). Pin: Brass

2. Wire range: N/A

3. Electrical rating: 300V, 15A.

4. Wire strip length: N/A

5. Operating temperature: -40C to +140C.

6. Max torque: N/A

7. Insulation resistance: DC 500V, 500M.

8. Dielectric withstand: AC 2500V for 1 minute.

9. Breakdown voltage: 4000V.

10. A = (N x P) + 2.0mm

11. B = (N - 1) x P

12. P (PITCH) = 5.0mm (.197").

13. N = Number of positions available 2 through 24.

ENTER DESCRIPTION EC NO: NEO2006-0310 DRWN: LROTHAUS 2006/01/09 CHKD: CYORK 2006/01/09 APPR: JPAWLICK 2006/01/10		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
			SYMBOLS			MM/IN		4:1	INCH		
			▽=0	mm	INCH	DRAWN BY	DATE	TITLE	5.0MM, EURO HEADER, VERTICAL, HI-TEMP		
			▽=0	4 PLACES ± --- ±.0015	LROTHAUS	12/6/05					
				3 PLACES ±0.038 ±.005	CHECKED BY	DATE					
				2 PLACES ±0.13 ±.01	C. YORK	01/06/06	MOLEX INCORPORATED	SHEET NO. 1 OF 1			
				1 PLACE ±0.3 ±---	APPROVED BY	DATE					
				ANGULAR ± 2 °	MATERIAL NO.	DOCUMENT NO.					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE CHART	SD-39521-001					
					SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

AA