


# IRFBF20S/LPbF

## HEXFET® Power MOSFET

- Surface Mount (IRFBF20S)
- Low-profile through-hole (IRFBF20L)
- Available in Tape & Reel (IRFBF20S)
- Dynamic dv/dt Rating
- 150°C Operating Temperature
- Fast Switching
- Fully Avalanche Rated
- Lead-Free



$$V_{DS} = 900V$$


$$R_{DS(on)} = 8.0\Omega$$

$$I_D = 1.7A$$

## Description

Third generation HEXFETs from International Rectifier provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The D<sup>2</sup>Pak is a surface mount power package capable of accommodating die sizes up to HEX-4. It provides the highest power capability and the lowest possible on-resistance in any existing surface mount package. The D<sup>2</sup>Pak is suitable for high current applications because of its low internal connection resistance and can dissipate up to 2.0W in a typical surface mount application. The through-hole version (IRFBF20L) is available for low-profile applications.



## Absolute Maximum Ratings

|                           | Parameter                                  | Max.                   | Units |
|---------------------------|--------------------------------------------|------------------------|-------|
| $I_D @ T_C = 25^\circ C$  | Continuous Drain Current, $V_{GS} @ 10V$ ⑤ | 1.7                    | A     |
| $I_D @ T_C = 100^\circ C$ | Continuous Drain Current, $V_{GS} @ 10V$ ⑤ | 1.1                    |       |
| $I_{DM}$                  | Pulsed Drain Current ①⑤                    | 6.8                    |       |
| $P_D @ T_A = 25^\circ C$  | Power Dissipation                          | 3.1                    | W     |
| $P_D @ T_C = 25^\circ C$  | Power Dissipation                          | 54                     | W     |
|                           | Linear Derating Factor                     | 0.43                   | W/°C  |
| $V_{GS}$                  | Gate-to-Source Voltage                     | $\pm 20$               | V     |
| $E_{AS}$                  | Single Pulse Avalanche Energy ②⑤           | 180                    | mJ    |
| $I_{AR}$                  | Avalanche Current ①                        | 1.7                    | A     |
| $E_{AR}$                  | Repetitive Avalanche Energy ①              | 5.4                    | mJ    |
| dv/dt                     | Peak Diode Recovery dv/dt ③⑤               | 1.5                    | V/ns  |
| $T_J$                     | Operating Junction and                     | -55 to + 150           | °C    |
| $T_{STG}$                 | Storage Temperature Range                  |                        |       |
|                           | Soldering Temperature, for 10 seconds      | 300 (1.6mm from case ) |       |


## Thermal Resistance

|                 | Parameter                                          | Typ. | Max. | Units |
|-----------------|----------------------------------------------------|------|------|-------|
| $R_{\theta JC}$ | Junction-to-Case                                   | ---  | 2.3  | °C/W  |
| $R_{\theta JA}$ | Junction-to-Ambient ( PCB Mounted, steady-state)** | ---  | 40   |       |

## Electrical Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise specified)

|                                 | Parameter                            | Min. | Typ. | Max. | Units              | Conditions                                                                                |
|---------------------------------|--------------------------------------|------|------|------|--------------------|-------------------------------------------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 900  | —    | —    | V                  | $V_{GS} = 0V, I_D = 250\mu A$                                                             |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 1.1  | —    | $V/^\circ\text{C}$ | Reference to $25^\circ\text{C}$ , $I_D = 1\text{mA}$ ⑤                                    |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | —    | 8.0  | $\Omega$           | $V_{GS} = 10V, I_D = 1.0A$ ④                                                              |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 2.0  | —    | 4.0  | V                  | $V_{DS} = V_{GS}, I_D = 250\mu A$                                                         |
| $g_{fs}$                        | Forward Transconductance             | 0.60 | —    | —    | S                  | $V_{DS} = 50V, I_D = 1.0A$ ⑤                                                              |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 100  | $\mu A$            | $V_{DS} = 900V, V_{GS} = 0V$                                                              |
|                                 |                                      | —    | —    | 500  |                    | $V_{DS} = 720V, V_{GS} = 0V, T_J = 125^\circ\text{C}$                                     |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA                 | $V_{GS} = 20V$                                                                            |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -100 |                    | $V_{GS} = -20V$                                                                           |
| $Q_g$                           | Total Gate Charge                    | —    | —    | 38   | nC                 | $I_D = 1.7A$                                                                              |
| $Q_{gs}$                        | Gate-to-Source Charge                | —    | —    | 4.7  |                    | $V_{DS} = 360V$                                                                           |
| $Q_{gd}$                        | Gate-to-Drain ("Miller") Charge      | —    | —    | 21   |                    | $V_{GS} = 10V$ , See Fig. 6 and 13 ④⑤                                                     |
| $t_{d(on)}$                     | Turn-On Delay Time                   | —    | 8.0  | —    | ns                 | $V_{DD} = 450V$<br>$I_D = 1.7A$<br>$R_G = 18\Omega$<br>$R_D = 280\Omega$ , See Fig. 10 ④⑤ |
| $t_r$                           | Rise Time                            | —    | 21   | —    |                    |                                                                                           |
| $t_{d(off)}$                    | Turn-Off Delay Time                  | —    | 56   | —    |                    |                                                                                           |
| $t_f$                           | Fall Time                            | —    | 32   | —    |                    |                                                                                           |
| $L_S$                           | Internal Source Inductance           | —    | 7.5  | —    | nH                 | Between lead, and center of die contact                                                   |
| $C_{iss}$                       | Input Capacitance                    | —    | 490  | —    | pF                 | $V_{GS} = 0V$                                                                             |
| $C_{oss}$                       | Output Capacitance                   | —    | 55   | —    |                    | $V_{DS} = 25V$                                                                            |
| $C_{rss}$                       | Reverse Transfer Capacitance         | —    | 18   | —    |                    | $f = 1.0\text{MHz}$ , See Fig. 5⑤                                                         |


## Source-Drain Ratings and Characteristics

|          | Parameter                              | Min.                                                                        | Typ. | Max. | Units   | Conditions                                                                                                                                           |
|----------|----------------------------------------|-----------------------------------------------------------------------------|------|------|---------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current (Body Diode) | —                                                                           | —    | 1.7  | A       | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$ | Pulsed Source Current (Body Diode) ①   | —                                                                           | —    | 6.8  |         |                                                                                                                                                      |
| $V_{SD}$ | Diode Forward Voltage                  | —                                                                           | —    | 1.5  | V       | $T_J = 25^\circ\text{C}, I_S = 1.7A, V_{GS} = 0V$ ④                                                                                                  |
| $t_{rr}$ | Reverse Recovery Time                  | —                                                                           | 350  | 530  | ns      | $T_J = 25^\circ\text{C}, I_F = 1.7A$                                                                                                                 |
| $Q_{rr}$ | Reverse Recovery Charge                | —                                                                           | 0.85 | 1.3  | $\mu C$ | $di/dt = 100A/\mu s$ ④⑤                                                                                                                              |
| $t_{on}$ | Forward Turn-On Time                   | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$ ) |      |      |         |                                                                                                                                                      |


### Notes:

- ① Repetitive rating; pulse width limited by max. junction temperature. ( See fig. 11 )
- ②  $V_{DD} = 50V$ , starting  $T_J = 25^\circ\text{C}$ ,  $L = 117\text{mH}$ ,  $R_G = 25\Omega$ ,  $I_{AS} = 1.7A$ . (See Figure 11)
- ③  $I_{SD} \leq 1.7A$ ,  $di/dt \leq 70A/\mu s$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  $T_J \leq 150^\circ\text{C}$
- ④ Pulse width  $\leq 300\mu s$ ; duty cycle  $\leq 2\%$ .
- ⑤ Uses IRFBF20 data and test conditions


\*\* When mounted on 1" square PCB (FR-4 or G-10 Material ).  
For recommended footprint and soldering techniques refer to application note #AN-994.




**Fig 1.** Typical Output Characteristics,




**Fig 2.** Typical Output Characteristics,




**Fig 3.** Typical Transfer Characteristics




**Fig 4.** Normalized On-Resistance  
Vs. Temperature




**Fig 5.** Typical Capacitance Vs. Drain-to-Source Voltage




**Fig 6.** Typical Gate Charge Vs. Gate-to-Source Voltage




**Fig 7.** Typical Source-Drain Diode Forward Voltage




**Fig 8.** Maximum Safe Operating Area




**Fig 9.** Maximum Drain Current Vs. Case Temperature




**Fig 10a.** Switching Time Test Circuit




**Fig 10b.** Switching Time Waveforms




**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Case




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms



**Fig 13a.** Basic Gate Charge Waveform



**Fig 12c.** Maximum Avalanche Energy Vs. Drain Current



**Fig 13b.** Gate Charge Test Circuit

**Circuit Layout Considerations**

- Low Stray Inductance
- Ground Plane
- Low Leakage Inductance
- Current Transformer


**Notes:**

- $dv/dt$  controlled by  $R_G$
- Driver same type as D.U.T.
- $I_{SD}$  controlled by Duty Factor "D"
- D.U.T. - Device Under Test



International  
**IOR** Rectifier

Dimensions are shown in millimeters (inches)



| HEXFET     | IGBTs, CoPACK | DIODES      |
|------------|---------------|-------------|
| 1.- GATE   | 1.- GATE      | 1.- ANODE * |
| 2.- DRAIN  | 2.- COLLECTOR | 2.- CATHODE |
| 3.- SOURCE | 3.- EMITTER   | 3.- ANODE   |

- PART DEPENDENT.

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES]
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4.  DIMENSION d1 AND c1 APPLY TO BASE METAL ONLY.
5. CONTROLLING DIMENSION: INCH.

EXAMPLE: THIS IS AN IRF530S WITH  
LOT CODE 8024  
ASSEMBLED ON WW 02, 2000  
IN THE ASSEMBLY LINE "L"

Note: "P" in assembly line position indicates "Lead-Free"

Diagram illustrating the marking on a component, showing the part number and date code.

**PART NUMBER**

F530S

**DATE CODE**

YEAR 0 = 2000

WEEK 02

LINE L

002L


80 24

OR

Diagram illustrating the marking on a component package:

- PART NUMBER:** F 530S
- DATE CODE:** P002A
- LEAD-FREE DESIGNATION:** P (Designates Lead-Free Product (Optional))
- YEAR:** 0 = 2000
- WEEK:** 02
- ASSEMBLY SITE CODE:** A

TO-262 Package Outline



| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 | 4     |
| A1     | 2.03        | 2.92  | .080     | .115 |       |
| b      | 0.51        | 0.99  | .020     | .039 |       |
| b1     | 0.51        | 0.89  | .020     | .035 |       |
| b2     | 1.14        | 1.40  | .045     | .055 | 4     |
| c      | 0.38        | 0.63  | .015     | .025 |       |
| c1     | 1.14        | 1.40  | .045     | .055 |       |
| c2     | 0.43        | .063  | .017     | .029 | 3     |
| D      | 8.51        | 9.65  | .335     | .380 |       |
| D1     | 5.33        |       | .210     |      |       |
| E      | 9.65        | 10.67 | .380     | .420 | 3     |
| E1     | 6.22        |       | .245     |      |       |
| e      | 2.54 BSC    |       | .100 BSC |      |       |
| L      | 13.46       | 14.09 | .530     | .555 |       |
| L1     | 3.56        | 3.71  | .140     | .146 |       |
| L2     |             | 1.65  |          | .065 |       |

LEAD ASSIGNMENTS


| HEXFET     | IGBT          |
|------------|---------------|
| 1.- GATE   | 1 - GATE      |
| 2.- DRAIN  | 2 - COLLECTOR |
| 3.- SOURCE | 3 - EMITTER   |
| 4.- DRAIN  |               |

- NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
  2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES]
  3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
  4. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
  5. CONTROLLING DIMENSION: INCH.


TO-262 Part Marking Information

EXAMPLE: THIS IS AN IRL3103L  
LOT CODE 1789  
ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position indicates "Lead-Free"




OR



# IRFBF20S/LPbF

International  
**IOR** Rectifier

## D<sup>2</sup>Pak Tape & Reel Information



Data and specifications subject to change without notice.

International  
**IOR** Rectifier

**IR WORLD HEADQUARTERS:** 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105

TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.07/04

www.irf.com