


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		B	REVISED PER 0G3B-0536-02	1/17/03	SS	GS
			B1	REVISED PER ECO-09-023929	16OCT09	KK	AEG

NOTES:

- 1
- FINISH-SILVER PLATE SEMI-BRIGHT 200-400u INCHES THICK, OVER NICKEL.
- 2
- FINISH GOLD PLATE 20-30u INCHES THICK, OVER NICKEL.
3.
- WIRE RACK PLATING MARKS PERMISSIBLE IN THREAD RELIEF. WHEN THREAD RELIEF IS ABSENT, FIRST FULL THREAD TO BE .050 FROM SHOULDER.
- 4
- PRELIMINARY PART NUMBER.
- 5
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	1.11	1,3	M3 X 0.5-6g	--	192059-4
	1.42	1,3	5 (.124)-40NC-2A	--	192059-3
	1.42	2	5 (.124)-40NC-2A	10924	192059-2
	1.42	1,3	M3 X 0.5-6g	09014	192059-1
	DIM B	FINISH (NOTE NO.)	THREAD A	WAS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03-13-92 D. WILSON	Tyco Electronics Corporation Harrisburg, PA 17105			
		CHK 04-01-92 R. JAYNE				
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET ASSY, 2mm		
		0 PLC ± -		PRODUCT SPEC		
		1 PLC ± -		APPLICATION SPEC		
		2 PLC ± .02		SIZE A3		
3 PLC ± .010		4 PLC ± -		CAGE CODE 00779		
MATERIAL BRASS		FINISH 1 2		DRAWING NO C-192059		
CUSTOMER DRAWING				RESTRICTED TO -		
SCALE 5:1				SHEET 1 OF 1		
REV B1						