



50W Universal Input Adapter PSA-50U Single Output Switching Power Supply



Features

- Low Cost
- Class B EMI
- No Load Power Consumption <1 Watt
- Power On LED
- Low Profile Design

Applications

- Portable Equipment
- Peripherals
- Networking
- Gaming Machines

Safety Compliance

- cUL 60950 3rd Edition
- CE
- TUV EN60950

Mechanical Characteristics

Dimensions: • Length: 125.5 ± 0.1 mm (4.94in) • Height: 37.5 ± 0.1 mm (1.48in)
• Width: 62.4 ± 0.1 mm (2.46in) • Weight: 0.35Kgs (0.77lbs)

Output Specifications

Model	DC Output Voltage	Load		Ripple and Noise (1)	Regulation	
		Min.	Max.		Line	Load
PSA-50U-120(S)	+12V	0A	4.2A	120mV p-p	±2%	±5%

(1) Measured by using a 12 inch twisted pair terminated with a 10µF capacitor and a 0.1µF ceramic in parallel.

INPUT**AC Input Voltage Rating**

100-240VAC

AC Input Voltage Range

90-264VAC

AC Input Frequency

47 to 63Hz

Input Current

1.5A(rms) 120VAC at max. Load

0.75A(rms) 240VAC at max. Load

Leakage Current

3.5mA max. for 254VAC/50Hz

Max. In-rush Current

40A for 120VAC at max. Load

80A for 240VAC at max. Load

(Cold Start @ ambient 25°C)

OUTPUT**Efficiency**78% typ. @120VAC, 60Hz and
max. Load**Hold-up Time**16m Sec. min. @120VAC, 60Hz
and max. Load**Overvoltage Protection**

16V max. @ min. Load

Overcurrent ProtectionOutput Equipment with Short
Circuit Protection - Auto Restart**ENVIRONMENTAL****Humidity**

Operation 5-80%

Temperature

Operation 0 to +40°C

Non-Operation -20°C to +70°C

EMI

EN 55022 Class B

FCC Class B

ImmunityEN61000 4-2: Air Level 3
Contact Level 2

EN61000 4-3: Level 2

EN61000 4-4: Level 2

EN61000 4-5: (L-G) Level 3

(L-N) Level 2

EN61000 4-6: Level 2

EN61000 4-8:

EN61000 4-11:


EN61000 3-2:

EN61000 3-3:

Dielectric Withstand (Hipot)Primary to secondary: 3000VAC for 1
minute 10mA (without shielding
board)Primary to F.G. 1500VAC for 1
minute 10mA (with shielding board)**MTBF**

50K Hrs. min. at max. Load

25°C ambient temperature

Output Connector2.1 x 5.5 mm Center Positive
Standard**Dimension Diagram Unit: mm (inch)**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[PSA-50U-120\(S\)](#)