




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		B6	REVISED PER ECO-11-004820	11MAR11	RK	HMR




PHYSICAL PROPERTIES:
HOUSING: THERMOPLASTIC, UL94V-0, BLACK.
TERMINALS: MATERIAL: COPPER ALLOY, PLATING SEE TABLE.
SCREWS: #6-32 STEEL, ZINC PLATING W/ CLEAR CHROMATE.
PITCH (TERMINAL SPACING): .375"
OPERATING TEMP: 105° C MAX


ELECTRICAL PROPERTIES:
RATED CURRENT: 20A
OPERATING VOLTAGE: 300V
WIRE RANGE: 12-22 AWG



2-796985-2




2-796985-4



2-796985-3

CUT TURRET OFF
FLUSH WITH BOTTOM
OF HOUSING



MOUNTING PANEL LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 5/27/03	 TE Connectivity					
		CHK S YODER 5/27/03						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S YODER 5/27/03	NAME					
	0 PLC ± -	PRODUCT SPEC	JC6-Q308-XX ASSEMBLY					
	1 PLC ± -	—						
	2 PLC ± .02	—						
	3 PLC ± .010	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO					
	4 PLC ± -	—						
MATERIAL	FINISH	WEIGHT	A300779			C-6-1437665-2		—
—	—	CUSTOMER DRAWING	SCALE		NTS	SHEET	1 OF 2	REV B6

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION
- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
FT	0		-	SEE SHEET 1		-	-

- 1

PRELIMINARY
- 2

MATTE TIN PLATE .0002 - .0006 MIN OVER .00005 MIN NICKEL.
- 3

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

BRIGHT TIN PL	9.000	9.314	23	JC6-Q308-23	2-1546700-2
BRIGHT TIN PL	8.625	8.939	22	JC6-Q308-22	2-1546700-1
BRIGHT TIN PL	8.250	8.564	21	JC6-Q308-21	2-1546700-0
BRIGHT TIN PL	7.875	8.189	20	JC6-Q308-20	1-1546700-9
BRIGHT TIN PL	7.500	7.814	19	JC6-Q308-19	1-1546700-8
BRIGHT TIN PL	7.125	7.439	18	JC6-Q308-18	1-1546700-7
BRIGHT TIN PL	6.750	7.064	17	JC6-Q308-17	1-1546700-6
BRIGHT TIN PL	6.375	6.689	16	JC6-Q308-16	1-1546700-5
BRIGHT TIN PL	6.000	6.314	15	JC6-Q308-15	1-1546700-4
BRIGHT TIN PL	5.625	5.939	14	JC6-Q308-14	1-1546700-3
BRIGHT TIN PL	5.250	5.564	13	JC6-Q308-13	1-1546700-2
BRIGHT TIN PL	4.875	5.189	12	JC6-Q308-12	796985-9
BRIGHT TIN PL	4.500	4.814	11	JC6-Q308-11	1-1546700-1
BRIGHT TIN PL	4.125	4.439	10	JC6-Q308-10	796985-6
BRIGHT TIN PL	3.750	4.064	9	JC6-Q308-09	1-1546700-0
BRIGHT TIN PL	3.375	3.689	8	JC6-Q308-08	6-1437665-9
BRIGHT TIN PL	3.000	3.314	7	JC6-Q308-07	6-1437665-8
BRIGHT TIN PL	2.625	2.939	6	JC6-Q308-06	6-1437665-7
BRIGHT TIN PL	2.250	2.564	5	JC6-Q308-05-175	2-796985-4
BRIGHT TIN PL	2.250	2.564	5	JC6-Q308-05	6-1437665-6
	1.875	2.189	4	JC6-Q308-04	6-1546700-5
BRIGHT TIN PL	1.875	2.189	4	JC6-Q308-04	6-1437665-5
BRIGHT TIN PL	1.500	1.814	3	JC6-Q308-03-174	2-796985-3
BRIGHT TIN PL	1.500	1.814	3	JC6-Q308-03-173	2-796985-2
BRIGHT TIN PL	1.500	1.814	3	JC6-Q308-03	6-1437665-4
BRIGHT TIN PL	1.125	1.439	2	JC6-Q308-02	6-1437665-2
PLATING	DIM. B	DIM. A	NO. OF POS.	CATALOG NUMBER	PART NO.

3

OBSOLETE

SEE FIGURE (PAGE 1)

SEE FIGURE (PAGE 1)


3

OBSOLETE

SEE FIGURE (PAGE 1)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES



MATERIAL
-

FINISH
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± -

DWN S SCHLEGEL 5/27/03
CHK S YODER 5/27/03
APVD S YODER 5/27/03
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -

CUSTOMER DRAWING

SCALE NTS

SHEET 2 OF 2

REV B6

STE

TE Connectivity

JC6-Q308-XX ASSEMBLY

SIZE A3CAGE CODE 00779DRAWING NO C-6-1437665-2RESTRICTED TO -