

## 74VCX16245

### Low Voltage 16-Bit Bidirectional Transceiver with 3.6V Tolerant Inputs and Outputs

#### General Description

The VCX16245 contains sixteen non-inverting bidirectional buffers with 3-STATE outputs and is intended for bus oriented applications. The device is byte controlled. Each byte has separate 3-STATE control inputs which can be shorted together for full 16-bit operation. The  $T/\bar{R}$  inputs determine the direction of data flow through the device. The  $\bar{O}\bar{E}$  inputs disable both the A and B ports by placing them in a high impedance state.

The 74VCX16245 is designed for low voltage (1.65 to 3.6V)  $V_{CC}$  applications with I/O compatibility up to 3.6V.

The 74VCX16245 is fabricated with an advanced CMOS technology to achieve high speed operation while maintaining low CMOS power dissipation.

#### Features

- 1.65V–3.6V  $V_{CC}$  supply operation
- 3.6V tolerant inputs and outputs
- $t_{PD}$ 
  - 2.5 ns max for 3.0V to 3.6V  $V_{CC}$
  - 3.0 ns max for 2.3V to 2.7V  $V_{CC}$
  - 6.0 ns max for 1.65V to 1.95V  $V_{CC}$
- Power-down high impedance inputs and outputs
- Supports live insertion/withdrawal (Note 1)
- Static Drive ( $I_{OH}/I_{OL}$ )
  - $\pm 24$  mA @ 3.0V  $V_{CC}$
  - $\pm 18$  mA @ 2.3V  $V_{CC}$
  - $\pm 6$  mA @ 1.65V  $V_{CC}$
- Uses patented noise/EMI reduction circuitry
- Latchup performance exceeds 300 mA
- ESD performance:
  - Human body model > 2000V
  - Machine model > 200V


**Note 1:** To ensure the high-impedance state during power up or power down,  $\bar{O}\bar{E}$  should be tied to  $V_{CC}$  through a pull-up resistor; the minimum value of the resistor is determined by the current-sourcing capability of the driver.

#### Ordering Code:

| Order Number  | Package Number | Package Description                                                         |
|---------------|----------------|-----------------------------------------------------------------------------|
| 74VCX16245MTD | MTD48          | 48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide |


Devices also available in Tape and Reel. Specify by appending the suffix letter "X" to the ordering code.

#### Logic Symbol



74VCX16245 Low Voltage 16-Bit Bidirectional Transceiver with 3.6V Tolerant Inputs and Outputs

Connection Diagram



Pin Descriptions

| Pin Names          | Description                      |
|--------------------|----------------------------------|
| $\overline{OE_n}$  | Output Enable Input (Active LOW) |
| $\overline{T/R_n}$ | Transmit/Receive Input           |
| $A_0-A_{15}$       | Side A Inputs or 3-STATE Outputs |
| $B_0-B_{15}$       | Side B Inputs or 3-STATE Outputs |


Truth Tables

| Inputs            |                    | Outputs                               |
|-------------------|--------------------|---------------------------------------|
| $\overline{OE_1}$ | $\overline{T/R_1}$ |                                       |
| L                 | L                  | Bus $B_0-B_7$ Data to Bus $A_0-A_7$   |
| L                 | H                  | Bus $A_0-A_7$ Data to Bus $B_0-B_7$   |
| H                 | X                  | HIGH Z State on $A_0-A_7$ , $B_0-B_7$ |

| Inputs            |                    | Outputs                                     |
|-------------------|--------------------|---------------------------------------------|
| $\overline{OE_2}$ | $\overline{T/R_2}$ |                                             |
| L                 | L                  | Bus $B_8-B_{15}$ Data to Bus $A_8-A_{15}$   |
| L                 | H                  | Bus $A_8-A_{15}$ Data to Bus $B_8-B_{15}$   |
| H                 | X                  | HIGH Z State on $A_8-A_{15}$ , $B_8-B_{15}$ |

H = HIGH Voltage Level  
L = LOW Voltage Level  
X = Immaterial (HIGH or LOW, inputs and I/O's may not float)  
Z = High Impedance

Logic Diagram



**Absolute Maximum Ratings**(Note 2)

|                                                                    |                         |
|--------------------------------------------------------------------|-------------------------|
| Supply Voltage ( $V_{CC}$ )                                        | –0.5V to +4.6V          |
| DC Input Voltage ( $V_I$ )                                         | –0.5V to +4.6V          |
| Output Voltage ( $V_O$ )                                           |                         |
| Outputs 3-STATE                                                    | –0.5V to +4.6V          |
| Outputs Active (Note 3)                                            | –0.5 to $V_{CC} + 0.5V$ |
| DC Input Diode Current ( $I_{IK}$ ) $V_I < 0V$                     | –50 mA                  |
| DC Output Diode Current ( $I_{OK}$ )                               |                         |
| $V_O < 0V$                                                         | –50 mA                  |
| $V_O > V_{CC}$                                                     | +50 mA                  |
| DC Output Source/Sink Current ( $I_{OH}/I_{OL}$ )                  | ±50 mA                  |
| DC $V_{CC}$ or Ground Current per Supply Pin ( $I_{CC}$ or Ground) | ±100 mA                 |
| Storage Temperature Range ( $T_{STG}$ )                            | –65°C to +150°C         |

**Recommended Operating Conditions** (Note 4)

|                                                 |                |
|-------------------------------------------------|----------------|
| Power Supply                                    |                |
| Operating                                       | 1.65V to 3.6V  |
| Data Retention Only                             | 1.2V to 3.6V   |
| Input Voltage                                   | –0.3V to 3.6V  |
| Output Voltage ( $V_O$ )                        |                |
| Output in Active States                         | 0V to $V_{CC}$ |
| Output in 3-STATE                               | 0.0V to 3.6V   |
| Output Current in $I_{OH}/I_{OL}$               |                |
| $V_{CC} = 3.0V$ to 3.6V                         | ±24 mA         |
| $V_{CC} = 2.3V$ to 2.7V                         | ±18 mA         |
| $V_{CC} = 1.65V$ to 2.3V                        | ±6 mA          |
| Free Air Operating Temperature ( $T_A$ )        | –40°C to +85°C |
| Minimum Input Edge Rate ( $\Delta t/\Delta V$ ) |                |
| $V_{IN} = 0.8V$ to 2.0V, $V_{CC} = 3.0V$        | 10 ns/V        |

**Note 2:** The "Absolute Maximum Ratings" are those values beyond which the safety of the device cannot be guaranteed. The device should not be operated at these limits. The parametric values defined in the "Electrical Characteristics" table are not guaranteed at the Absolute Maximum Ratings. The Recommended Operating Conditions tables will define the conditions for actual device operation.

**Note 3:**  $I_O$  Absolute Maximum Rating must be observed.

**Note 4:** Floating or unused pin (inputs or I/O's) must be held HIGH or LOW.

**DC Electrical Characteristics (2.7V <  $V_{CC}$  ≤ 3.6V)**

| Symbol          | Parameter                      | Conditions                                                                                                   | $V_{CC}$<br>(V)              | Min                                 | Max                       | Units |
|-----------------|--------------------------------|--------------------------------------------------------------------------------------------------------------|------------------------------|-------------------------------------|---------------------------|-------|
| $V_{IH}$        | HIGH Level Input Voltage       |                                                                                                              | 2.7–3.6                      | 2.0                                 |                           | V     |
| $V_{IL}$        | LOW Level Input Voltage        |                                                                                                              | 2.7–3.6                      |                                     | 0.8                       | V     |
| $V_{OH}$        | HIGH Level Output Voltage      | $I_{OH} = -100 \mu A$<br>$I_{OH} = -12 \text{ mA}$<br>$I_{OH} = -18 \text{ mA}$<br>$I_{OH} = -24 \text{ mA}$ | 2.7–3.6<br>2.7<br>3.0<br>3.0 | $V_{CC} - 0.2$<br>2.2<br>2.4<br>2.2 |                           | V     |
| $V_{OL}$        | LOW Level Output Voltage       | $I_{OL} = 100 \mu A$<br>$I_{OL} = 12 \text{ mA}$<br>$I_{OL} = 18 \text{ mA}$<br>$I_{OL} = 24 \text{ mA}$     | 2.7–3.6<br>2.7<br>3.0<br>3.0 |                                     | 0.2<br>0.4<br>0.4<br>0.55 | V     |
| $I_I$           | Input Leakage Current          | $0V \leq V_I \leq 3.6V$                                                                                      | 2.7–3.6                      |                                     | ±5.0                      | μA    |
| $I_{OZ}$        | 3-STATE Output Leakage         | $0V \leq V_O \leq 3.6V$<br>$V_I = V_{IH}$ or $V_{IL}$                                                        | 2.7–3.6                      |                                     | ±10                       | μA    |
| $I_{OFF}$       | Power Off Leakage Current      | $0V \leq (V_I, V_O) \leq 3.6V$                                                                               | 0                            |                                     | 10                        | μA    |
| $I_{CC}$        | Quiescent Supply Current       | $V_I = V_{CC}$ or GND<br>$V_{CC} \leq (V_I, V_O) \leq 3.6V$ (Note 5)                                         | 2.7–3.6<br>2.7–3.6           |                                     | 20<br>±20                 | μA    |
| $\Delta I_{CC}$ | Increase in $I_{CC}$ per Input | $V_{IH} = V_{CC} - 0.6V$                                                                                     | 2.7–3.6                      |                                     | 750                       | μA    |

**Note 5:** Outputs disabled or 3-STATE only.

### DC Electrical Characteristics ( $2.3V \leq V_{CC} \leq 2.7V$ )

| Symbol           | Parameter                 | Conditions                                                                                                      | V <sub>CC</sub><br>(V)       | Min                                        | Max               | Units |
|------------------|---------------------------|-----------------------------------------------------------------------------------------------------------------|------------------------------|--------------------------------------------|-------------------|-------|
| V <sub>IH</sub>  | HIGH Level Input Voltage  |                                                                                                                 | 2.3–2.7                      | 1.6                                        |                   | V     |
| V <sub>IL</sub>  | LOW Level Input Voltage   |                                                                                                                 | 2.3–2.7                      |                                            | 0.7               | V     |
| V <sub>OH</sub>  | HIGH Level Output Voltage | I <sub>OH</sub> = –100 µA<br>I <sub>OH</sub> = –6 mA<br>I <sub>OH</sub> = –12 mA<br>I <sub>OH</sub> = –18 mA    | 2.3–2.7<br>2.3<br>2.3<br>2.3 | V <sub>CC</sub> – 0.2<br>2.0<br>1.8<br>1.7 |                   | V     |
| V <sub>OL</sub>  | LOW Level Output Voltage  | I <sub>OL</sub> = 100 µA<br>I <sub>OL</sub> = 12 mA<br>I <sub>OL</sub> = 18 mA                                  | 2.3–2.7<br>2.3<br>2.3        |                                            | 0.2<br>0.4<br>0.6 | V     |
| I <sub>I</sub>   | Input Leakage Current     | 0 ≤ V <sub>I</sub> ≤ 3.6V                                                                                       | 2.3–2.7                      |                                            | ±5.0              | µA    |
| I <sub>OZ</sub>  | 3-STATE Output Leakage    | 0 ≤ V <sub>O</sub> ≤ 3.6V<br>V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                | 2.3–2.7                      |                                            | ±10               | µA    |
| I <sub>OFF</sub> | Power Off Leakage Current | 0 ≤ (V <sub>I</sub> , V <sub>O</sub> ) ≤ 3.6V                                                                   | 0                            |                                            | 10                | µA    |
| I <sub>CC</sub>  | Quiescent Supply Current  | V <sub>I</sub> = V <sub>CC</sub> or GND<br>V <sub>CC</sub> ≤ (V <sub>I</sub> , V <sub>O</sub> ) ≤ 3.6V (Note 6) | 2.3–2.7<br>2.3–2.7           |                                            | 20<br>±20         | µA    |

**Note 6:** Outputs disabled or 3-STATE only.

### DC Electrical Characteristics ( $1.65V \leq V_{CC} < 2.3V$ )

| Symbol           | Parameter                 | Conditions                                                                                                      | V <sub>CC</sub><br>(V) | Min                           | Max                    | Units |
|------------------|---------------------------|-----------------------------------------------------------------------------------------------------------------|------------------------|-------------------------------|------------------------|-------|
| V <sub>IH</sub>  | HIGH Level Input Voltage  |                                                                                                                 | 1.65–2.3               | 0.65 × V <sub>CC</sub>        |                        | V     |
| V <sub>IL</sub>  | LOW Level Input Voltage   |                                                                                                                 | 1.65–2.3               |                               | 0.35 × V <sub>CC</sub> | V     |
| V <sub>OH</sub>  | HIGH Level Output Voltage | I <sub>OH</sub> = –100 µA<br>I <sub>OH</sub> = –6 mA                                                            | 1.65–2.3<br>1.65       | V <sub>CC</sub> – 0.2<br>1.25 |                        | V     |
| V <sub>OL</sub>  | LOW Level Output Voltage  | I <sub>OL</sub> = 100 µA<br>I <sub>OL</sub> = 6 mA                                                              | 1.65–2.3<br>1.65       |                               | 0.2<br>0.3             | V     |
| I <sub>I</sub>   | Input Leakage Current     | 0 ≤ V <sub>I</sub> ≤ 3.6V                                                                                       | 1.65–2.3               |                               | ±5.0                   | µA    |
| I <sub>OZ</sub>  | 3-STATE Output Leakage    | 0 ≤ V <sub>O</sub> ≤ 3.6V<br>V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>                                | 1.65–2.3               |                               | ±10                    | µA    |
| I <sub>OFF</sub> | Power Off Leakage Current | 0 ≤ (V <sub>I</sub> , V <sub>O</sub> ) ≤ 3.6V                                                                   | 0                      |                               | 10                     | µA    |
| I <sub>CC</sub>  | Quiescent Supply Current  | V <sub>I</sub> = V <sub>CC</sub> or GND<br>V <sub>CC</sub> ≤ (V <sub>I</sub> , V <sub>O</sub> ) ≤ 3.6V (Note 7) | 1.65–2.3<br>1.65–2.3   |                               | 20<br>±20              | µA    |

**Note 7:** Outputs disabled or 3-STATE only.

## AC Electrical Characteristics (Note 8)

| Symbol                                 | Parameter                         | T <sub>A</sub> = -40°C to +85°C, C <sub>L</sub> = 30 pF, R <sub>L</sub> = 500Ω |     |                             |     |                                |      | Units |
|----------------------------------------|-----------------------------------|--------------------------------------------------------------------------------|-----|-----------------------------|-----|--------------------------------|------|-------|
|                                        |                                   | V <sub>CC</sub> = 3.3V ±0.3V                                                   |     | V <sub>CC</sub> = 2.5 ±0.2V |     | V <sub>CC</sub> = 1.8V ± 0.15V |      |       |
|                                        |                                   | Min                                                                            | Max | Min                         | Max | Min                            | Max  |       |
| t <sub>PHL</sub> , t <sub>PLH</sub>    | Prop Delay                        | 0.8                                                                            | 2.5 | 1.0                         | 3.0 | 1.5                            | 6.0  | ns    |
| t <sub>PZL</sub> , t <sub>PZH</sub>    | Output Enable Time                | 0.8                                                                            | 3.8 | 1.0                         | 4.9 | 1.5                            | 9.3  | ns    |
| t <sub>PLZ</sub> , t <sub>PHZ</sub>    | Output Disable Time               | 0.8                                                                            | 3.7 | 1.0                         | 4.2 | 1.5                            | 7.6  | ns    |
| t <sub>OSHL</sub><br>t <sub>OSLH</sub> | Output to Output<br>Skew (Note 9) |                                                                                | 0.5 |                             | 0.5 |                                | 0.75 | ns    |

**Note 8:** For  $C_L = 50\text{pF}$ , add approximately 300ps to the AC maximum specification.

**Note 9:** Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW ( $t_{OSHL}$ ) or LOW-to-HIGH ( $t_{OSLH}$ ).

## Dynamic Switching Characteristics

| Symbol    | Parameter                               | Conditions                                          | $V_{CC}$<br>(V)   | $T_A = +25^{\circ}\text{C}$ | Units |
|-----------|-----------------------------------------|-----------------------------------------------------|-------------------|-----------------------------|-------|
|           |                                         |                                                     |                   | Typical                     |       |
| $V_{OLP}$ | Quiet Output Dynamic<br>Peak $V_{OL}$   | $C_L = 30 \text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0V$ | 1.8<br>2.5<br>3.3 | 0.25<br>0.6<br>0.8          | V     |
| $V_{OLV}$ | Quiet Output Dynamic<br>Valley $V_{OL}$ | $C_L = 30 \text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0V$ | 1.8<br>2.5<br>3.3 | -0.25<br>-0.6<br>-0.8       | V     |
| $V_{OHV}$ | Quiet Output Dynamic<br>Valley $V_{OH}$ | $C_L = 30 \text{ pF}, V_{IH} = V_{CC}, V_{IL} = 0V$ | 1.8<br>2.5<br>3.3 | 1.5<br>1.9<br>2.2           | V     |

## Capacitance

| Symbol   | Parameter                     | Conditions                                                                                  | $T_A = +25^{\circ}\text{C}$ | Units |
|----------|-------------------------------|---------------------------------------------------------------------------------------------|-----------------------------|-------|
| $C_{IN}$ | Input Capacitance             | $V_{CC} = 1.8V, 2.5V, \text{ or } 3.3V, V_I = 0V \text{ or } V_{CC}$                        | 6                           | pF    |
| $C_{IO}$ | Output Capacitance            | $V_I = 0V, \text{ or } V_{CC}, V_{CC} = 1.8V, 2.5V \text{ or } 3.3V$                        | 7                           | pF    |
| $C_{PD}$ | Power Dissipation Capacitance | $V_I = 0V \text{ or } V_{CC}, F = 10 \text{ MHz}$<br>$V_{CC} = 1.8V, 2.5V \text{ or } 3.3V$ | 20                          | pF    |

## AC Loading and Waveforms




FIGURE 1. AC Test Circuit

| TEST               | SWITCH                                                                                          |
|--------------------|-------------------------------------------------------------------------------------------------|
| $t_{PLH}, t_{PHL}$ | Open                                                                                            |
| $t_{PZL}, t_{PLZ}$ | 6V at $V_{CC} = 3.3 \pm 0.3V$ ;<br>$V_{CC} \times 2$ at $V_{CC} = 2.5 \pm 0.2V; 1.8V \pm 0.15V$ |
| $t_{PZH}, t_{PHZ}$ | GND                                                                                             |




FIGURE 2. Waveform for Inverting and Non-inverting Functions




FIGURE 3. 3-STATE Output High Enable and Disable Times for Low Voltage Logic





FIGURE 4. 3-STATE Output Low Enable and Disable Times for Low Voltage Logic

| Symbol   | $V_{CC}$        |                  |                  |
|----------|-----------------|------------------|------------------|
|          | $3.3V \pm 0.3V$ | $2.5V \pm 0.2V$  | $1.8V \pm 0.15V$ |
| $V_{mi}$ | 1.5V            | $V_{CC}/2$       | $V_{CC}/2$       |
| $V_{mo}$ | 1.5V            | $V_{CC}/2$       | $V_{CC}/2$       |
| $V_X$    | $V_{OL} + 0.3V$ | $V_{OL} + 0.15V$ | $V_{OL} + 0.15V$ |
| $V_Y$    | $V_{OH} - 0.3V$ | $V_{OH} - 0.15V$ | $V_{OH} - 0.15V$ |

## Physical Dimensions inches (millimeters) unless otherwise noted



**48-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 6.1mm Wide  
Package Number MTD48**

### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

[www.fairchildsemi.com](http://www.fairchildsemi.com)