




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
0		RELEASED	06/09/04	CC

H5906XXX	"L" (length)
076	3"
152	6"
205	8"
229/230	9"
305	12"
457/460	18"
610	24"



- NOTE:
1. WIRES TO BE #26 AWG MIL STD W16878 TYPE B (BELDEN #8504 OR EQUIVELANT) IN COLORS AND LENGTHS LISTED.
 2. CABLE INSULATION TO BE CAPTIVATED BY CRIMP TERMINAL, SEE ATTACHED DRAWINGS FOR ACCEPTABILITY.
 3. WIRE LENGTH IS 152mm (6.0in) WHITE N29203 (STRIP LENGTH OF WIRE ON BOTH ENDS IS 2.5 ± .3mm).
 4. USE CABLE TIE N22211 FOR EACH HARNESS. ATTACH TIE AND CLIP EXCESS FLUSH LEAVING NO SHARP EDGE..
 5. WIRES ARE BLACK (N29202).
 6. WIRES ARE WHITE (N29203).
 7. CONNECTOR N22230 IS POPULATED IN POSITIONS 1,2,3,4 AND 5 (STRIP LENGTH OF WIRE IS 2.5 ± .3mm).
 8. CONNECTOR N22231 IS POPULATED IN POSITIONS 1,2 AND 3 (STRIP LENGTH OF WIRE IS 2.5 ± .3mm).
 9. CONNECTOR N22217 IS POPULATED IN POSITIONS 1,2,4,5,7 AND 8 (STRIP LENGTH OF WIRE IS 1.65 ± .25mm).

TOLERANCES FRACTIONAL ± 1/8 2 PL. DEC. ± .01 3 PL. DEC. ± .005		USED ON DMW PRODUCTS APPROVALS DRAWN CC CHECKED CC APPROVED CC		DATE 06/09/04 06/09/04 06/09/04	
MATERIAL FINISH		TITLE WIRING HARNESS H5906		P/N H5906	
DO NOT SCALE		SCALE		DRAWING NUMBER H5906	
				SHEET 1 OF 1	

ENDICOTT RESEARCH GROUP, INC.
2601 WARNE ST., ENDICOTT, NY 13760 607-754-9187

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Digital View:](#)

[426061100](#)