

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-017552	01AUG06	JMS	FWK

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 Ni PLATING
- 5 ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:

DC - 11 GHz

NOMINAL IMPEDANCE:

50 Ohm

INSULATION RESISTANCE:

5000 MOhm

WORKING VOLTAGE:

1000 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:

2500 Volts RMS Max

CONTACT RESISTANCE:

CENTRE CONTACT:

1.00 mOhm Max

OUTER CONTACT:

1.00 mOhm Max

VSWR @ xGHz:

N/A

INSERTION LOSS xdb:

N/A
- 6 MECHANICAL CHARATERISTICS

COUPLING RETENTION FORCE:


445N Min

DURABILITY:


500 Cycles Min
- 7 ENVIRONMENTAL CHARACTERISTICS

OPERATING TEMPERATURE:

-65 to +165 DegC
- 8 FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 9 ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



		1	1	BRASS	4	BODY 2	6
		1	1	BRASS	4	CHASSIS	5
		1	1	BRASS	3	CONTACT II	4
		1	1	BRASS	3	CONTACT I	3
		3	3	PTFE		INSULATION	2
		1	1	BRASS	4	BODY 1	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		4	4				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL	01AUG06	tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE	
DIMENSIONS: mm		CHK S.PARLOW	01AUG06		
		APVD F.WHEELER-KING		NAME TYPE N T. ADAPTOR J-J-J 50 OHM	
		PRODUCT SPEC —			
MATERIAL SEE TABLE		APPLICATION SPEC —		SIZE A3	
		WEIGHT —		CAGE CODE 00779	
FINISH —		CUSTOMER DRAWING		DRAWING NO C-1478177	
				RESTRICTED TO —	
				SCALE NTS	
				SHEET 1 OF 1	
				REV B	