


60 Watts

APA18 (18 Amps)

Total Power: 60 Watts
 Input Voltages: 3.0V to 5.5V
 No. of Outputs: Single



Special Features

- Point of load (POL) applications
- High Current slew rate at 2.5A/us¹
- Open frame SIP
- High efficiency, 3.3V @ 95% (Typ)
- Adjustable Output through external resistor programming
- -40°C to +85°C Ambient operating temperature
- UVLO protection
- Positive Enable function
- Low output ripple and noise
- Regulation to zero load

Environmental

Operating temperature
 -40°C to +85°C (Ambient temperature)
 Storage temperature: -40°C to +125°C
 MTBF: >1 million hours

Safety

UL, cUL 609500 Recognized (Pending)
 TUV EN60950 Licensed (Pending)

Electrical Specs

Input

Input range 3.0V to 5.5V
 Efficiency 3.3V @ 95% (Typ)

Control

Enable TTL compatible
 (positive enable)

Output

Line Regulation <0.5%
 Load Regulation
 0.75Vo 10mV
 0.75 < Vo < 3.3V 15mV
 3.3V ≤ Vo 30mV
 Load Current 18A max (Po ≤ 60W)
 Ripple and noise 50mV_{p-p}
 Output Adjust Range 0.75V - 3.3V
 Current Slew Rate up to 2.5A/μS
 Transient Response¹ 300mV typical deviation (3.3Vo)
 for 50% to 100% step load
 100 μS recovery
 Remote Sense 10% of Vo
 Turn On Input Voltage 3.0V (Typical)
 OCP/OTP Hiccup - auto recovery
 Isolation Non-Isolated module

Specifications subject to change without notice.

Note: 1. with output capacitor of 100uF Tantalum + 1 uF Ceramic cap

AMERICAS

5810 Van Allen Way
Carlsbad, CA 92008
Telephone: 760-930-4600
Facsimile: 760-930-0698

EUROPE

Astec House, Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX, UK
Telephone: 44 (1384) 842-211
Facsimile: 44 (1384) 843-355

ASIA

Units 2111-2116, Level 21
Tower1, Metroplaza
223, Hing Fong Road
Fwai Fong, New Territories
Hong Kong
Telephone: 852-2437-9662
Facsimile: 852-2402-4426



APA18T04-9

Ordering Information

Input Voltage	Output Voltage	Output Current	Efficiency Full Load (Typ)	Model Number
3.0V - 5.5V	0.75 to 3.6V	18A	95%	APA18T04-9
3.0V - 5.5V	0.75 to 3.6V	18A	95%	APA18T04-9H


Note:

- 18A max output current with total output power limited to 60W - minimal output derating required
- Typical Efficiency for 3.3V output; full load; nominal input voltage; 200LFM at $T_A=25^\circ\text{C}$
- Suffix "H" for Horizontal pins

Pin Assignment

Notes:

1. All specifications are typical at nominal line, full load and 25°C ambient temperature unless otherwise noted.
2. All specifications subject to change without notice. Mechanical drawings are for reference only
3. Technical Reference Notes should be consulted for detailed information
4. Warranty: 1yr



Mechanical Dimensions - Vertical type

* Astec reserves the right to make changes to the information contained herein without notice and assumes no liability as a result of its use or application. (REV B: August, 2005)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Emerson Network Power:

[APA18T04-9L](#) [APA18T12-9L](#)