






PART NUMBER CODING
SWR204-NREN-D__-ST-GA

NUMBER OF POSITIONS

(CONTACTS PER ROW)



RECOMMENDED PCB LAYOUT



- NOTES:
1. INSULATOR MATERIAL: NYLON66, UL94V-0, COLOR:GREY (PANTONE 7528C).
 2. CONTACT MATERIAL: BRASS.
 3. CONTACT PLATING: TIN OVERALL.
 4. CURRENT RATING: 3 AMPS.
 5. VOLTAGE RATING: 250V AC/DC.
 6. INSULATOR RESISTANCE: 1000 MEGOHMS MIN.
 7. CONTACT RESISTANCE: 10 MILLIOHMS MAX.
 8. DIELECTRIC WITHSTANDING VOLTAGE: 800V AC.
 9. OPERATING TEMPERATURE: -25° C TO +85° C.
 10. MATES WITH SWH204 SERIES DUAL ROW HOUSING.



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM[INCHES]
TOLERANCES:
ANGULAR: ± 5°
.X= ± .3 [.01]
.XX= ± .15 [.006]
.XXX= ± .050 [.0020]
SURFACE FINISH: 63 Rc
REMOVE ALL BURRS AND SHARP EDGES .010 MAX

INTERPRET DIMENSIONS AND GEOMETRIC TOLERANCING PER: ANSI Y14.5M-1994

THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.

DATE

7/17/2009

NAME

JH

DESCRIPTION

WAFER, 2mm CC, DUAL ROW, ST

PART NUMBER

SWR204-NREN-D__-ST-GA

SIZE

C

DWG. NO.

11285

REV

A

SCALE: 5:1

SHEET 1 OF 1

SULLINS

CONNECTOR SOLUTIONS

DESCRIPTION

WAFER, 2mm CC, DUAL ROW, ST

PART NUMBER

SWR204-NREN-D__-ST-GA