

EMI FILTER & TVS ARRAY

APPLICATIONS

- ✓ Cellular Phones
- ✓ SMART Cards
- ✓ Notebooks & Handheld Devices
- ✓ Personal Digital Assistants (PDAs)
- ✓ Ground Positioning Systems (GPS)

IEC COMPATIBILITY (EN61000-4)


- ✓ 61000-4-2 (ESD): Air - 15kV, Contact - 8kV
- ✓ 61000-4-4 (EFT): 40A - 5/50ns

FEATURES


- ✓ ESD Protection > 25 kilovolts
- ✓ 18 Watts Peak Pulse Power per Line (8/20μs)
- ✓ Bidirectional EMI Filtering/TVS Low Pass Filters
- ✓ Low Insertion Loss: -3db Roll-Off @ 200MHz
- ✓ Protects Up to Two (2) Data Lines

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SC-70-5L
- ✓ Weight 0.1 grams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ 8mm Tape and Reel Per EIA Standard 481-1-A
- ✓ Device Marking: Marking Code



PIN CONFIGURATION



EMIF01-100 & EMIF01-150

DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified			
PARAMETER	SYMBOL	VALUE	UNITS
Peak Pulse Power ($t_p = 8/20\mu s$) - See Figure 1	P_{PP}	18	Watts
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C
Typical Series Resistance per Line	R	100 to 150	Ohms

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified							
PART NUMBER	DEVICE MARKING	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM REVERSE LEAKAGE CURRENT $V_{WM} = 3V$ I_D μA	TYPICAL FORWARD VOLTAGE I@50mA, 8/20 μs V_F VOLTS	CUT-OFF FREQUENCY MHz	MAXIMUM CAPACITANCE (See Note 1) 0V @ 1 MHz C pF
EMIF01-100	E10	3.0	6.0	0.5	1.0	220	50
EMIF01-150	E15	3.0	6.0	0.5	1.0	200	50

Note 1: Cin between pins 1 & 2, 3 & 2, 4 & 2 and 5 & 2.

GRAPHS

FIGURE 1
PEAK PULSE POWER VS PULSE TIME




FIGURE 2
PULSE WAVE FORM






FIGURE 3
OVERSHOOT & CLAMPING VOLTAGE FOR EMIF01-100



ESD Test Pulse: 25 kilovolt, 1/30ns (waveform)

EMIF01-100 & EMIF01-150

PACKAGE OUTLINE & DIMENSIONS



PART NUMBER SUFFIXES USED FOR TAPE & REEL ORDERING:
 Surface mount product is taped and reeled in accordance with EIA-481.
 Suffix-T7 = 7 Inch Reel - 3,000 pieces per reel i.e.: EMIF01-100-T7
 Suffix-T13 = 13 Inch Reel - 10,000 pieces per reel i.e.: EMIF01-100-T13

ProTek Devices
 2929 South Fair Lane, Tempe, AZ 85282
 Tel: 602-431-8101 Fax: 602-431-2288
 E-Mail: sales@protekdevices.com
 Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2003

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.