

Single-Phase Auto Transfer Switch / Metered PDU, 1.4kW 15A 120V, 1U Horizontal Rackmount, 8 NEMA 5-15R outlets, 2 NEMA 5-15P inputs

MODEL NUMBER: PDUMH15AT



Description

Tripp Lite Metered ATS / Auto Transfer Switch provides a redundant power option for single-corded network devices. Dual input cords support separate connection to PRIMARY and SECONDARY power sources. The ATS will normally maintain continuous output to all outlets as derived from the primary input cable. If the primary power source becomes unstable or fails altogether, the ATS will switch over to the secondary power source until the primary input is restored and stable. Super-fast switchover between primary and secondary power sources occurs within milliseconds. ATS functionality is supported by any two compatible AC power sources, regardless of phase angle, to support a variety of advanced redundant power networking applications. Enables fault tolerant hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system. In a two-UPS environment, the primary input cable must be supported by a full time sine wave UPS with zero transfer time. Tripp Lite SmartOnline series is highly recommended for use as the primary UPS in a two-UPS application. ATS configurations utilizing separate mains circuits, backup generators and even separate utility power grid feeds are fully supported. On-board ATS processor constantly evaluates power quality on both input sources to prevent transfer to the secondary source when unavailable or of lower quality than the primary source. Front input LED's display primary or secondary power availability.

Features

- 120V 15A Automatic Transfer Switch (ATS) / Metered PDU (Agency de-rated to 12A continuous)
- Provides a redundant power option for critical networking equipment with a single input power cord
- 2 digit display reports output power consumption in amps
- 1U horizontal rackmount form factor; 14.5 in. / 36.8 cm depth
- 8 built-in NEMA 5-15R outlets
- Set of two 12 ft. / 3.6m NEMA 5-15P input cables support connection to separate PRIMARY and SECONDARY power sources
- ATS circuits normally maintain output sourced from the primary input cable; As primary input power fails or becomes unstable, the ATS will switch to maintain output sourced from the secondary input cable until power on the primary input is restored and stable
- ATS configurations enable fault-tolerant, hot-swappable UPS protection when used with a single UPS and fully redundant UPS protection when each cord is connected to a separate UPS system (in a two-UPS environment, the primary input cable must be supported by an online UPS with zero transfer time)

Highlights

- Single phase 15A 120V Auto Transfer Switch / ATS PDU
- Enables redundant-power option for single-corded network devices
- Separate primary & secondary inputs connect to any two compatible power sources
- 1U horizontal rackmount; 2 NEMA 5-15P inputs; 8 NEMA 5-15R outlets
- Two digit visual current meter; Upgrade options available

Applications

- Ideal means to provide single-corded network gear a redundant power option

Package Includes

- PDU with attached 5-15P primary input cord
- Detachable C13 to NEMA 5-15P 12 ft / 3.6m secondary input cord
- 1U mounting brackets
- User manual with warranty information



similar to Tripp Lite SmartOnline series)

- Advanced ATS configurations utilizing separate mains circuits, backup generators and even separate out of phase utility power grid feeds are fully supported
- On-board ATS processor constantly evaluates power quality on both inputs to prevent transfer to the secondary source when unavailable or of lower quality than the primary source
- Super-fast switchover between primary and secondary power sources occurs in 2-7 milliseconds
- Built-in card slot supports optional SNMPWEBCARD for permanent upgrade to a switched & monitored PDU system
- Outlets are factory programmed for sequential turn-on at 250 millisecond intervals when the PDU is first energized to prevent inrush-related equipment interaction on startup
- Front panel LEDs confirm power availability on both input lines
- TAA Compliant Version Available - Order Tripp Lite PDUMH15ATAA

Specifications

OVERVIEW	
PDU Type	Auto-Transfer Switch; Metered
OUTPUT	
Output Capacity Details	1.4kW (120V input), 1.5kW (127V input), 1.2kW (100V input); 15A maximum (Agency de-rated to 12A continuous)
Frequency compatibility	60 Hz
Output VA	1800
Output nominal voltage	100-127V nominal, single phase
Outlet quantity / type	8 NEMA 5-15R
Outlet Type	NEMA 5-15R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps (A)	15
Maximum Input Amps (A) Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input cord length (ft.)	12
Input cord length (m)	3.66
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Front panel LEDs	10 front panel LEDs display power on - off status for each outlet, plus 3 LEDs for power status on each input line cord. Digital Current Meter displays output power consumption in amps.
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (HWD/in)	6.25 x 22.5 x 23.5
Shipping Dimensions (HWD/cm)	15.9 x 57.2 x 59.7
Shipping weight (lbs)	15.2
Shipping weight (kg)	6.9
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 14.5
Unit Dimensions (HWD/cm)	4.44 x 44.4 x 36.8
Unit weight (lbs)	11
Unit weight (kg)	5
Material of construction	Steel
Style	Rackmount
Form factors supported	1U rackmount
PDU Form Factor	Horizontal (1U, 2U, etc)
ENVIRONMENTAL	
Relative Humidity	Up to 95% (non-condensing)
COMMUNICATIONS	
SNMP compatibility	Includes slot for optional SNMPWEBCARD accessory to enable remote individual outlet control over IP
SPECIAL FEATURES	
Appearance	Black 1U rackmount steel chassis
CERTIFICATIONS	
TAA Compliant Option	TAA Compliant Version Available - Order Tripp Lite PDUMH15ATAA
Certifications	Tested to UL 60950-1 (USA), CSA (Canada), Class A (Emissions), NOM (Mexico), RoHS compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[PDUMH15AT](#)