


TH-TM Indent Hinge - No Mounting Hole (Stainless)





Characteristic

Choose the size from wide variety of selections.

Application

Various types of industrial machines



Parts List

No.	Part Name	Material	Finish	Quantity
1	Hinge Piece (A)	SUS304	—	1
2	Hinge Piece (B)			1
3	Shaft			1

Specification (a)

Model No.	A	B	C	D	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-55	30	50	φ3	t1.5	5	8	26.0	2055
TH-TM-65		51	φ2	t0.8		2	12.5	2065
TH-TM-56	35	50	φ3	t1.5	3	12	27.5	2056
TH-TM-54		45		t1.2		9	23.5	2054
TH-TM-57	40	75	φ4	t1	5	5	37.0	2057
TH-TM-66	41.5	64	φ3	t1.2		6	34.0	2066
TH-TM-58	45	75	φ4	t2		60	73.0	2058
TH-TM-67	48	76		t1.5		8	58.0	2067
TH-TM-68	56	89	φ5	t2		10	85.0	2068
TH-TM-69	71.5	102		t2		18	154.0	2069

Specification (b)

Model No.	A	B	C	D	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-62	18.5	25	ϕ 2	t0.8	4	2	4.5	2062
TH-TM-63	21.5	32				2	6.5	2063
TH-TM-64	26	38				2	8.5	2064
TH-TM-61	40	500	ϕ 3	t1.5	40	—	308.0	2061
TH-TM-59	50	150	ϕ 4		6	—	124.0	2059
TH-TM-60		200		t1.2	16	—	131.0	2060

TH-TM Indent Hinge - No Mounting Hole (Stainless)




Characteristic

Choose the size from wide variety of selections.

Application

Various types of devices



Parts List

No.	Part Name	Material	Finish		Quantity
			No.100~ No.111	No.118~ No.121	
1	Hinge Piece(A)	SUS304	Barrel Polishing	Buffing	1
2	Hinge Piece(B)				1
3	Shaft			—	1

Specification

Model No.	A	B	C	D	Division	Door Weight (kg)	Net Weight (g)	Code No.
TH-TM-100	20	25	φ2.1	t0.8	3	2	4.7	2165
TH-TM-101	22	32				2	6.6	2166
TH-TM-102	26	38				2	9.4	2167
TH-TM-103	34		φ3.1	t1.2		17	17.8	2168
TH-TM-104	30	51	φ2.4	t0.8	5	3.2	13.8	2169
TH-TM-105	38		φ3.4	t1.2	3	20	26.6	2170
TH-TM-106	33	64	φ2.4	t1.0	5	14	20.6	2171
TH-TM-118		40	φ3	t1.5	3	23	22.7	2152
TH-TM-119		50				27	28.7	2153
TH-TM-107	42	64	φ3.4	t1.2	5	6	35.4	2172
TH-TM-108	41	76	φ3.1	t1.0		14	34.6	2173
TH-TM-109	49		φ4.2	t1.5		8	61.0	2174
TH-TM-110	56	89	φ5.2	t1.7		36	98.4	2175
TH-TM-111	70	102	φ5.6	t1.8		37	144.9	2176
TH-TM-120	50	65	φ4.5	t2	5	—	72.6	2154
TH-TM-121		75				—	83.2	2155