




SEMITOP[®] 2

IGBT Module

SK 9GD065


Preliminary Data

Features

- Compact design
- One screw mounting
- Heat transfer and isolation through direct copper bonded aluminium oxide ceramic (DCB)
- Ultrafast NPT technology IGBT
- CAL technology FWD

Typical Applications


- Switching (not for linear use)
- Inverter
- Switched mode power supplies
- UPS



GD

Absolute Maximum Ratings				$T_s = 25\text{ °C}$, unless otherwise specified	
Symbol	Conditions			Values	Units
IGBT					
V_{CES}	$T_j = 25\text{ °C}$			600	V
I_C	$T_j = 125\text{ °C}$	$T_s = 25\text{ °C}$		11	A
		$T_s = 80\text{ °C}$		8	A
I_{CRM}	$I_{CRM} = 2 \times I_{Cnom}$			12	A
V_{GES}				± 20	V
t_{psc}	$V_{CC} = 300\text{ V}$; $V_{GE} \leq 20\text{ V}$; $T_j = 125\text{ °C}$ $V_{CES} < 600\text{ V}$			10	μs
Inverse Diode					
I_F	$T_j = 125\text{ °C}$	$T_s = 25\text{ °C}$		22	A
		$T_s = 80\text{ °C}$		15	A
I_{FRM}	$I_{FRM} = 2 \times I_{Fnom}$			30	A
Module					
$I_{t(RMS)}$					A
T_{vj}				-40 ... +150	$^{\circ}\text{C}$
T_{stg}				-40 ... +125	$^{\circ}\text{C}$
V_{isol}	AC, 1 min.			2500	V

Characteristics			T _s = 25 °C, unless otherwise specified			
Symbol	Conditions		min.	typ.	max.	Units
IGBT						
V _{GE(th)}	V _{GE} = V _{CE} , I _C = 0,2 mA		3	4	5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = V _{CES} T _j = 25 °C T _j = 125 °C				0,03	mA mA
I _{GES}	V _{CE} = 0 V, V _{GE} = 20 V T _j = 25 °C T _j = 125 °C				120	nA nA
V _{CE0}	T _j = 25 °C T _j = 125 °C			1,2 1,1		V V
r _{CE}	V _{GE} = 15 V T _j = 25°C T _j = 125°C			133 183		mΩ mΩ
V _{CE(sat)}	I _{Cnom} = 6 A, V _{GE} = 15 V T _j = 25°C _{chiplev.} T _j = 125°C _{chiplev.}			2 2,2	2,5 2,7	V V
C _{ies} C _{oes} C _{res}	V _{CE} = 25, V _{GE} = 0 V f = 1 MHz			0,35 0,038 0,023		nF nF nF
t _{d(on)} t _r E _{on}	R _{Gon} = 120 Ω	V _{CC} = 300V I _{Cnom} = 6A		20 25 0,22		ns ns mJ
t _{d(off)} t _f E _{off}	R _{Goff} = 120 Ω	T _j = 125 °C V _{GE} =±15V		145 25 0,12		ns ns mJ
R _{th(j-s)}	per IGBT				2,6	K/W



IGBT Module

SK 9GD065


Preliminary Data

Features

- Compact design
- One screw mounting
- Heat transfer and isolation through direct copper bonded aluminium oxide ceramic (DCB)
- Ultrafast NPT technology IGBT
- CAL technology FWD

Typical Applications


- Switching (not for linear use)
- Inverter
- Switched mode power supplies
- UPS




Characteristics						
Symbol	Conditions		min.	typ.	max.	Units
Inverse Diode						
V _F = V _{EC}	I _{Fnom} = 15 A; V _{GE} = 0 V	T _j = 25 °C _{chiplev.}		1,4	1,7	V
		T _j = 125 °C _{chiplev.}		1,4	1,7	V
V _{F0}		T _j = 25 °C		1	1,1	V
		T _j = 125 °C		0,9	1	V
r _F		T _j = 25 °C		30	40	mΩ
		T _j = 125 °C		33	47	mΩ
I _{RRM}	I _{Fnom} = 15 A	T _j = 125 °C		22		A
Q _{rr}	di/dt = 1100 A/μs			1,5		μC
E _{rr}	V _{CC} = 300V			0,31		mJ
R _{th(j-s)D}	per diode				2,3	K/W
M _s	to heat sink				2	Nm
w				21		g

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX.

This technical information specifies semiconductor devices but promises no characteristics. No warranty or guarantee expressed or implied is made regarding delivery, performance or suitability.



Case T47 (Suggested hole diameter, in the PCB, for solder pins and plastic mounting pins: 2mm)



Case T 47

GD