





COIL: @ 25°C
 RESISTANCE _____ 50 OHMS $\pm 10\%$
 NOMINAL VOLTAGE _____ 5.0 VDC
 MUST OPERATE _____ 2.7 VDC
 MUST RELEASE _____ 1.4 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:

VIBRATION _____ 10 _____ CPS TO _____ 3000 _____ CPS @ _____ 30 _____ g's
 SHOCK _____ 75 _____ g's _____ 6 _____ MS. DURATION
 TEMPERATURE _____ -65 _____ °C TO _____ +125 _____ °C

NOTES: _____ OPERATE TIME 2.0 MS MAX
 _____ RELEASE TIME 4.0 MS MAX
 _____ CONTACT BOUNCE TIME 1.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: _____ LOW LEVEL TO
 1 AMP 28 VDC RESISTIVE 100,000 OPERATIONS

DR. _____ R.B. 10/23/98 (CK) _____ 10/20/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. _____ C. I. I. STD.
 CUST. NO. _____ REV. _____

SMGAD RELAY

SMGAD-5