


TOSHIBA Transistor Silicon PNP Epitaxial Type (PCT process) (Transistor with Built-in Bias Resistor)

RN2901AFS, RN2902AFS, RN2903AFS RN2904AFS, RN2905AFS, RN2906AFS


Switching, Inverter Circuit, Interface Circuit and
Driver Circuit Applications

- Two devices are incorporated into a fine-pitch, small-mold (6-pin) package.
- Incorporating a bias resistor into a transistor reduces the parts count.
Reducing the parts count enables the manufacture of ever more compact equipment and saves assembly cost.
- Complementary to the RN1901AFS~RN1906AFS
- Lead (Pb) - free

Equivalent Circuit and Bias Resistor Values



Type No.	R1 (kΩ)	R2 (kΩ)
RN2901AFS	4.7	4.7
RN2902AFS	10	10
RN2903AFS	22	22
RN2904AFS	47	47
RN2905AFS	2.2	47
RN2906AFS	4.7	47




Maximum Ratings (Ta = 25°C) (Q1, Q2 common)

Characteristic	Symbol	Rating	Unit
Collector-base voltage	V _{CB0}	−50	V
Collector-emitter voltage	V _{CEO}	−50	V
Emitter-base voltage	V _{EBO}	−10	V
		−5	V
Collector current	I _C	−80	mA
Collector power dissipation	P _C (Note)	50	mW
Junction temperature	T _j	150	°C
Storage temperature range	T _{stg}	−55~150	°C







Note: Total rating







Equivalent Circuit (top view)















Electrical Characteristics (Ta = 25°C) (Q1, Q2 common)

Characteristic		Symbol	Test Condition	Min	Typ.	Max	Unit
Collector cutoff current	RN2901AFS~2906AFS	I_{CBO}	$V_{CB} = -50\text{ V}, I_E = 0$	—	—	-100	nA
		I_{CEO}	$V_{CE} = -50\text{ V}, I_B = 0$	—	—	-500	
Emitter cutoff current	RN2901AFS	I_{EBO}	$V_{EB} = -10\text{ V}, I_C = 0$	-0.89	—	-1.33	mA
	RN2902AFS			-0.41	—	-0.63	
	RN2903AFS			-0.18	—	-0.29	
	RN2904AFS			-0.088	—	-0.133	
	RN2905AFS	I_{EBO}	$V_{EB} = -5\text{ V}, I_C = 0$	-0.085	—	-0.127	
	RN2906AFS			-0.08	—	-0.121	
DC current gain	RN2901AFS	h_{FE}	$V_{CE} = -5\text{ V}, I_C = -10\text{ mA}$	30	—	—	
	RN2902AFS			50	—	—	
	RN2903AFS			70	—	—	
	RN2904AFS			80	—	—	
	RN2905AFS			80	—	—	
	RN2906AFS			80	—	—	
Collector-emitter saturation voltage	RN2901AFS	$V_{CE(sat)}$	$I_C = -5\text{ mA}, I_B = -0.5\text{ mA}$	—	—	-0.15	V
	RN2902AFS~2906AFS		$I_C = -5\text{ mA}, I_B = -0.25\text{ mA}$				
Input voltage (ON)	RN2901AFS	$V_{I(ON)}$	$V_{CE} = -0.2\text{ V}, I_C = -5\text{ mA}$	-1.2	—	-2.2	V
	RN2902AFS			-1.2	—	-2.6	
	RN2903AFS			-1.3	—	-3.5	
	RN2904AFS			-1.5	—	-5.0	
	RN2905AFS			-0.6	—	-1.1	
	RN2906AFS			-0.7	—	-1.3	
Input voltage (OFF)	RN2901AFS~2904AFS	$V_{I(OFF)}$	$V_{CE} = -5\text{ V}, I_C = -0.1\text{ mA}$	-0.8	—	-1.5	V
	RN2905AFS, 2906AFS			-0.5	—	-0.8	
Collector output capacitance	RN2901AFS~2906AFS	C_{ob}	$V_{CB} = -10\text{ V}, I_E = 0, f = 1\text{ MHz}$	—	-0.9	—	pF
Input resistor	RN2901AFS	R1	—	3.76	4.7	5.64	k Ω
	RN2902AFS			8	10	12	
	RN2903AFS			17.6	22	26.4	
	RN2904AFS			37.6	47	56.4	
	RN2905AFS			1.76	2.2	2.64	
	RN2906AFS			3.76	4.7	5.64	
Resistor ratio	RN2901AFS~2904AFS	R1/R2	—	0.8	1.0	1.2	
	RN2905AFS			0.0376	0.0468	0.0562	
	RN2906AFS			0.08	0.1	0.12	









Type Name	Marking
RN2901AFS	
RN2902AFS	
RN2903AFS	
RN2904AFS	
RN2905AFS	
RN2906AFS	

RESTRICTIONS ON PRODUCT US

030619EAA

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.