





P Series

Audio

[back](#)

[Print](#)

NC7FP-1



Smallest available traditional style metal panel mount connector with large solder cups for ease hard wiring.





7 pole female receptacle, solder contacts, Nickel housing, silver contacts

Features & Benefits

- Smallest available hard wiring receptacles with large solder cups
- Short female receptacle
- Compatible with switchcraft D*M, D*F; Cannon XLB2*31, XLB2*32

Frontplattenausschnitt (Rückseite)

Panel cut out (rear side)



				*Lieferant darf ohne Ruecksprache nicht geaendert werden	Werkstoff:	Massstab:		Datum	Name
				Zeichnung urheberrechtlich geschuetzt (DIN 34) (C)		2:1	Gezeichnet	09.11.90	Illenberger
				Benennung:	(FP-1)		Geprueft		
					NC7FP-1		Gesehen		
							Ersetzt durch:		Blatt
							Ersatz fuer:		von Blatt
A	Aktuelle Zeichnung	25.03.98	Alinjak				Zechn. Nr.	3102 St 11 16	
Ind.	Aenderung	Datum	Name						

NEUTRIK AG FL-9494 SCHAAN




P Series



Audio

NC7FP-1



There are no technical infos for this product.

Product

Connector Type	XLR
Gender	female

Electrical

Capacitance between contacts	≤ 9 pF
Contact resistance	≤ 5 m Ω
Dielectric strength	1,5 kVdc
Insulation resistance	> 2 G Ω (initial)
Insulation resistance	> 1 G Ω (after damp heat test)
Rated current per contact	5 A
Rated voltage	50 V

Mechanical

Insertion force	≤ 20 N
Withdrawal force	≤ 20 N

Lifetime	> 1000 mating cycles
Wire size	max. 1.0 mm ²
Wire size	max. 18 AWG
Wiring	Solder contacts
Locking device	latch lock
Mounting direction	front
Chassis shape	P
Material	
Contact plating	2 µm Ag over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6.6 30 % GR)
Locking element	Steel Ck67
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C
Optical	
Mobile Cables	