



PRODUCT SPECIFICATION

MICRO-FIT

1.0 SCOPE

This Product Specification covers the 3.00 mm (.118 inch) centerline (pitch) square pin headers when mated with either printed circuit board (PCB) connector or connectors terminated with 20 to 30 AWG wire using crimp technology.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBERS

Receptacle: 43025 Terminal: 43030
Plug: 43020 Terminal: 43031
Headers: 43045, 44914
Test Plug: 44242 (recommended for continuity testing only)
Other products conforming to this specification are noted on the individual drawings.

2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

Housings: Receptacle and Plug - Polyester, Nylon; Headers - LCP
Terminal: Phosphor Bronze
Pins: Brass, Modified Tin/Brass

2.3 SAFETY AGENCY APPROVALS

File Numbers:
UL: E29179
CSA: LR19980
TUV: 72081037

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

Test Summary: TS-43045-001

4.0 RATINGS

4.1 SAFETY AGENCY RATINGS

Series	Agency Voltage Rating (AC RMS or DC)			Agency Current Rating (Single Circuit) (Amps)		
	UL	CSA	TUV	UL	CSA	TUV
43020	350	250	250	5	7	5
43025	600	250	250	5	7	5
43045	600	250	250	5	5	5
44914	600	250	250	5	5	5

(Current ratings are maximum and may vary depending on wire size, circuit count, and end-use application. Further testing may be required in the end-use application.)

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
M8	EC No: UCP2012-1359	PRODUCT SPECIFICATION			1 of 8
	DATE: 2011/10/28	MICRO-FIT			
		DUAL ROW CONNECTORS			
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-43045		MMSTROH	SSOUSEK	FSMITH	



PRODUCT SPECIFICATION

4.2 CURRENT DERATING AND APPLICABLE WIRES

Current is dependent on connector size, contact material, plating, ambient temperature, printed circuit board characteristics and related factors. Actual current rating is application dependent and should be evaluated for each application.

<u>AWG</u>	<u>Max. Outside Insulation Diameter</u>
20	1.85 mm (.073 inch)
22	1.85 mm (.073 inch)
24	1.85 mm (.073 inch)
26	1.27 mm (.050 inch)
28	1.27 mm (.050 inch)
30	1.27 mm (.050 inch)

CURRENT DERATING REFERENCE INFORMATION

AWG	2-circuit		6-circuit		12-circuit		24-circuit	
	W-W	W-B	W-W	W-B	W-W	W-B	W-W	W-B
	Amps	Amps	Amps	Amps	Amps	Amps	Amps	Amps
20	6.5	7	5	* 5.5	4.5	* 5	* 4	4.5
22	5.5	* 6	* 4	* 4.5	* 3.5	* 4	* 3	* 3.5
24	5	5.5	4	* 4.5	3	* 3.5	* 2	* 3
26	4	4.5	3	* 4	2.5	* 3.5	* 1.5	2.5
28	3	* 4	* 2	* 3	* 2	* 3	* 1	* 2
30	3	3.5	2	* 3	2	* 2.5	* 1	1

- 1) Values are for REFERENCE ONLY.
- 2) Current deratings are based on not exceeding 30°C Temperature Rise.
- 3) PCB trace design can greatly affect temperature rise results in Wire-to-Board applications.
- 4) Data is for all circuits powered.
- 5) * indicates interpolated information.
- 6) **W-W**: Wire-to-Wire **W-B**: Wire-to-Board

4.3 CURRENT FOR TEST PLUG 44242

2.5 Amps Maximum (Pogo pin current capacity)

Test plugs are for testing purposes only and not intended for continuous use.

4.4 TEMPERATURE

Operating: - 40°C to + 105°C (Including Terminal Temperature Rise)

Non-operating: - 40°C to + 105°C

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
M8	EC No: UCP2012-1359	PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS			2 of 8
	DATE: 2011/10/28				
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-43045		MMSTROH	SSOUSEK	FSMITH	



PRODUCT SPECIFICATION

5.0 PERFORMANCE

5.1 ELECTRICAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Contact Resistance (Low Level)	Mate connectors: apply a maximum voltage of 20 mV and a current of 100 mA. (Does not include wire resistance)	10 milliohms MAXIMUM [initial]
Contact Resistance of Wire Termination (Low Level)	Terminate the applicable wire to the terminal and measure wire using a voltage of 20 mV and a current of 100 mA.	5 milliohms MAXIMUM [initial]
Insulation Resistance	Unmate & unmount connectors: apply a voltage of 500 VDC between adjacent terminals and between terminals to ground.	1000 Megohms MINIMUM
Dielectric Withstanding Voltage	Unmate connectors: apply a voltage of {two times the rated voltage plus 1000 volts} VAC for 1 minute between adjacent terminals and between terminals to ground.	No breakdown; current leakage < 5 mA
Capacitance	Measure between adjacent terminals at 1 MHz.	2 picofarads MAXIMUM
Temperature Rise (via Current Cycling)	Mate connectors: measure the temperature rise at the rated current after: 1) 96 hours (steady state) 2) 240 hours (45 minutes ON and 15 minutes OFF per hour) 3) 96 hours (steady state)	Temperature rise: +30°C MAXIMUM

5.2 MECHANICAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Connector Mate and Unmate Forces	Mate and unmate connector (male to female) at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute. (Per circuit)	8.0 N (1.8 lbf) MAXIMUM insertion force & 3.7 N (0.8 lbf) MINIMUM withdrawal force
Terminal Retention Force (in Housing)	Axial pullout force on the terminal in the housing at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	24.5 N (5.5 lbf) MINIMUM retention force
Terminal Insertion Force (into Housing)	Apply an axial insertion force on the terminal at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	14.7 N (3.3 lbf) MAXIMUM insertion force

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
M8	EC No: UCP2012-1359 DATE: 2011/10/28	PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	3 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43045	MMSTROH	SSOUSEK	FSMITH



PRODUCT SPECIFICATION

5.2 MECHANICAL REQUIREMENTS

Durability	Mate connectors up to 30 cycles at a maximum rate of 10 cycles per minute prior to Environmental Tests.	20 milliohms MAXIMUM (change from initial)
Vibration (Random)	Mate connectors and vibrate per EIA 364-28, test condition VII, Letter D. Test Duration: 15 minutes each axis.	20 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
Shock (Mechanical)	Mate connectors and shock at 50 g's with 1/2 sine wave (11 milliseconds) shocks in the $\pm X, \pm Y, \pm Z$ axes (18 shocks total).	20 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
Wire Pullout Force (Axial) (Wire from Terminal)	Apply an axial pullout force on the wire at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	MINIMUM pullout force 20 awg: 57.8 N (13.0 lbf) 22 awg: 35.6 N (8.0 lbf) 24 awg: 22.2 N (5.0 lbf) 26 awg: 13.3 N (3.0 lbf) 28 awg: 8.9 N (2.0 lbf) 30 awg: 6.6 N (1.5 lbf)
Normal Force	Apply a perpendicular force.	2.7 N (0.6 lbf) MINIMUM
Pin to Header Retention	Apply axial push force to pin at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	13.7 N (3.1 lbf) MINIMUM pushout force
Thumb Latch to Ramp Yield Strength	Full mate and then Unmate the connectors at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	68.4 N (15.4 lbf) MINIMUM Yield Strength
Panel Mount Retention	Insert connector in panel. Apply an axial force on the connector in the opposite direction of insertion at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	155.7 N (35 lbf) MINIMUM pushout force
Compliant Pin Insertion Force into PCB Hole (44914 Series)	Apply an axial insertion force on the terminal at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	106.7 N (24 lbf) MAXIMUM Insertion force (Per Terminal)
Compliant Pin Retention Force in PCB Hole (44914 Series)	Apply an axial extraction force on the terminal at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	35.6 N (8 lbf) MINIMUM Retention force (Per Terminal)

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
M8	EC No: UCP2012-1359 DATE: 2011/10/28	PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	4 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43045	MMSTROH	SSOUSEK	FSMITH



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Thermal Aging	Mate connectors; expose to: 240 hours at $105 \pm 2^{\circ}\text{C}$ OR 500 hours at $85 \pm 2^{\circ}\text{C}$	20 milliohms MAXIMUM (change from initial)
Humidity (Steady State)	Mate connectors: expose to a temperature of $40 \pm 2^{\circ}\text{C}$ with a relative humidity of 90-95% for 96 hours. Note: Remove surface moisture and air dry for 1 hour prior to measurements.	20 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 1000 Megohms MINIMUM
Solderability	Per SMES-152	Solder coverage: 95% MINIMUM (per SMES-152)
Solder Resistance	A) Wave Solder Process Dip connector terminal tails in solder; Solder Duration: 10 seconds MAX Solder Temperature: 260°C MAX Per ES-40000-5013 B) Convection Reflow Solder Process 235°C MAX Per ES-40000-5013 Parts identified with a green dot on the primary shipping carton label and all parts with a manufacturing date after 11/1/2007: 260°C MAX Per ES-40000-5013	Visual: No Damage to insulator material
Cold Resistance	Mate connectors: Duration: 96 hours; Temperature: $-40 \pm 3^{\circ}\text{C}$	20 milliohms MAXIMUM (change from initial)

6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage per the packaging specifications listed below:

Receptacle and Plug: Bulk Packaged

Headers: PK-70873-0313, PK-70873-0314, PK-70873-05**.

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
M8	EC No: UCP2012-1359 DATE: 2011/10/28	PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	5 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43045	MMSTROH	SSOUSEK	FSMITH



PRODUCT SPECIFICATION

7.0 GAGES AND FIXTURES


It is recommended that test plugs (Series 44242) be used for continuity testing of receptacles. Standard mating parts should not be used for harness testing.

NOTE: The use of unauthorized testing devices and/or probes with a Molex product may cause damage to and affect functionality of the Molex product, and such use may void any and all warranties, expressed or implied.

8.0 OTHER INFORMATION

8.1 CABLE TIE AND OR WIRE TWIST LOCATION

CKT Sizes	Dim T Min.
2-8	.500 (12.70)
10-16	.750 (19.10)
18-24	1.000 (25.40)



The "T" dimension defines a "free" length of wire, or a length of wire that is not subject to significant bias by external factors such as a wire tie, wire twisting, or other means of bending or deforming of the wires that repositions them from their natural relaxed state or location where they enter the housing. Wires are to be dressed in such a manner to allow the terminals to float freely in the pocket.

8.2 CONTACT ENGAGEMENT FOR FULLY MATED COMPONENTS

Receptacle	Mated to Plug/ Header	Application	Contact Wipe
43025 Receptacle ⁽¹⁾	43020 Plug	Wire-to-Wire	0.094 in/(2.39 mm)
	43045 Header 44914 CPI Header	Wire-to-Board	0.069 in/(1.75mm)


Note (1): Contact Wipe is based on 43030 female crimp terminal. If using 46235 female crimp terminal, reduce Contact Wipe by .005 in/(0.13 mm).

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
M8	EC No: UCP2012-1359 DATE: 2011/10/28	PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	6 of 8
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43045	MMSTROH	SSOUSEK	FSMITH




PRODUCT SPECIFICATION


8.3 STANDARD POLARIZATION FOR HEADERS AND PLUGS (HEADERS ARE SHOWN)




2-CKT.




14-CKT.




4-CKT.




16-CKT.




6-CKT.




18-CKT.




8-CKT.




20-CKT.




10-CKT.



22-CKT.



12-CKT.




24-CKT.

REVISION: M8	ECR/ECN INFORMATION: EC No: UCP2012-1359 DATE: 2011/10/28	TITLE: PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	SHEET No. 7 of 8
DOCUMENT NUMBER: PS-43045	CREATED / REVISED BY: MMSTROH	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH




PRODUCT SPECIFICATION


8.4 STANDARD POLARIZATION FOR RECEPTACLES




24-CKT.




2-CKT.




22-CKT.




4-CKT.




20-CKT.




6-CKT.




18-CKT.




8-CKT.




16-CKT.



10-CKT.



14-CKT.



12-CKT.

REVISION: M8	ECR/ECN INFORMATION: EC No: UCP2012-1359 DATE: 2011/10/28	TITLE: PRODUCT SPECIFICATION MICRO-FIT DUAL ROW CONNECTORS	SHEET No. 8 of 8
DOCUMENT NUMBER: PS-43045	CREATED / REVISED BY: MMSTROH	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH