








NOTES

- 適合ハウジング: 503764シリーズ
APPLICABLE HPUSING: 503764 SERIES
- 材質: 銅合金
MATERIAL: COPPER ALLOY
- メッキ仕様
PLATING
接点部: 金メッキ
バレル部: 錫メッキ
ニッケル下地メッキ
CONTACT: GOLD PLATING
BARREL: TIN PLATING
NICKEL UNDER PLATING
- 圧着後CS-503765-001の内容を満たす事
FULFILL THE CONTENTS OF CS-503765-001
AFTER CRIMP.
- 圧着時の注意事項としてATS-57427-000を参照
AS ATTENTION AT THE TIME OF CRIMP,
REFER TO ATS-57427-000



SECTION A-A



SECTION B-B

Ø 0.5 - 0.7 mm	AWG #28 -30	5037650098	CHAIN
INS. RANGE	WIRE RANGE	ORDER No.	FORM

RELEASED EC NO: J2014-1278 DRWN: YWAKE CHKD: KASAKAWA APPR: NUKITA A	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		10 UNDER	± 0.2	DRAWN BY YWAKE	DATE 2014/03/03	TITLE 1.0 WORE TO BOARD CONN. R/A H=1.5MM REC CRIMP TERM				
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2014/03/03					
		30 OVER	± 0.3	APPROVED BY NUKITA	DATE 2014/03/05	molex				
		ANGULAR ±3 °		MATERIAL NO. SEE CHART						
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
	REV									