



Part number		Wire range AWG (mm ²)	Tab size	Housing color	Max. Wire Insul. Dia.	Dimensions (in.)		
Prefix	PK					A $\begin{smallmatrix} +.015 \\ -.04 \end{smallmatrix}$	B $\begin{smallmatrix} +.010 \\ -.03 \end{smallmatrix}$	C $\begin{smallmatrix} +.010 \\ -.03 \end{smallmatrix}$
DV18-187B	-C -M -MY	22-18 (.5-1.5)	.187 X .032 (4.8 X 0.8)	Red	.150 (3.81)	.75 (19.1)	.23 (5.8)	.10 (2.5)
* DV14-187B	-C -M	16-14 (1.5-2.5)	.187 X .032 (4.8 X 0.8)	Blue	.170 (4.32)	.75 (19.1)	.23 (5.8)	.10 (2.5)
DV18-188B	-C -M -MY	22-18 (.5-1.5)	.187 X .020 (4.8 X 0.5)	Red	.150 (3.81)	.76 (19.3)	.23 (5.8)	.10 (2.5)
* DV14-188B	-C -M	16-14 (1.5-2.5)	.187 X .020 (4.8 X 0.5)	Blue	.162 (4.11)	.79 (20.1)	.23 (5.8)	.10 (2.5)



Notes:

1. Used for:
 - A. Stranded copper wire only
 - B. 221°F (105°C) maximum temperature rating
 - C. 600V maximum voltage rating
2. Package quantity:
 - A. Standard: -C = 100
 - B. Bulk : -M = 1000, -MY = 1000
3. Material:
 - A. Stamping: .016 (0.41) thick tin plated brass
 - B. Housing : Vinyl
4. Wire strip length: $1/4 \begin{matrix} +1/32 \\ -0 \end{matrix} (6.3 \begin{matrix} +0.8 \\ -0 \end{matrix})$
5. Initial insertion force :12 LB (53N) maximum
Initial withdrawal force: 12 LB (53N) maximum
6 LB (27N) minimum
6. Installation tool: CT-520, CT-1525
 - A. U.L. Listed & CSA Certified
 - B. U.L. Recognized
7. Dimensions in brackets are in millimeters or mm



A41554_05

05	12/06	DAW	DAW	DV18-188B .150 MAX. WIRE INSUL. DIA. WAS .136, .76 "A" LGTH. WAS .79. REMOVED CUTOFF TAB FROM DISCONNECT ILLUSTRATION	TR00190	TR0	LA	 PANDUIT CORP. TINLEY PARK, ILLINOIS
04	6/06	DAW	DAW	REMOVED MAX. AMPERAGE NOTE	TR00134	TR0	LA	
03	5/05	JHNU	LA	ADDED PACKAGING CODE "MY" TO DRAWING.	012743	TR0	LA	Vinyl insulated barrel female disconnect butted seam (.187 tab size)
02	5/98	TM	JW	ADDED CT-1525 TO TOOL NOTE	06872	TK	LA	
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	CUST	CAD FILE A41554_05 DRAWING NO A41554

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DV18-187B-MY](#) [DV14-188B-C](#) [DV14-187B-C](#) [DV14-187B-M](#) [DV18-187B-CY](#) [DV18-188B-CY](#) [DV14-188B-M](#)
[DV18-188B-MY](#)