

SEALED TERMINAL AND WIRE LEAD OPTIONS OPTION -E AND -EW

FEATURES

- 1/4, 1/2, and 1 Amp
- Limit, Overtravel, or Panel Seal
- Butt or Wiping Contact
- Normally Open or Normally Closed
- Momentary or Push/Pull
- Series 23, 30, 39 and 46



Option -E
Epoxy-Sealed
Terminals



Option -EW,
Potted Base & 6"
Wire Leads

SPECIFICATIONS

Rating Criteria

Make and Break Current Rating: See page for standard part number

Contact Resistance: 25 milliohms maximum on a new switch. Less than 4 milliohms per inch of wire for wire lead option styles.

Insulation Resistance: 1,000 megohms minimum between mutually insulated parts

Voltage Breakdown: 1,000 Vac minimum between mutually insulated parts

Materials and Finishes

Potting Sleeve (Series 39): Thermoset Plastic

Wire Leads: #26AWG, (.99mm diameter) insulated Teflon, Copper stranded wire, per MIL-W-16878, Type E. Ends are stripped 0.250" (6.35) and solder dipped. For other specifications, see Page References.

Standard Part Number Red Button	Standard Part Number Black Button	Choices of Suffix	Length Behind Panel In inches (and millimeters)	
			Standard Switch & Terminals	-EW Style Body
23-1	23-4	-E	0.665 (16,89)	—
30-1	30-3	-E, -EW	0.592 (15,04)	0.645 (16,38)
30-15	30-37	-E, -EW	0.679 (17,25)	0.728 (18,49)
30-17 RED (25,58)	30-17 BLK	-E, -EW	0.958 (24,33)	1.007
30-16 RED (25,58)	30-16 BLK	-E, -EW	0.958 (24,33)	1.007
30-251 RED	30-251 BLK	-E, -EW	0.632 (16,05)	0.685 (17,40)
30-252 RED	30-252 BLK	-E, -EW	0.645 (16,38)	0.700 (17,78)
30-32 RED (22,76)	30-32 BLK	-E, -EW	0.867 (22,02)	0.896
30-6	30-2	-E, -EW	0.605 (15,37)	0.640 (16,26)
30-601 RED	30-601 BLK	-E, -EW	0.592 (15,04)	0.645 (16,38)
39-1*	39-3*	-EW**	0.315 (8,00)	0.440 (11,18)
39-12*	39-2	-E, -EW	0.490 (12,45)	0.575 (14,61)
39-101	39-24*	-EW**	0.455 (11,56)	0.575 (14,61)
39-351 RED	—	-EW**	0.650 (16,51)	0.775 (19,69)
39-352 RED*	39-351 BLK	-EW**	0.350 (8,89)	0.450 (11,43)
39-601 RED	39-352 BLK*	-E, -EW	0.529 (13,44)	0.630 (16,00)
39-701***	39-601 BLK	-EW*	0.315 (8,00)	0.440 (11,18)
39-702***	—	-EW**	0.800 (20,32)	0.925 (23,50)
46-101 RED	—	-E, -EW	0.510 (12,95)	0.750 (19,05)
46-102 RED	46-101 BLK	-E, -EW	0.890 (22,61)	0.957 (24,31)
46-110 RED	46-102 BLK	-E, -EW	0.890 (22,61)	0.957 (24,31)
46-111 RED	46-110 BLK	-E, -EW	0.890 (22,61)	0.957 (24,31)
46-150 RED	46-111 BLK	-E, -EW	0.890 (22,61)	0.957 (24,31)
46-151 RED	46-150 BLK	-E, -EW	0.957 (24,31)	1.024 (26,01)
46-200 RED	46-151 BLK	-E, -EW	0.957 (24,31)	1.024 (26,01)
46-201 RED	46-200 BLK	-E	0.921 (23,39)	—
46-270 RED	46-201 BLK	-E	0.921 (23,39)	—
46-271 RED	46-270 BLK	-E	0.957 (24,31)	—
	46-271 BLK	-E	0.957 (24,31)	—

*Epoxy potting sleeve enlarges the diameter of the -EW style to 0.300 (7,62).

**Sealed terminal (-E) option is not necessary; terminals have sealed construction.

***Natural Color Button

†Adjustable from 1.214 (30,84) to 1.334 (33,88) dependent on button height, see switch pages.