

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

OCT ,2005.



COPYRIGHT 2005

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC


DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST REVISION	25OCT05	DK	JC
	B	ECR-06-012727	26MAY06	DK	JC

A: 17.5
E: 30.6
L: 120
N: 109
P: 34
S: 6.3
T: 3.1 Diam.

All dimensions in mm.
(Nominal values only)



DESCRIPTION:
LEAD MATERIAL:
LEAD CROSS-SECTION:
HYBRID PROTECTION:
MARKING:

HIGH VOLTAGE TUBULAR RESISTOR
NICKEL PLATED MILD STEEL
SEE DIAGRAM ABOVE
ORGANIC ENCAPSULATION
TYCO CGS VAL TOL DATECODE HVRX30B

NOTE: X REPLACED WITH M FOR MEADERED TRACK OR L FOR LINEAR TRACK

FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF.

RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24OCT05 DAVE KENNEDY	tyco Electronics		Tyco Electronics Corporation Dorcan, Swindon, SN3 5HH	
DIMENSIONS: MM		CHK 25OCT05 J CATCHPOLE	NAME HVR30B			
		APVD 25OCT05 J CATCHPOLE	SIZE A3			
		PRODUCT SPEC	CAGE CODE 00779			
MATERIAL -		FINISH -	APPLICATION SPEC -		DRAWING NO C=1625951	
		WEIGHT -	CUSTOMER DRAWING		RESTRICTED TO -	
			SCALE NTS		SHEET 1 OF 1 REV B	