

GRADE	COL	Min Thk mm	UL 94 Flame Class	RTI °C			H W I	H A I	H V T R	D 4 9 5	C T I
				EL	WI	WOI					

DSM Engineering Plastics

E47960

Akulon – PA 66

S223-DH, S223-EH, S223-FH

All	0.71	HB	130	100	130	4	0	1	-	-
All	1.5	V-2	130	100	130	4	0	0	-	-
All	3.0	V-2	130	100	130	2	0	0	6	0

S223-E

All	0.4	V-2	65	65	65	-	-	-	-	-
All	1.5	V-2	65	65	65	4	0	0	-	-
All	3.0	V-2	65	65	65	3	0	0	7	0

S223-F

All	1.5	V-2	65	65	65	4	0	0	-	-
All	3.0	V-2	65	65	65	3	0	0	7	0

S225-KS (h2)(j1)

All	0.38	V-0	65	65	65	-	-	-	-	-
All	0.75	V-0	130	90	120	4	0	-	-	-
All	1.5	V-0	130	90	120	4	0	-	-	-
All	3.0	V-0	130	90	120	3	0	0	5	0

S240-C

NC	3.0	V-2	65	65	65	2	0	0	5	0
----	-----	-----	----	----	----	---	---	---	---	---

S240-CH

NC	3.0	V-2	65	65	65	-	-	-	-	-
----	-----	-----	----	----	----	---	---	---	---	---

(h2) Virgin and regrind, from 1% to 50% by weight inclusive, have the same basic material characteristics, except for HWI

(j1) Virgin and regrind, from 1% to 100% by weight inclusive, have the same basic characteristics with respect to Flammability.

DSM Engineering Plastics - Property Data

Akulon® S223-F

PA66

Low/Medium Viscosity

Properties	Typical Data	Unit	Test Method
MECHANICAL PROPERTIES			
	dry / cond		
Tensile modulus	3400 / 1500	MPa	ISO 527-1/-2
Yield stress	90 / 60	MPa	ISO 527-1/-2
Yield strain	3.5 / 20	%	ISO 527-1/-2
Nominal strain at break	40 / >50	%	ISO 527-1/-2
Charpy impact strength (+23°C)	N / N	kJ/m²	ISO 179/1eU
Charpy impact strength (-30°C)	N / N	kJ/m²	ISO 179/1eU
Charpy notched impact strength (+23°C)	7 / 14	kJ/m²	ISO 179/1eA
Charpy notched impact strength (-30°C)	7 / 7	kJ/m²	ISO 179/1eA
THERMAL PROPERTIES			
	dry / cond		
Melting temperature (10°C/min)	260 / *	°C	ISO 11357-1/-3
Temp. of deflection under load (1.80 MPa)	75 / *	°C	ISO 75-1/-2
Temp. of deflection under load (0.45 MPa)	220 / *	°C	ISO 75-1/-2
Coeff. of linear therm. expansion (parallel)	1 / *	E-4/°C	ISO 11359-1/-2
Coeff. of linear therm. expansion (normal)	1 / *	E-4/°C	ISO 11359-1/-2
Burning Behav. at 1.6 mm nom. thickn.	V-2 / *	class	IEC 60695-11-10
Thickness tested	1.5 / *	mm	IEC 60695-11-10
Burning Behav. at thickness h	V-2 / *	class	IEC 60695-11-10
Thickness tested	3 / *	mm	IEC 60695-11-10
ELECTRICAL PROPERTIES			
	dry / cond		
Relative permittivity (100Hz)	3.2 / 10	-	IEC 60250
Relative permittivity (1 MHz)	3 / 4	-	IEC 60250
Dissipation factor (100 Hz)	60 / 1400	E-4	IEC 60250
Dissipation factor (1 MHz)	170 / 1000	E-4	IEC 60250
Volume resistivity	1E13 / 1E10	Ohm*m	IEC 60093
Surface resistivity	* / 1E14	Ohm	IEC 60093
Electric strength	25 / 20	kV/mm	IEC 60243-1
Comparative tracking index	600 / 600	-	IEC 60112
OTHER PROPERTIES			
	dry / cond		
Water absorption	9 / *	%	Sim. to ISO 62
Humidity absorption	2.4 / *	%	Sim. to ISO 62
Density	1140 / -	kg/m³	ISO 1183

10.03.2004



FOR INTERNAL USE ONLY

Unlimited. **DSM**

All information supplied by or on behalf of DSM in relation to its products, whether in the nature of data, recommendations or otherwise, is supported by research and, in good faith, believed reliable, but DSM assumes no liability and makes no warranties of any kind, express or implied, including, but not limited to, those of title, merchantability, fitness for a particular purpose or non-infringement or any warranty arising from a course of dealing, usage, or trade practice whatsoever in respect of application, processing or use made of the aforementioned information or product. The user assumes all responsibility for the use of all information provided and shall verify quality and other properties or any consequence from the use of all such information.



QMFZ2.E47960 Plastics - Component

[Page Bottom](#)
[Print-friendly version](#)
[Questions?](#)
[Previous Page](#)

Plastics - Component

[See General Information for Plastics - Component](#)
DSM ENGINEERING PLASTICS B V
E47960
POSTBUS 43
6130 AA SITTARD, THE NETHERLANDS

									H	D	
		Min.		H	H	R T I			V	4	C
		Thk	Flame	W	A	Elec	Mech		T	9	T
Material Dsg	Color	mm	Class	I	I		Imp	Str	R	5	I
Acrylonitrile Butadiene Styrene/Polycarbonate (ABS/PC), "Stapron C", furnished as pellets.											
CF 102	ALL	1.5	V-0	2	0	60	60	60	4	7	1
		2.1	V-0, 5VB	2	0	60	60	60			
		3.0	V-0	1	0	60	60	60			
CF 202	ALL	1.5	V-0	3	0	60	60	60	0	7	0
		2.1	V-0, 5VB	3	0	60	60	60			
		3.0	V-0	2	0	60	60	60			
CF 203	ALL	1.5	V-0	-	-	60	60	60			
		3.0	V-0	-	-	60	60	60			
CM 204	ALL	1.5	HB	4	0	60	60	60	2	6	1
		3.0	HB	3	0	60	60	60			
CM 205	ALL	1.5	HB	4	0	60	60	60	2	6	1

		3.0	HB	3	0	60	60	60			
CM 205 U	ALL	1.5	HB	4	0	60	60	60	2	6	1
		3.0	HB	3	0	60	60	60			
CM 404	ALL	1.5	HB	3	0	60	60	60	2	6	2
		3.0	HB	3	0	60	60	60			
CM 405	ALL	1.5	HB	3	0	60	60	60	2	6	2
		3.0	HB	3	0	60	60	60			
CM 405 U	ALL	1.5	HB	3	0	60	60	60	2	6	2
		3.0	HB	3	0	60	60	60			
CM 504	ALL	1.5	HB	4	0	60	60	60	0	6	2
		3.0	HB	2	0	60	60	60			
CM 505	ALL	1.5	HB	4	0	60	60	60	0	6	2
		3.0	HB	2	0	60	60	60			
CM 505 U	ALL	1.5	HB	4	0	60	60	60	0	6	2
		3.0	HB	2	0	60	60	60			
Acrylonitrile Butadiene Styrene/Polycarbonate (ABS/PC), high impact, very high flow, "Xantar C", furnished as pellets.											
CM 206	ALL	1.5	HB	4	0	60	60	60	0	6	0
		3.0	HB	3	0	60	60	60			
Polyamide (PA), glass reinforced, "Akulon", furnished as pellets.											
IG-S250F6	NC, BK	0.4	V-0	-	-	-	-	-	1	6	2
		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	0	140	125	125			
		3.0	V-0	0	0	140	130	130			
Polyamide 4/6 (PA4/6), flame retardant, "Stanyl", furnished as pellets.											
TE350	NC, BK	0.75	V-0	4	0	130	110	110	1	7	2
		1.5	V-0	2	0	130	110	120			
		3.0	V-0	1	0	130	110	120			
Polyamide 4/6 (PA4/6), glass reinforced, "Stanyl", furnished as pellets.											

TE200F6	NC	0.9	HB	3	0	-	-	-	0	5	1	
		1.5	HB	3	0	-	-	-				
		3.0	HB	0	0	-	-	-				
TW200F6	NC, BK	0.90	HB	3	0	140	120	120	0	5	2	
		1.5	HB	3	0	140	125	130				
		3.0	HB	0	0	140	140	140				
TW241F10	NC, BK	0.75	HB	-	-	65	65	65				
TW241F6, 46HF4130												
		0.75	HB	-	-	65	65	65	0	5	2	
		0.9	HB	3	0	140	120	120				
		1.5	HB	3	0	140	125	130				
		3.0	HB	0	0	140	140	140				
TW271F6	NC, BK	0.75	HB	3	0	-	-	-	3	2		
		1.5	HB	0	0	-	-	-				
		3.0	HB	0	0	-	-	-				
Polyamide 4/6 (PA4/6), glass reinforced, flame retardant, "Stanyl", furnished as pellets.												
46HF5040(h1)(j)												
		ALL	0.35	V-0	-	-	65	65	65	1	7	2
		0.75	V-0	0	0	140	110	120				
		1.5	V-0	0	1	140	125	125				
		3.0	V-0	0	0	140	130	130				
TE250F3(h4)(h5)												
		NC, BK	0.9	V-0	4	0	130	110	110	1	7	3
		1.5	V-0	2	0	130	110	120				
		3.0	V-0	1	0	130	110	120				
TE250F6(h1)(j)												
	ALL	0.35	V-0	-	-	-	-	-	1	6	2	

		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	0	140	125	125			
		3.0	V-0	0	0	140	130	130			
TE250F8(h1)(j)											
	ALL	0.35	V-0	-	-	65	65	65	1	7	2
		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	1	140	125	125			
		3.0	V-0	0	0	140	130	130			
TE250F9	ALL	0.75	V-0	0	0	140	110	120	1	7	2
		1.5	V-0	0	1	140	125	125			
		3.0	V-0	0	0	140	130	130			
TS250F6D(h1)(j)											
	ALL	0.67	V-0	-	-	140	110	120	1	6	2
		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	0	140	125	125			
		3.0	V-0	0	0	140	130	130			
TS250F8(h1)	ALL	0.75	V-0	0	0	140	110	120	1	7	2
		1.5	V-0	0	1	140	125	125			
		3.0	V-0	0	0	140	130	130			
TW250F6	NC, BK	0.75	V-0	0	0	140	120	130	1	7	3
		1.5	V-0	0	0	140	130	140			
		3.0	V-0	0	0	140	140	140			
Polyamide 4/6 (PA4/6), glass reinforced, flame retardant, high flow, "Stanyl", furnished as pellets.											
46HF5041LW	NC, BK	0.4	V-0	-	-	65	65	65	1	5	2
		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	0	140	125	125			
		3.0	V-0	0	0	140	130	130			
46HF5050	NC, BK	0.4	V-0	-	-	65	65	65	1	5	2

		0.75	V-0	0	0	140	110	120			
		1.5	V-0	0	0	140	125	125			
		3.0	V-0	0	0	140	130	130			
Polyamide 4/6 (PA4/6), mineral reinforced, flame retardant, "Stanyl", furnished as pellets.											
TS250FK33	NC, BK	0.75	V-0	-	-	65	65	65			
		1.5	V-0	-	-	65	65	65			
		3.0	V-0	-	-	65	65	65			
Polyamide 4/6 (PA4/6), "Stanyl", furnished as pellets.											
TE258F6	ALL	0.38	V-0	-	-	65	65	65	1	5	3
		0.75	V-0	0	0	65	65	65			
		1.5	V-0	0	0	65	65	65			
		3.0	V-0	0	0	65	65	65			
TE300	NC	0.90	V-2	4	0	130	-	-	0	5	0
		1.5	V-2	4	0	130	-	-			
		3.0	V-2	3	0	130	-	-			
TE341	NC, BK	0.75	V-2	4	0	130	-	-	0		
		1.5	V-2	4	0	130	-	-			
		3.0	V-2	3	0	130	-	-			
TE351	NC, BK	1.5	V-0	2	0	130	-	-	1	7	2
		3.0	V-0	0	0	130	-	-			
TS250F(h)(g2)											
	ALL	0.75	V-0	-	-	65	65	65			
TW300	NC	0.75	V-2	4	0	150	115	120	1	6	1
		1.5	V-2	3	0	150	115	130			
		3.0	V-2	3	0	150	115	130			
TW341	NC, BK	0.75	V-2	4	0	150	115	120	1	6	2
		1.5	V-2	3	0	150	115	130			

		3.0	V-2	3	0	150	115	130		
TW371	NC	1.5	HB	-	-	-	-	-		
		3.0	HB	-	-	-	-	-		
TW441	NC	0.75	V-2	-	-	-	-	-		
		1.5	V-2	-	-	-	-	-		
		3.0	V-2	-	-	-	-	-		
Polyamide 4/6 (PA4/6), furnished as pellets.										
TS 256F(g)(h)										
	ALL	0.75	V-0	-	-	65	65	65		
TW241F8	NC, BK	0.75	HB	-	-	65	65	65		
Polyamide 6 (PA6), glass reinforced, "Akulon", furnished as pellets.										
K222-KGV4	ALL	0.80	V-2	3	0	140	-	130		0
		1.2	V-2	2	0	140	-	130		
		1.5	V-2	2	0	140	-	130		
		3.0	V-2	1	0	140	-	130		
K224-G(a)	ALL	0.75	HB	-	0	65	65	65	0	5
		1.5	HB	4	0	65	65	65		
		3.0	HB	4	0	65	65	65		
K224-G(b), K224-TG(b)										
	ALL	0.75	HB	-	0	65	65	65	0	5
		1.5	HB	4	0	65	65	65		
		3.0	HB	4	0	65	65	65		
K224-G0, K224-TG0										
	ALL	0.75	HB	3	0	65	65	65	0	5
		1.5	HB	2	0	65	65	65		
		3.0	HB	0	0	65	65	65		
K224-G3	ALL	0.75	HB	4	0	65	65	65	0	5
		1.5	HB	3	0	65	65	65		
		3.0	HB	3	0	65	65	65		
K224-G6	ALL	0.75	HB	-	0	65	65	65	0	5

		1.5	HB	4	0	65	65	65			
		3.0	HB	4	0	65	65	65			
K224-HG(a)	ALL	0.71	HB	3	0	140	120	140	1	6	1
		1.5	HB	1	0	140	125	150			
		3.0	HB	0	0	140	130	150			
K224-HG(b)	ALL	0.71	HB	3	0	140	120	140	1	6	1
		1.5	HB	1	0	140	125	150			
		3.0	HB	0	0	140	130	150			
K224-HG3	ALL	0.71	HB	4	0	150	120	150	1	6	1
		1.5	HB	4	0	150	125	150			
		3.0	HB	4	0	150	130	150			
K224-HG6	ALL	0.75	HB	2	0	140	120	140	1	6	1
		1.5	HB	1	0	140	125	150			
		3.0	HB	0	0	140	130	150			
K224-HGR24	BK	0.75	HB	-	-	65	65	65	2		
		1.5	HB	-	-	65	65	65			
		3.0	HB	-	-	65	65	65			
Polyamide 6 (PA6), glass reinforced, high flow, "Akulon", furnished as pellets.											
K-FG6	ALL	0.75	HB	4	-	65	65	65	1	5	1
		1.5	HB	4	-	65	65	65			
		3.0	HB	4	-	65	65	65			
Polyamide 6 (PA6), heat stabilized, "Akulon", furnished as pellets.											
F136-DH	ALL	1.5	HB	4	0	65	65	65	0	7	1
		3.0	HB	3	0	65	65	65			
Polyamide 6 (PA6), heat stabilized, flame retardant, "Akulon", furnished as pellets.											
K225-KS	NC	0.38	V-0	-	-	65	65	65	0	5	0
		ALL	0.75	V-0	3	0	150	75	95		
		1.5	V-0	3	0	150	75	95			
		3.0	V-0	2	0	150	80	95			
Polyamide 6 (PA6), heat stabilized, laser writable, flame retardant, "Akulon", furnished as pellets.											

K225-KWS	ALL	0.75	V-0	4	0	150	75	95	0	5	0	
		1.5	V-0	2	0	150	75	95				
		3.0	V-0	0	0	150	80	95				
Polyamide 6 (PA6), mineral reinforced, "Akulon", furnished as pellets.												
K222-KGMV14	GY	0.75	V-2	3	0	65	65	65				
		1.5	V-2	2	0	65	65	65				
		3.0	V-2	1	0	65	65	65				
K222-KMV5	ALL	0.75	V-2	4	0	65	65	65				
		1.5	V-2	4	0	65	65	65				
		3.0	V-2	3	0	65	65	65				
K223-HM6	ALL	0.71	HB	4	0	140	100	140	0	5	1	
		1.5	HB	4	0	140	110	140				
		3.0	HB	3	0	140	120	140				
K223-HMS6	ALL	0.74	V-2	3	0	140	100	140	1	5	2	
		1.5	V-0	2	0	140	110	140				
		3.0	V-0	1	0	140	120	140				
K223-KMV6	ALL	0.75 - 0.8	V-2	3	0	140	110	140				
		GY	1.5	V-2	2	0	140	110				140
		3.0	V-0	1	0	140	110	140				
Polyamide 6 (PA6), "Akulon", furnished as pellets.												
F150-CZ	NC	1.5	HB	4	0	65	65	65	0	7	0	
		3.0	HB	4	0	65	65	65				
F223-D	NC	0.75	V-2	-	-	120	65	85	0	7	0	
		ALL	1.5	V-2	4	0	120	65	85			
		3.0	V-2	3	0	120	70	85				
F232-D	ALL	1.5	HB	4	0	65	65	65	0	7	0	
		3.0	HB	4	0	65	65	65				
F236-C	NC	1.5	HB	4	0	65	65	65	0	7	0	
		3.0	HB	4	0	65	65	65				
K222-D	ALL	0.71	-	-	-	130	65	85	0		0	

		1.5	V-2	4	0	130	70	85			
		3.0	V-2	4	0	130	70	85			
K222-KWGV4	GY	0.75	V-2	3	0	140	-	130		1	
		1.2	V-2	2	0	140	-	130			
		1.5	V-2	2	0	140	-	130			
		3.0	V-2	1	0	140	-	130			
Polyamide 6 (PA6), "Akulon Ultraflow", furnished as pellets.											
K-FKGS6	ALL	0.75	V-0	2	0	140	110	110		1	
		1.5	V-0	1	0	140	110	130			
		3.0	V-0	0	0	140	110	130			
Polyamide 66 (PA66), glass reinforced, "Akulon", furnished as pellets.											
S223-G(a)	ALL	0.71	-	4	0	65	65	65	1	5	1
		1.5	HB	3	0	65	65	65			
		3.0	HB	3	0	65	65	65			
S223-G(b)	ALL	0.71	-	2	0	65	65	65	1	5	0
		1.5	HB	1	0	65	65	65			
		3.0	HB	0	0	65	65	65			
S223-G6	ALL	0.71	-	4	0	65	65	65	1	5	1
		1.5	HB	3	0	65	65	65			
		3.0	HB	3	0	65	65	65			
S223-HG(g3)	ALL	0.71	HB	4	0	140	120	120	1	6	1
		1.5	HB	4	0	140	125	130			
		3.0	HB	4	0	140	130	130			
S223-HG6	ALL	0.71	HB	4	0	140	130	130	1	6	1
		1.5	HB	4	0	140	130	130			
		3.0	HB	3	0	140	130	130			
Polyamide 66 (PA66), heat stabilized, "Akulon", furnished as pellets.											
S240-CH	NC	3.0	V-2	-	-	65	65	65			
Polyamide 66 (PA66), mineral reinforced, "Akulon", furnished as pellets.											
S223-HM8	ALL	0.71	HB	3	0	140	130	130	0	5	0

		1.5	HB	3	0	140	130	130			
		3.0	HB	2	0	140	130	140			
S224-KMV7	GY	0.75	V-2	0	0	150	115	140	1		
		1.5	V-1	0	0	150	120	140			
		3.0	V-0	0	0	150	125	140			
Polyamide 66 (PA66), "Akulon", furnished as pellets.											
S223-DH, S223-EH, S223-FH											
	ALL	0.71	HB	4	0	130	100	130	0	6	0
		1.5	V-2	4	0	130	100	130			
		3.0	V-2	2	0	130	100	130			
S223-E	ALL	0.4	V-2	-	-	65	65	65	0	7	0
		1.5	V-2	4	0	65	65	65			
		3.0	V-2	3	0	65	65	65			
S223-F	ALL	1.5	V-2	4	0	65	65	65	0	7	0
		3.0	V-2	3	0	65	65	65			
S225-KS (h2) (j1)											
	ALL	0.38	V-0	-	-	65	65	65	0	5	0
		0.75	V-0	4	0	130	90	120			
		1.5	V-0	4	0	130	90	120			
		3.0	V-0	3	0	130	90	120			
S240-C	NC	3.0	V-2	2	0	65	65	65	0	5	0
Polyamide 66 (PA66), "Nylatron", furnished as granular material.											
GS-51	GY	1.5	HB	-	-	65	65	65			
Polyamide 66 (PA66), "NYLATRON", furnished as pellets.											
GS-S	GY	1.5	HB	-	-	65	65	65			
Polybutylene Terephthalate (PBT), 15% glass filled, 12% flame retardant, "Arnite", furnished as pellets.											
TV4 230 S	ALL	0.75	V-2	3	1	140	130	140	2	5	2
		1.5	V-0	3	2	140	130	140			
		3.0	V-0	2	2	140	130	140			
Polybutylene Terephthalate (PBT), glass reinforced, "Arnite", furnished as pellets.											

TV4 240	ALL	0.75	HB	3	1	140	130	130	2	5	1
		1.5	HB	2	2	140	130	130			
		3.0	HB	1	2	140	130	130			
TV4 240 S	ALL	0.75	V-2	3	1	140	130	140	2	5	2
		1.5	V-0	2	2	140	130	140			
		3.0	V-0	2	2	140	130	140			
Polybutylene Terephthalate (PBT), glass reinforced, flame retardant, "Arnite", furnished as pellets.											
TV4 241 SL	NC	1.5	V-0	-	-	145	120	140			
Polybutylene Terephthalate (PBT), glass reinforced, flame retardant, high flow, "Arnite", furnished as pellets.											
TV4 230 SF (h6)											
	NC, BK	0.4	V-2	4	0	75	75	75	4	5	2
	ALL	0.75	V-0	3	0	130	140	130			
		1.5	V-0, 5VB	2	0	130	140	130			
		2.0	V-0, 5VA	2	0	130	140	130			
		3.0	V-0, 5VA	1	0	130	140	130			
	TV4 260 SF(h3)										
	NC, BK	0.4	V-2	4	0	130	75	75	4	5	2
	ALL	0.75	V-0	3	0	140	150	140			
		1.5	V-0	2	0	140	150	140			
		3.0	V-0	1	0	140	150	140			
Polybutylene Terephthalate (PBT), mineral reinforced, "Arnite", furnished as pellets.											
TM4 250	NC	0.75	HB	4	0	150	115	140			
		1.5	HB	3	0	150	130	140			
		3.0	HB	3	0	150	130	140			
Polybutylene Terephthalate (PBT), "Arnite", furnished as pellets.											
T06 200 SN	ALL	0.75	V-0	-	-	75	75	75			

		3.00	V-0	-	-	75	75	75			
Polybutylene Terephthalate (PBT), "ARNITE", furnished as pellets.											
T06 200 SNF(h)											
	ALL	0.75	V-0	4	0	140	110	130	0	5	0
		1.5	V-0	3	0	140	110	130			
		3.0	V-0	2	0	140	110	130			
Polybutylene Terephthalate (PBT), "Arnite", furnished as pellets.											
T06 200, T06 202											
	ALL	0.75	HB	4	0	130	95	125	0	4	0
		1.5	HB	4	0	130	110	130			
		3.0	HB	3	0	130	110	130			
T06 204 SN	ALL	0.75	V-0	-	-	75	75	75			3
		3.0	V-0	-	-	75	75	75			
T08 200	ALL	0.75	HB	4	0	130	95	125			0
		1.5	HB	4	0	130	110	130			
		3.0	HB	3	0	130	110	130			
TV4 241 SN	ALL	0.75	V-2	4	0	140	130	140	0	5	3
		1.5	V-0	3	0	140	130	140			
		3.0	V-0	2	0	140	130	140			
TV4 260 S	ALL	0.50	V-2	-	-	75	75	75	1	5	2
		0.75	V-2	3	0	140	130	140			
		1.5	V-0	3	0	140	130	140			
		3.0	V-0	2	0	140	130	140			
TV4 260 SN	ALL	0.75	V-2	3	4	140	130	140			2
		1.6	V-0	2	4	140	130	140			
		3.0	V-0	1	4	140	140	140			
TV4 260 SY	GY	0.75	V-2	3	1	130	120	130	0	7	2
		1.5	V-0	3	1	130	120	130			
		3.0	V-0	0	1	130	120	140			
TV4 261	ALL	0.71	HB	3	1	140	130	140	2	5	1

		1.5	HB	2	2	140	130	140				
		3.0	HB	2	2	140	130	140				
TV4 264 SN (i)												
	ALL	0.4	V-2	-	-	75	75	75	4			3
		0.75	V-0	4	2	140	110	120				
		1.5	V-0	2	0	140	110	130				
		3.0	V-0	0	0	140	110	140				
TV4 270	ALL	0.75	-	3	2	140	130	140	2	6	1	
		1.5	HB	1	2	140	130	140				
		3.0	HB	1	2	140	130	140				
TV6 240	ALL	0.75	-	3	2	140	130	140	2	5	1	
		1.5	HB	2	2	140	130	140				
		3.0	HB	1	2	140	130	140				
TV6 241 S	ALL	0.75	V-2	4	1	140	130	140	2	5	2	
		1.0	V-0	4	2	140	130	140				
		1.5	V-0	4	2	140	130	140				
		2.0	V-0	1	2	140	130	140				
		3.0	V-0	1	2	140	130	140				
TV6 260 T	GY	1.5	HB	-	-	75	75	75				
TV6 264 SN	BK	0.38	V-0	-	-	75	75	75	4			3
	ALL	0.75	V-0	4	2	140	110	120				
		1.5	V-0	2	0	140	110	130				
		3.0	V-0	0	0	140	110	140				
Polybutylene Terephthalate (PBT), furnished as granular material.												
TV6 241 SN	ALL	0.75	V-2	4	2	140	130	140	2	5	2	
		1.0	V-0	4	2	140	130	140				
		1.5	V-0	4	2	140	130	130				
		3.0	V-0	1	2	140	130	140				
Polybutylene Terephthalate/Polycarbonate (PBT/PC), glass reinforced, flame retardant, "Arnite", furnished as pellets.												
TV4 660 SN (r1)												

	ALL	0.75	V-0	-	-	75	75	75	0	6	3
		1.5	V-0	2	0	75	75	75			
		3.0	V-0	1	0	75	75	75			
Polycarbonate (PC), glass reinforced, "Xantar", furnished as pellets.											
15(x)(f1), 25(x)(f1), 27(x)(f1), 30(x)(f1)											
	ALL	1.5	V-2	3	0	130	125	125	2	5	2
		3.0	V-2	2	0	130	130	130			
Polycarbonate (PC), glass reinforced, flame retardant, "Xantar", furnished as pellets.											
MX 1094	ALL	1.5	V-0	3	3	130	125	125	1	6	3
		3.0	V-0	2	1	130	130	130			
Polycarbonate (PC), impact modified, flame retardant, "Xantar", furnished as pellets.											
MX 1004	GY, BK	1.5	V-0	2	0	80	80	80	2	7	0
		3.0	V-0	1	0	80	80	80			
Polycarbonate (PC), "Xantar", furnished as pellets.											
18(x)(f1), 19(x)(f1), 22(x)(f1), 24(x)(f1)											
	ALL	0.75	V-2	-	-	130	125	125	2	5	2
		1.5	V-2	3	0	130	125	125			
		3.0	V-2	2	0	130	130	130			
F 22 (y)(f1), F 23 (y)(f1), F 25 (y)(f1)											
	ALL	1.5	V-2	2	0	130	125	125	2	6	2
		3.0	V-0	3	1	130	125	130			
FC 19 (y)(f1), FC 22 (y)(f1)											
	ALL	1.5	V-0	2	1	130	125	125	3	6	2
		3.0	V-0	2	0	130	125	130			
MX 2042 FD(f1)											
	NC	1.5	V-2	3	0	130	125	125	2	5	2
		3.0	V-2	2	0	130	130	130			
Polycarbonate (PC), structural foam, "Xantar ", furnished as pellets.											
MX 1056(a1) (foamed)											
	GY	6.0	V-0,	-	-	80	80	80			

			5VA								
SF 22(a1)	ALL	4.8	V-0, 5VA	-	-	80	80	80	1	6	4
		6.0	V-0, 5VA	2	4	80	80	80			
SF 2220 (b1)											
	ALL	4.8	V-0, 5VA	-	-	80	80	80			
SF 2230 (d1)											
	ALL	4.8	V-0, 5VA	-	-	80	80	80			
Polycarbonate (PC), "Xantar ", furnished as pellets.											
FC 23 (y)(f1), FC 25 (y)(f1)											
	ALL	1.5	V-0	2	1	130	125	125	3	6	2
		3.0	V-0, 5VA	2	0	130	125	130			
G2F 23 (y)(f1), G2F 25 (y)(f1)											
	ALL	1.5	V-0	3	3	130	125	125	1	6	3
		3.0	V-0, 5VA	2	1	130	130	130			
G4F 22 (y)(f1), G4F 23 (y)(f1), G4F 25 (y)(f1)											
	ALL	1.2	V-0	-	-	80	80	80	1	6	3
		1.5	V-0	3	3	130	125	125			
		3.0	V-0	2	1	130	130	130			
G6F 23 (y)(f1)											
	ALL	1.5	V-0	3	4	130	125	125	0	5	3
		3.0	V-0	2	1	130	130	130			
G8F 23 (y)(f1)											
	ALL	1.5	V-0	2	4	130	125	125	1	5	3
		3.0	V-0	2	0	130	130	130			
MX 1000	ALL	1.5	V-0	2	1	110	85	105	2	5	2
		2.0	5VB	2	1	110	85	105			
		3.0	V-0	0	1	110	105	110			

MX 1001	ALL	0.75	V-0	3	0	80	80	80	0	6	2
		1.5	V-0	2	0	80	80	80			
		3.0	V-0	2	0	80	80	80			
MX 1002	BK	1.2	V-1	-	-	80	80	80	2	5	2
	ALL	1.5	V-0	2	1	110	85	105			
		2.0	5VB	2	1	110	85	105			
		3.0	V-0	0	1	110	105	110			
MX 1056	GY	4.0	V-0, 5VA	-	-	80	80	80			
MX 1060(f1), MX 1061(f1)											
	ALL	1.5	V-2	3	0	130	125	125	2	5	2
		3.0	V-2	2	0	130	130	130			
MX 1080	ALL	1.5	V-0	3	4	80	80	80	0	5	3
		3.0	V-0	2	1	80	80	80			
MX 1081(f1)	ALL	1.5	V-0	3	3	130	125	125	1	6	3
		3.0	V-0, 5VA	2	1	130	130	130			
MX 1082(f1)	ALL	1.2	V-0	-	-	80	80	80	1	6	3
		1.5	V-0	3	3	130	125	125			
		3.0	V-0	2	1	130	130	130			
MX 1092	ALL	0.75	V-0	3	0	80	80	80	2	6	3
		1.5	V-0	2	3	80	80	80			
		3.0	V-0	2	3	80	80	80			
MX 2003(f1)	ALL	1.5	V-2	3	0	130	125	125	2	5	2
		3.0	V-2	2	0	130	130	130			
MX 2007(f1)	ALL	1.5	V-2	3	0	130	125	125	2	5	2
		3.0	V-2	2	0	130	130	130			
MX 2015(f1)	ALL	1.5	V-0	3	1	130	125	125	3	6	2
		3.0	V-0	2	0	130	125	130			
Polycarbonate/Acrylonitrile Butadiene Styrene (PC/ABS), flame retardant, "Xantar C", furnished as pellets.											

CF 407	ALL	1.5	V-0	3	-	60	60	60	0	7	0
		3.0	V-0	2	-	60	60	60			
Polycarbonate/Acrylonitrile Butadiene Styrene (PC/ABS), high impact, very high flow, "Xantar C", furnished as pellets.											
CM 206 U	ALL	1.5	HB	4	0	60	60	60	0	6	0
		3.0	HB	3	0	60	60	60			
CM 406	ALL	1.5	HB	4	0	60	60	60	0	7	2
		3.0	HB	3	0	60	60	60			
CM 406 U	ALL	1.5	HB	4	0	60	60	60	0	7	2
		3.0	HB	3	0	60	60	60			
CM 506	ALL	1.5	HB	3	0	60	60	60	0	7	2
		3.0	HB	3	0	60	60	60			
CM 506 U	ALL	1.5	HB	3	0	60	60	60	0	7	2
		3.0	HB	3	0	60	60	60			
Polycarbonate/Acrylonitrile Butadiene Styrene (PC/ABS), "Xantar C", furnished as pellets.											
CE 407	ALL	1.5	V-0	2	0	60	60	60	0	6	0
		3.0	V-0	1	0	60	60	60			
CF 107	ALL	1.5	V-0	2	0	60	60	60	0	6	1
		2.0	V-0, 5VB	2	0	60	60	60			
		3.0	V-0, 5VB	1	0	60	60	60			
MC 3433	ALL	1.5	V-0	3	0	60	60	60	2	6	2
		3.0	V-0	2	0	60	60	60			
Polyester Elastomer, "Arnitel", furnished as pellets.											
PL380	NC	1.5	HB	-	-	50	50	50			
		3.0	HB	-	-	50	50	50			
PL460-S	ALL	1.5	V-0	-	-	50	50	50			
UM551, UM552											
	ALL	0.75	HB	4	1	160	120	150	0	5	0
		1.5	HB	3	0	160	120	150			

		3.0	HB	2	0	160	120	150			
Polyester Elastomer, furnished as pellets.											
EL740-S	ALL	1.5	V-0	-	-	50	50	50			
		3.0	V-0	-	-	50	50	50			
Polyethylene Terephthalate (PET), glass reinforced, "Arnite", furnished as pellets.											
AV2 343	ALL	0.75	HB	4	3	130	120	125	3	5	2
		1.5	HB	3	3	130	120	125			
		3.0	HB	3	3	130	120	125			
AV2 360 S	ALL	0.71	V-2	3	0	150	125	140	4	6	
		1.5	V-0	0	3	150	130	140			
		3.0	V-0	0	3	150	130	140			
AV2 365 SN	ALL	0.75	V-0	-	-	130	120	125	0	5	3
		1.5	V-0	0	0	130	120	125			
		3.0	V-0	0	0	130	120	125			
	NC	0.4	V-0	-	-	130	120	125			
		2.1	5VA	0	0	130	120	125			
AV2 370, AV2 372											
	ALL	0.75	HB	2	3	150	120	130	3	5	2
		1.5	HB	1	3	150	125	130			
		3.0	HB	0	3	150	130	130			
AV2 390	ALL	0.81	HB	2	4	150	120	140	0	5	2
		1.5	HB	1	4	150	120	140			
		3.0	HB	0	4	150	120	140			
Polyethylene Terephthalate (PET), unfilled, very high viscosity, extrusion, "Arnite", furnished as pellets.											
A06 101	NC	0.93	HB	-	-	75	75	75	0	6	0
		1.5	HB	3	0	75	75	75			
		3.0	HB	3	0	75	75	75			
Polyethylene Terephthalate (PET), "Arnite", furnished as pellets.											
A04 900	ALL	0.75	HB	4	0	75	75	75	2	5	1
		1.5	HB	3	0	75	75	75			

		3.0	HB	3	0	75	75	75	
Thermoplastic Elastomer (TPE), "Arnite", furnished as pellets.									
EL250	NC	1.5	HB	-	-	50	50	50	
Thermoplastic Elastomer (TPE), polyester, "Arnitel", furnished as pellets.									
EL550, EM550									
	NC, BK	1.5	HB	-	-	50	50	50	
Thermoplastic Elastomer (TPE), Polyester, "Arnitel", furnished as pellets.									
EL630, EM630									
	NC, BK	1.5	HB	-	-	-	-	-	
Thermoplastic Elastomer (TPE), polyester -ester, flame retarded, "Arnitel", furnished as pellets.									
UM551-V	NC	1.5	V-2	-	-	50	50	50	
Thermoplastic Elastomer (TPE), polyether-ester elastomer, "Arnitel", furnished as pellets.									
EL740, EM740									
	NC, BK	1.5	HB	-	-	50	50	50	
EM460	NC, BK	1.5	HB	-	-	50	50	50	
PL650	NC, BK	1.5	HB	-	-	50	50	50	

(a) - Represents 16-29% range.

(a1) - Density range 0.92 - 1.27g/cc.

(b) - Represents 31-49% range.

(b1) - Density range 1.0 - 1.35g/cc.

(d1) - Density range 1.07 - 1.27g/cc.

(f1) - Suitable for outdoor use with respect to exposure to Ultraviolet Light, Water Exposure and Immersion in accordance with UL 746C.

(g) - Denotes a single digit 4-8 incl.

(g2) - Represents a number 2-10 excluding 8, denoting glass content range 10-50%.

(g3) - May be replaced by a one digit number [3-8, excluding 6] representing a 31-49% glass content range.

(h) - Virgin and regrind up to 50% by weight inclusive, have the same basic material characteristics.

(h1) - Virgin and regrind, up to 50% by weight inclusive, in thicknesses of 0.75mm and greater, have the same basic material characteristics, except for CTI.

(h2) - Virgin and regrind up to 50% by weight inclusive, have the same basic material characteristics, except for HWI

(h3) - Virgin and regrind up to 50% by weight inclusive, have the same basic material characteristics in the 0.75 mm thickness and greater, and with respect to Flammability in the 0.4 mm thickness and greater.

(h4) - Virgin and regrind, from 0 to 50% by weight inclusive, have the same basic material characteristics, except for RTI

(h5) - Virgin and regrind, from 0 to 100% by weight inclusive, have the same basic material characteristics, with respect to Flammability.

(h6) - Virgin and regrind up to 50% by weight have the same flammability characteristics (>0.4 mm only) and the same basic material characteristics (>0.75 mm only) except with respect to 5VA/5VB.

(i) - Virgin and regrind up to 50% by weight inclusive, have the same basic material characteristics with respect to flammability (GY, 0.75-3.0 mm only)

(j) - Virgin and regrind, up to 100% by weight inclusive, have the same basic material characteristics with respect to Flammability in the 0.75mm thickness and greater.

(j1) - Virgin and regrind, up to 100% by weight inclusive, have the same basic material characteristics with respect to flammability.

(r1) - Virgin and regrind, up to 50% by weight, have the same basic material characteristics in unpigmented (NC) and black (BK) only.

(x) - Represents one or two letters to specify the additive package, xx can be B, R, U, UR, SR, FD

(y) - One or two letters B, R, U, UR specifying additive package.

Marking: Company name or tradename "APSCOM" , "Akulon" , "Akulon Ultraflow" , "Arnite" , "Arnitel" and material designation on container, wrapper or finished part.

Last Updated on 2005-02-08

[Page Top](#)

[Notice of Disclaimer](#)

[Questions?](#)

Previous Page

[UL Listed and Classified](#)

[UL Recognized](#)

[Products Certified for](#)

[Products](#)[Components](#)[Canada](#)

This page and all contents are Copyright © 2005 by Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2005 Underwriters Laboratories Inc.®"