

Figure 1 is a dimensional drawing of a straight and curved tip. The drawing shows two views of a probe tip. The top view is a side profile with dimensions: E (total height), B $\pm .01 (.25)$ (tip height), F REF. (reference length), C REF. (reference length), and A $\pm .01 (.25)$ (tip height). The bottom view shows the tip profile with labels for 'STRAIGHT TIP' and 'CURVED TIP'. A 'THEORETICAL POINT' is indicated on the side profile.

PANDUIT * PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE ^{lbs.} (N)	CROSS SECTION	TIP STYLE	WEIGHT ^{lbs.} /100 pcs (g)
	MIN. ⁱⁿ (mm)	MAX. ⁱⁿ (mm)										
PLT4S	.06 (1.5)	4.00 (102)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	14.5 (368)	50 (222)	STANDARD	CURVED	.56 (254)
PLT4.5S	.06 (1.5)	4.50 (114)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	15.5 (394)	50 (222)	STANDARD	CURVED	.57 (257)
PLT5S	.06 (1.5)	5.00 (127)	.052 (1.3)	.190 (4.8)	.265 (6.7)	.220 (5.6)	.337 (8.6)	17.5 (445)	50 (222)	STANDARD	CURVED	.65 (293)
PLT6LH	.188 (4.8)	6.00 (152)	.075 (1.9)	.300 (7.6)	.372 (9.4)	.325 (8.3)	.480 (12.2)	21.9 (556)	120 (534)	LIGHT HEAVY	STRAIGHT	1.86 (845)
PLT7LH	.188 (4.8)	7.00 (178)	.075 (1.9)	.300 (7.6)	.372 (9.4)	.325 (8.3)	.480 (12.2)	24.7 (627)	120 (534)	LIGHT HEAVY	STRAIGHT	2.09 (950)
PLT8LH	.188 (4.8)	8.00 (203)	.075 (1.9)	.300 (7.6)	.372 (9.4)	.325 (8.3)	.480 (12.2)	27.6 (701)	120 (534)	LIGHT HEAVY	STRAIGHT	2.32 (1054)
PLT9LH	.188 (4.8)	9.00 (229)	.075 (1.9)	.300 (7.6)	.372 (9.4)	.325 (8.3)	.480 (12.2)	30.5 (775)	120 (534)	LIGHT HEAVY	STRAIGHT	2.56 (1161)
PLT10LH	.188 (4.8)	10.31 (262)	.075 (1.9)	.300 (7.6)	.372 (9.4)	.325 (8.3)	.480 (12.2)	34.3 (871)	120 (534)	LIGHT HEAVY	STRAIGHT	2.83 (1285)

1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

SS_5540_00.PRT

										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS		
										PANDUIT CORP. TINLEY PARK, ILLINOIS		
										PAN-TY CABLE TIES PLT SERIES		
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± ----- (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± -----		
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY CEW	MAT'L: NYLON 6/6	
24	11/4/02	JABO		ADDED DIMENSION 'C' TO CABLE TIE, MISSING ON DRAWING.	5540	24				DATE 12-27-84		SCALE NONE
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			CHK'D HVP		DRAWING NO. SS-5540 SHEET 3