

4		3		2		1							
THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC		DIST		REVISIONS					
© COPYRIGHT — By —		ALL RIGHTS RESERVED.		—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
									G1	REVISED PER ECO-11-020548	02FEB12	KH	DR

1 FOR 2.67[.105] TO 3.56[.140] WIRE INSULATION DIA

INSULATION

SERRATIONS

AMP

AMP

AMP

AMP

BODY

27.05

[1.065]

MAX

WIRE STOP

100	LOOSE PC/BOX	INSULATION: PVC COLOR: BLUE BODY: COPPER PER ASTM B152 TIN PLATE PER ASTM B545	8-34068-1
2500	34068 ON TAPE		2-34068-1
1000	LOOSE PIECE		34068
QTY	PACKAGE TYPE	MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.20[.008]
4 PLC ± -
ANGLES ± 5°

MATERIAL

-

FINISH

-

DWN
KIRAN HOLAL
02FEB12

CHK
ROHDE DANIEL
02FEB12

APVD
ROHDE DANIEL
02FEB12

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

STE

TE Connectivity

NAME

WIRE SPLICE PLASTI GRIP, BUTT, WIRE SIZE: 16-14

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-34068

-

CUSTOMER DRAWING

SCALE 8:1

SHEET 1 OF 1

REV G1

1470-19 (3/11)