

SPECIFICATION FOR APPROVAL

客 戶

CUSTOMER:

客 戶 料 號

CUSTOMER PARTS NO.:

品 名

DC BRUSHLESS FAN

DESCRIPTION:

機種

BP802524L-02

MODEL NO.:

檔案序號

D802524LB-A0

FILE NO.:

核示 ISSUE	研發 R&D	品保 QA	版數 REVISION

客 戶 承 認

CUSTOMER APPROVAL

BI-SONIC TECHNOLOGY CO., LTD

HEADQUARTER: 2F, NO. 137, LANE 235, PAO CHAIO RD.,
HSIN-TIEN CITY, TAIPEI HSIEN, 231, TAIWAN , R.O.C.

TEL:(02)89192168 FAX:(02)89192169

PERFORMANCE SPECIFICATION

PRODUCT TITLE : DC BRUSHLESS FAN

MODEL NO : BP802524L-02

1、SCOPE :

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE DC BRUSHLESS AXIAL FLOW FAN. THE FAN MOTOR IS WITH TWO PHASES AND FOUR POLES.

2、ELECTRICAL CHARACTERISTICS :

ALL MEASUREMENTS PERFORMED AT 20~30°C ROOM TEMPERATURE & 50~70%R.H.UNLESS OTHERWISE SPECIFIED.

ITEM	DESCRIPTION	UNIT	SYMBOL	SPEC.	CONDITION
1	RATED VOLTAGE	VOLTS	V	24	
2	OPERATION VOLTAGE	VOLTS	V	20.4~27.6	
3	INPUT CURRENT	AMP	A	0.09MAX	AT RATED VOLTAGE
4	INPUT POWER	WATTS	W	2.16MAX	AT RATED VOLTAGE
5	ROTATION SPEED	RPM	RPM	2200± 10%	AT RATED VOLTAGE FREE AIR
6	ACOUSTICAL NOISE (AVG)	dB(A)	dB(A)	25± 10%	DETAILS SEE ATTACHED PAGE.
7	MAX. AIR-FLOW	CFM	Q	27.8± 10%	TWO-CHAMBER METHODS DETAILS SEE ATTACHED PAGE.
8	MAX. AIR-PRESSURE	mmHzO	P	2.45± 10%	TWO-CHAMBER METHODS DETAILS SEE ATTACHED PAGE.
9	STARTING VOLTAGE	VOLTS	V	12	AT RATED VOLTAGE
10	INSULATION RESISTANCE	MEG. OHM	MΩ	10MΩ MIN. AT 500V DC	BETWEEN FRAME AND (+) LEAD WIRE
11	DIELECTRIC STRENGTH	MILLI-AMP	mA	5mA MAX. AT 500V AC 60Hz. FOR 1 MINUTE	BETWEEN FRAME AND (+) LEAD WIRE

BI-SONIC TECHNOLOGY
CO., LTD.

FILE NO :

D802524LB-A0

REVISIONS :

ITEM	DESCRIPTION	SPEC.	
12	ROTATION	CW VIEW FROM NAME PLATE SIDE	
13	AIR-FLOW DIRECTION	AIR INTAKE OVER THE STRUTS	
14	INSULATION RANK	UL : CLASS A	
15	LIFE EXPECTANCY	50000 HOURS CONTINUOUS	☆

☆ LIFE IS DEFINED AS THE TIME MOTOR SPEED DECREASED MORE THAN 30% COMPARED WITH INITIAL VALUE.

3、MECHANICAL

- 3-1. DIMENSIONS----- SEE SECTION 8
- 3-2. FRAME ----- PLASTIC PBT UL : 94V-0 RATING + FIBRE GLASS.
- 3-3. FAN BLADE----- PLASTIC PBT UL : 94V-0 RATING + FIBRE GLASS.
- 3-4. BEARING SYSTEM ----- BALL BEARING
- 3-5. WEIGHT----- 100 GRAMS
- 3-6. LEAD WIRE----- 1007 AWG # 24
 - + POSITIVERED
 - NEGATIVE.....BLACK

4、ENVIRONMENTAL :

- 4-1. OPERATING TEMPERATURE----- -10 TO +70°C
- 4-2. STORAGE TEMPERATURE----- -40 TO +75°C
- 4-3. DROP TEST

IN MINIMUM PACKAGING CONDITION FAN WITHSTANDS EACH ONE DROP OF THREE FACES FROM 30CM DISTANCE HEIGHT ONTO 10mm THICKNESS OF WOODEN BOARD.
- 4-4. VIBRATION TEST

FREQUENCY :10— 55Hz AMPLITUDE : 4MM

X , Y , Z DIRECTION EACH FOR 1 HR.

**BI-SONIC TECHNOLOGY
CO., LTD.**

FILE NO :

D802524LB-A0

REVISIONS :

4-5. SHOCK TEST

APPLY PEAK ACCELERATION 50g AND KEEP DURATION OF THE PULSE FOR 11ms (HALF SINE WAVE) .

5 、 PROTECTION :

5-1. POLARITY PROTECTION


BUILT-IN ELECTRONIC CIRCUIT PROTECTS THE FAN AGAINST REVERSE CONNECTION OF POSITIVE AND REVERSE LEADS .

5-2. LOCKED ROTOR PROTECTION

IMPEDANCE OF MOTOR COIL WINDING PROTECTS MOTOR FROM FLAMING IN THE CONDITION OF 72 Hrs LOCKED ROTOR AT RATED VOLTAGE .

6 、 ACOUSTICAL NOISE :

6-1. MEASUREMENT SET-UP



6-2. MEASUREMENT PERFORMED IN ANECHOIC TEST CHAMBER UNDER FREE AIR CONDITION .

6-3. CHAMBER BACKGROUND NOISE 17dB MAX .

6-4. READING TAKEN FROM SPECTRUM ANALYZER .

6-5. NOISE DISTRIBUTION CURVE SEE ATTACHED PAGE .


7 、 STATICS PRESSURE VS AIR FLOW CURVE :

MEASURED PER TWO CHAMBER METHOD .

DATA-CURVE SEE ATTACHED PAGE .

8、DIMENSIONS DRAWING：

UNIT:mm





**BI-SONIC TECHNOLOGY
CO., LTD.**

FILE NO：

D802524LB-A0

REVISIONS：

BI-SONIC FAN PERFORMANCE CURVES



BI-SONIC FAN PERFORMANCE DATA SHEET

Customer: Fan Model:8025-24L Testing Method: Constant Voltage Testing Voltage: DC 24 V, 0Hz Barometric Pressure (cmHg): Dry Bulb Temperature (C):23.9 Relative Humidity (%) 58 File Name:8025-24L	Test No: 8025-24L System Setup:outlet Chamber Testing Date:09-21-1998 Barometric Density (kg/m3):1.14 Testing Engineer:Hsieh Hsin Yuan Remark:
--	--

No	CFM	mmAq	inAq	A	RPM	Watt	
1	27.5	0.51	0.06	0.09	2275	2.16	
2	24.25	0.75	0.018	0.09	2275	2.16	
3	19.94	1.08	0.029	0.09	2276	2.16	
4	12.61	1.23	0.038	0.09	2291	2.16	
5	10.35	1.62	0.049	0.09	2297	2.16	
6	7.47	1.78	0.059	0.09	2295	2.16	
7	4.49	1.95	0.072	0.09	2287	2.16	
8	0.01	2.32	0.085	0.09	2273	2.16	

BI-SONIC TECHNOLOGY CORP NOISE TEST REPORT

測試機種: 8025-L

測試目的: ☐ Evaluation 評估

工 令: _____

☐ IPQC

取 樣: _____ pcs

☐ QA

資料代碼:

8025-L

測試頻率:

10KHz

測試感度:

0dB

觸發感度:

8/128

觸發位置:

100點

Y軸上限:


30.00

Y軸下限:

10.00

平均次數:

3次



OV. AL	—	23.02771dB	MAXIM	1.500kHz	16.22742dB
LEFT	5.000kHz	1.43494 dB	MINIM	0.0000Hz	-289.418dB

結果分析: _____

(1) Background Noise : 17dBA

(2) FFT Analyzer

(3) Sound Pressure Level Meter

No.RR01.04A

Reporter: _____

Date : 2000-09-25

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bi-Sonic:](#)

[BP802524L-02 W-G](#)