



April 2015

# Multilayer Balun

For 1920-2170MHz

# HHM17146A1

---

**1.6x0.8mm [EIA 0603]\***

\* Dimensions Code JIS[EIA]


**Multilayer Balun**

For 1920-2170MHz


Conformity to RoHS Directive

**HHM17146A1****■ SHAPES AND DIMENSIONS**

[Top view]




[Bottom view]



## Terminal functions

1	Unbalanced port
2	GND or DC feed+ RF GND
3	Balanced port
4	Balanced port
5	GND
6	N.C.

Dimensions in mm

**■ RECOMMENDED LAND PATTERN**

○ RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. <http://product.tdk.com/en/environment/rohs/>

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

## HHM17146A1

## ■ ELECTRICAL CHARACTERISTICS

Item	Frequency Range (MHz)	Min.	Typ.	Max.
Unbalanced Port Characteristic Impedance ( $\Omega$ )			50 (Nominal)	
Balanced Port Characteristic Impedance ( $\Omega$ )			50 (Nominal)	
Return Loss at Unbalanced Port (dB)	1920 to 2170	10	—	—
Phase Balance (deg.)	1920 to 2170	170	—	190
Amplitude Balance (dB)	1920 to 2170	-1.0	—	1.0
Insertion Loss (dB)	1920 to 2170	—	—	0.8

## ■ TEMPERATURE RANGE


Operating temperature (°C)	Storage temperature (°C)
-40 to +85	-40 to +85

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.


## HHM17146A1

## ■ FREQUENCY CHARACTERISTICS


## □ INSERTION LOSS




## □ AMPLITUDE BALANCE



## □ RETURN LOSS




## □ PHASE BALANCE



- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.

## ■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering		Peak	
			Critical zone (T3 to T4)			
Temp.	Time		Temp.	Time	Temp.	Time
$T_1$ 150°C	$T_2$ 200°C	$t_1$ 60 to 120sec	$T_3$ 217°C	$t_2$ 60 to 120sec	$T_4$ 240 to 260°C	$t_3^*$ 30sec max.

\*  $t_3$  : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

# REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

## SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

### REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

(1) Aerospace/Aviation equipment	(8) Public information-processing equipment
(2) Transportation equipment (cars, electric trains, ships, etc.)	(9) Military equipment
(3) Medical equipment	(10) Electric heating apparatus, burning equipment
(4) Power-generation control equipment	(11) Disaster prevention/crime prevention equipment
(5) Atomic energy-related equipment	(12) Safety equipment
(6) Seabed equipment	(13) Other applications that are not considered general-purpose applications
(7) Transportation control equipment	

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.

---

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.