

MOS FIELD EFFECT TRANSISTOR

2SK3299

SWITCHING N-CHANNEL POWER MOS FET INDUSTRIAL USE

DESCRIPTION

The 2SK3299 is N-Channel MOS FET device that features a low gate charge and excellent switching characteristics, designed for high voltage applications such as switching power supply, AC adapter.

ORDERING INFORMATION

PART NUMBER	PACKAGE
2SK3299	TO-220AB
2SK3299-S	TO-262
2SK3299-ZJ	TO-263

FEATURES

- Low gate charge
 $Q_G = 34 \text{ nC TYP. } (V_{DD} = 450 \text{ V}, V_{GS} = 10 \text{ V}, I_D = 10 \text{ A})$
- Gate voltage rating $\pm 30 \text{ V}$
- Low on-state resistance
 $R_{DS(on)} = 0.75 \Omega \text{ MAX. } (V_{GS} = 10 \text{ V}, I_D = 5.0 \text{ A})$
- Avalanche capability ratings
- Surface mount package available

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$)

Drain to Source Voltage ($V_{GS} = 0 \text{ V}$)	V_{DSS}	600	V
Gate to Source Voltage ($V_{DS} = 0 \text{ V}$)	V_{GSS}	± 30	V
Drain Current (DC) ($T_c = 25^\circ\text{C}$)	$I_D(\text{DC})$	± 10	A
Drain Current (Pulse) ^{Note1}	$I_D(\text{pulse})$	± 40	A
Total Power Dissipation ($T_A = 25^\circ\text{C}$)	P_{T1}	1.5	W
Total Power Dissipation ($T_c = 25^\circ\text{C}$)	P_{T2}	75	W
Channel Temperature	T_{ch}	150	$^\circ\text{C}$
Storage Temperature	T_{stg}	-55 to +150	$^\circ\text{C}$
Single Avalanche Current ^{Note2}	I_{AS}	10	A
Single Avalanche Energy ^{Note2}	E_{AS}	66.7	mJ

Notes 1. $PW \leq 10 \mu\text{s}$, Duty Cycle $\leq 1\%$


2. Starting $T_{ch} = 25^\circ\text{C}$, $V_{DD} = 150 \text{ V}$, $R_g = 25 \Omega$, $V_{GS} = 20 \text{ V} \rightarrow 0 \text{ V}$

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.
Not all devices/types available in every country. Please check with local NEC representative for availability and additional information.


ELECTRICAL CHARACTERISTICS($T_A = 25^\circ\text{C}$)

CHARACTERISTICS	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Drain Leakage Current	I_{DSS}	$V_{DS} = 600 \text{ V}, V_{GS} = 0 \text{ V}$			100	μA
Gate Leakage Current	I_{GSS}	$V_{GS} = \pm 30 \text{ V}, V_{DS} = 0 \text{ V}$			± 100	nA
Gate Cut-off Voltage	$V_{GS(\text{off})}$	$V_{DS} = 10 \text{ V}, I_D = 1 \text{ mA}$	2.5		3.5	V
Forward Transfer Admittance	$ y_{fs} $	$V_{DS} = 10 \text{ V}, I_D = 5.0 \text{ A}$	3.2			S
Drain to Source On-state Resistance	$R_{DS(\text{on})}$	$V_{GS} = 10 \text{ V}, I_D = 5.0 \text{ A}$		0.68	0.75	Ω
Input Capacitance	C_{iss}	$V_{DS} = 10 \text{ V}$		1580		pF
Output Capacitance	C_{oss}	$V_{GS} = 0 \text{ V}$		280		pF
Reverse Transfer Capacitance	C_{rss}	$f = 1 \text{ MHz}$		25		pF
Turn-on Delay Time	$t_{d(\text{on})}$	$V_{DD} = 150 \text{ V}, I_D = 5.0 \text{ A}$		27		ns
Rise Time	t_r	$V_{GS(\text{on})} = 10 \text{ V}$		17		ns
Turn-off Delay Time	$t_{d(\text{off})}$	$R_G = 10 \Omega$		66		ns
Fall Time	t_f			24		ns
Total Gate Charge	Q_G	$V_{DD} = 450 \text{ V}$		34		nC
Gate to Source Charge	Q_{GS}	$V_{GS} = 10 \text{ V}$		8.2		nC
Gate to Drain Charge	Q_{GD}	$I_D = 10 \text{ A}$		12.3		nC
Diode Forward Voltage	$V_{F(\text{S-D})}$	$I_F = 10 \text{ A}, V_{GS} = 0 \text{ V}$		1.0		V
Reverse Recovery Time	t_{rr}	$I_F = 10 \text{ A}, V_{GS} = 0 \text{ V}$		1.9		μs
Reverse Recovery Charge	Q_{rr}	$di/dt = 50 \text{ A}/\mu\text{s}$		12		μC


TEST CIRCUIT 1 AVALANCHE CAPABILITY















TEST CIRCUIT 2 SWITCHING TIME






TEST CIRCUIT 3 GATE CHARGE






★ TYPICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)






TRANSIENT THERMAL RESISTANCE vs. PULSE WIDTH






PACKAGE DRAWINGS (Unit : mm)


1)TO-220AB (MP-25)




2)TO-262 (MP-25 Fin Cut)



3)TO-263 (MP-25ZJ)



EQUIVALENT CIRCUIT



Remark Strong electric field, when exposed to this device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop generation of static electricity as much as possible, and quickly dissipate it once, when it has occurred.

- **The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.**
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.
- NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.
- Descriptions of circuits, software, and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software, and information in the design of the customer's equipment shall be done under the full responsibility of the customer. NEC Corporation assumes no responsibility for any losses incurred by the customer or third parties arising from the use of these circuits, software, and information.
- While NEC Corporation has been making continuous effort to enhance the reliability of its semiconductor devices, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC semiconductor device, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features.
- NEC devices are classified into the following three quality grades:
"Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.

Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots

Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)

Specific: Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc.

The quality grade of NEC devices is "Standard" unless otherwise specified in NEC's Data Sheets or Data Books. If customers intend to use NEC devices for applications other than those specified for Standard quality grade, they should contact an NEC sales representative in advance.