

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 1/25
	Document prepared and responsible for				
	M. Obritzhauser				Standard Programme
	Responsible for technical data				
		Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D


EGSTON

Switch Mode Power Supply

Product Name: P2xFSW3 12W

Standard Programme

Input:	90 - 264 V AC
Output :	4,5V – 24V max. 12W max. 2,4A
Type:	P2xFSW3 12W



CONFIDENTIAL

This document contains proprietary information originated and/or owned by EGSTON GmbH. This information shall not be duplicated, used or disclosed in whole, or in part, to any other party or used for any other purpose without the prior consent of EGSTON GmbH.

Copyright © 2005 EGSTON GmbH.
A-3730 Eggenburg, Grafenberger Strasse 37
All Rights Reserved.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 2/25		
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			11	11	05	D

1.1	Evolution	3
2	Scope	3
3	Technical Specification Sheet	4
3.1	Input Specification	4
3.2	Safety and Environmental Conditions	4
3.3	Output Specification	5
3.3.1	Output template	6
3.3.2	Output Ripple Voltage	7
4	Mechanical Parameters	9
4.1	Housing dimension	9
4.1.1	Euro housing	9
4.1.2	US Housing	10
4.1.3	UK Housing	10
4.1.4	Desk Top Housing	11
4.1.5	Australia Housing	12
4.1.6	Housing Material	12
5	Cable And Connector	13
6	Marking on the housing	13
6.1	Plug In Devices	13
6.1.1	EU/UK devices	13
6.1.2	US devices	14
6.1.3	Australia Version	14
6.1.4	Desktop Devices	15
7	EMC	16
7.1	Emission with representative 15V device:	16
7.2	Immunity To Flicker	18
7.3	Immunity to Fast Transients (Burst)	18
7.4	Immunity to Radiated Electromagnetic Field	18
7.5	Immunity to Electrostatic Discharge	18
7.6	Surge Capability	18
7.7	Immunity to conducted disturbances	18
7.8	Immunity to voltage dips, short interruptions and voltage variations	18
8	Reliability	19
8.1	MTBF	19
8.2	Maintainability	19
9	Safety	20
9.1	Dielectric Strength	20
9.2	Over-current Protection	20
9.3	Single Component Failure	20
9.4	Short Circuit	20
10	Approvals and test standards	21
10.1	Test Standards	21
10.2	Approvals	21
10.2.1	EU/UK devices	21
10.2.2	US devices	22
10.2.3	Desktop Devices	22
10.2.4	Australia Devices	22
11	Ordering Information	23
12	Packaging and weight	24
13	Specials Features:	25
13.1	Output voltage tolerance 1%	25
13.2	Visual operation Display (green LED)	25
13.3	Current regulation	25
13.4	Cable Compensation with 4 wire system	25
13.5	Pluggable secondary cable	25
13.6	Customer specific secondary Plug	25
13.7	Print module	25

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 3/25	
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

1.1 Evolution

Edition	Date	Responsible	Reason of change
A	28.05.2003	Obritzhauser	First edition
B	29.07.2003	Obritzhauser	EMC Standards Revised
C	04.02.2004	Obritzhauser	Input Voltage Range Extended
D	11.11.2005	Obritzhauser	Australia Version implemented

2 SCOPE

This document describes a switch mode power supply unit (AC/DC converter) with fixed output voltage.

The unit is designed as a Wall Plug In power supply or a Desk Top Module.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 4/25		
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			11	11	05	D

3 TECHNICAL SPECIFICATION SHEET

3.1 Input Specification

Parameter	Key	Min	Typ.	Max	Unit	Test Cond.
Input Voltage	U_{IN}	90		264	V	AC
Input Current	I_{IN}	3	250	320	mA	
Input Frequency	f_{IN}	47		63	Hz	
Efficiency	η	75		85	%	At full load
Switching Frequency	f_{sw}		40		kHz	
Stand-by power	P_{stb}		650		mW	Without load

Input Voltage

If the input voltage is out of operating range, the power supply does not meet the full specification. Above the specified upper limit of the input voltage the unit can get damaged. Below the specified lower limit of the input voltage the unit does not meet the specification.

Efficiency Under Load

The efficiency is defined as the ratio between the output power and input power.

3.2 Safety and Environmental Conditions

Parameter	Key	Min	Typ.	Max	Unit	Test Cond.
Dielectric Strength		4,24			kV _{Dc}	
Operating Temperature		-5		40	°C	
		23		104	°F	
Storage Temperature		-30	25	80	°C	
		-22	77	176	°F	
Humidity				95	%	

	PRODUCT SPECIFICATION P2xFSW3 12W							Page 5/25
	Document prepared and responsible for							
	M. Obritzhauser				Standard Programme			
	Responsible for technical data				Day	Month	Year	Revision
	M. Obritzhauser				11	11	05	D


3.3 Output Specification

Parameter	Key	Min	Typ.	Max	Unit	Test Cond.	Available on request
Output Voltage	U_2	4,5		24	V	0 – 2,4 A	
Output voltage tolerance	T_{U2}			3	%	at PCB	1% Cable compensation
Output Current	$I_{2 \text{ Nominal}}$	2,4			A		Current regulation
Max. Overload current	$I_{2 \text{ Overload}}$		180 160		% of $I_{2 \text{ Nominal}}$	$U_{IN} = 264V$ $U_{IN} = 90V$	
Output Power	P_2		12		W		
Ripple Voltage	$U_{2,rms}$			50 50	mV _{rms}	$U_{IN} = 264V$ $U_{IN} = 90V$	

The unit is not long time overload proof. If the unit is powered longer than 1 min in overload conditions (current range between $I_{2 \text{ Nominal}}$ and $I_{2 \text{ Overload}}$), the device can be damaged.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 6/25
	Document prepared and responsible for				
	M. Obritzhauser				Standard Programme
	Responsible for technical data				
		Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

3.3.1 Output template



Specified operating area:

At an output current from 0A to $I_{2\text{ Nominal}}$ the unit fulfills all specified data.

Overload area:

At an output current from $I_{2\text{ Nominal}}$ to $I_{2\text{ Overload}}$ the power supply delivers the specified output voltage U_2 .

The unit is not long time overload proof. If the unit is powered longer than 1 min in overload conditions, the device can be damaged.

Trickle mode area:


If the power demand would be higher than $I_{2\text{ Overload}}$ or the power supply works in short circuit the output voltage and current can not be defined (this parameters are not stable). The wattage of the SMPS is de-rated. In this mode the unit can not be damaged. After removing this conditions the unit fulfills the specification.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 7/25
	Document prepared and responsible for				
	M. Obritzhauser				Standard Programme
	Responsible for technical data				Day Month Year Revision
	M. Obritzhauser				11 11 05 D


3.3.2 Output Ripple Voltage

The output ripple voltage is measured with an oscilloscope 20Mhz band limited at a representative 15V sample.

3.3.2.1 Measurement at 230V input voltage and 0,8A load




Ripple Voltage at switching frequency measured at a temperature of +25°C




Ripple Voltage at mains frequency measured at a temperature of +25°C

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 8/25
	Document prepared and responsible for				
	M. Obritzhauser				Standard Programme
	Responsible for technical data				
	M. Obritzhauser	Day	Month	Year	Revision
		11	11	05	D

3.3.2.2 Measurement at 120V input voltage and 0,8A load



Ripple Voltage at switching frequency measured at a temperature of +25°C




Ripple Voltage at mains frequency measured at a temperature of +25°C

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 9/25
	Document prepared and responsible for				.
	M. Obritzhauser				Standard Programme
	Responsible for technical data				Day Month Year Revision
	M. Obritzhauser				11 11 05 D

4 MECHANICAL PARAMETERS


4.1 Housing dimension

4.1.1 Euro housing




	PRODUCT SPECIFICATION P2xFSW3 12W			Page 10/25		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

4.1.2 US Housing




4.1.3 UK Housing




	PRODUCT SPECIFICATION P2xFSW3 12W				Page 11/25		
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			11	11	05	D

4.1.4 Desk Top Housing

With IEC 320 C14 Primary Plug




With IEC 320 C8 primary Plug



	PRODUCT SPECIFICATION P2xFSW3 12W			Page 12/25	
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

4.1.5 Australia Housing



4.1.6 Housing Material

	12W UK,EURO,US, AUS	DESKTOP
Material	PA6	PA6
Flammability rate	V0	V0

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 13/25
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

5 CABLE AND CONNECTOR

According to customer's requirements.

6 MARKING ON THE HOUSING

6.1 Plug In Devices

6.1.1 EU/UK devices

Laser marking
Product name
Input parameters
Output parameters
Product code
Safety Instructions

 Conformity Mark with the EU low voltage directive and EMC directive



ENEC Mark



GS Mark

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 14/25
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

6.1.2 US devices

Laser marking
 Product name
 Input parameters
 Output parameters
 Product code
 Safety Instructions



Conformity Mark with the EU low voltage directive and EMC directive



GS Mark



UL Mark for Canada and the United States

6.1.3 Australia Version

Laser marking
 Product name
 Input parameters
 Output parameters
 Serial number
 Product code
 Sign to read manual
 Safety Instructions
 Australia Approval number

	PRODUCT SPECIFICATION P2xFSW3 12W			Page 15/25
	Document prepared and responsible for			
	M. Obritzhauser		Standard Programme	
	Responsible for technical data	Day	Month	Year Revision
	M. Obritzhauser	11	11	05 D

6.1.4 Desktop Devices

Laser marking
 Product name
 Input parameters
 Output parameters
 Product code
 Safety Instructions



Conformity Mark with the EU low voltage directive and EMC directive



ENEC Mark



GS Mark



UL Mark for Canada and the United States

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 16/25	
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D


7 EMC

The units meet the following EMC requirements:

7.1 Emission with representative 15V device:


Test passed according to EN55022 Class B.

Primary: 230V AC, Secondary: 15V / 800mA , Temperature: 25°C, Load connected to ground, Peak and Average Measurement.



Date: 05-30-2003

Limit: C22_B_QP
PMM 8010




Date: 05-30-2003

Limit: C22_B_AV

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 17/25	
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

Test passed according to FCC15 Class B.

Primary: 120V AC, Secondary: 15V / 800mA , Temperature: 25°C, Load connected to ground, Peak Measurement



	PRODUCT SPECIFICATION P2xFSW3 12W			Page 18/25		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

7.2 Immunity To Flicker

Test according to EN 61000-3-2

7.3 Immunity to Fast Transients (Burst)

Test according to EN61000-4-4

Input Line: 2.0kV – 5/50 ns – 5.0 kHz

Output Line: 2.0kV – 5/50 ns – 5.0 kHz

7.4 Immunity to Radiated Electromagnetic Field

Test according to EN 61000-4-3

Test characteristic: 80 – 1000 MHz; 80% AM (1kHz), 3V/m

7.5 Immunity to Electrostatic Discharge

Test according to EN 61000-4-2

Test characteristic: Contact discharge 6kV

Air discharge 8kV

7.6 Surge Capability

Test according to EN61000-4-5

Test characteristic: line to line: 1kV Surge

line to earth: 2kV Surge

7.7 Immunity to conducted disturbances

Test according to EN 61000-4-6

Test characteristic: 150kHz – 80 MHz; 80% AM (1kHz), 3V

7.8 Immunity to voltage dips, short interruptions and voltage variations

Test according to EN 61000-4-11

Test criterion C

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 19/25		
	Document prepared and responsible for						
	M. Obritzhauser			Standard Programme			
	Responsible for technical data			Day	Month	Year	Revision
	M. Obritzhauser			11	11	05	D

8 RELIABILITY

8.1 MTBF

at 240V input voltage $\geq 2.300.000$ hours

at 100V input voltage $\geq 2.000.000$ hours

MTBF calculation according SN 29500 at 40°C ambient temperature

8.2 Maintainability

The power supply is not to be repaired.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 20/25
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

9 SAFETY

The units pass the following tests:

9.1 Dielectric Strength

The input isolation test voltage is 3kV 50/60 Hz, sinusoidal waveform. Test duration is 2 seconds for 100% test, 1 minute 4,24KV DC or lot-test.

9.2 Over-current Protection

The unit is not long time over-current proof. If the unit is powered longer than 1 min in overload conditions, the device can be damaged.

9.3 Single Component Failure

A single component failure does not cause any damage to persons or ambient (fire, explosions, etc).

9.4 Short Circuit

The power supply is designed with a short circuit protection. A shortened output does not cause any damage to persons or ambient (fire, explosions, etc.) After removing this conditions the unit fulfills the specification.

	PRODUCT SPECIFICATION P2xFSW3 12W			Page 21/25		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

10 APPROVALS AND TEST STANDARDS

10.1 Test Standards

EN 60 950
 UL 1310
 EN 61000-6-1
 EN 55022
 EN 55011
 EN 55014-1
 EN 61204-3

10.2 Approvals

10.2.1 EU/UK devices



Conformity with the EU low voltage directive and EMC directive



ENEC



GS

	PRODUCT SPECIFICATION P2xFSW3 12W			Page 22/25		
	Document prepared and responsible for					
	M. Obritzhauser		Standard Programme			
	Responsible for technical data		Day	Month	Year	Revision
	M. Obritzhauser		11	11	05	D

10.2.2 US devices

 Conformity with the EU low voltage directive and EMC directive



GS



UL for Canada and the United States

10.2.3 Desktop Devices

 Conformity with the EU low voltage directive and EMC directive



ENEC



GS



UL for Canada and the United States

10.2.4 Australia Devices

Queensland Government – Department of Industrial Relations
Egston approval number: Q050400

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 23/25
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

11 ORDERING INFORMATION

	POWER CLASS	12 Watt
P	SUPPLY TYPE	P = New Gereneration Power Supply
2	OPERATION TEMP. RANGE	2 = -5°C to +40°C
E	PRIMARY CONNECTOR	E = Euro plug U = US/Japan/Canada Plug G = United Kingdom Plug D = Desktop Module A= Ausralia Plug
F	CABLE CONNECTION	F = Fixed
S	APPLICATION	S = Standard M = Medical H = Household
W	WIDE INPUT RANGE	W = 90V-264V
3	OUTPUT STABILITY	3 = 3%
12W	HOUSING DIMENSION	12W
12V	OUTPUT VOLTAGE	4.5V-24V
1A	OUTPUT CURRENT	2400mA max.

	PRODUCT SPECIFICATION P2xFSW3 12W				Page 25/25
	Document prepared and responsible for				
	M. Obritzhauser		Standard Programme		
	Responsible for technical data	Day	Month	Year	Revision
	M. Obritzhauser	11	11	05	D

13 SPECIALS FEATURES:

Following Specials can be offered on request

13.1 Output voltage tolerance 1%

The output voltage can be adjusted with a tolerance of $\pm 1\%$.

13.2 Visual operation Display (green LED)

When the green led is shining the output voltage is delivered.

13.3 Current regulation

The secondary voltage will be reduced when the selected output current is reached.

The max. Current which can be selected is 80% of $I_{2\text{ Nominal}}$.

The current regulation can be delivered at the secondary voltage range from 5 to 24V.

13.4 Cable Compensation with 4 wire system

The voltage drop of the secondary cable will be compensated.

The maximum output wattage is defined at the PCB.

13.5 Pluggable secondary cable

Only available at Egston Standard Wall Plug In Powersupplies.

13.6 Customer specific secondary Plug

13.7 Print module

The power supply is built in a housing which can be soldered on to a PCB.