


10/100BASE-TX QUAD PORT TRANSFORMER MODULES

For Use with Level One's LXT974, LXT975
and LXT980 Series of PHY Solutions



-  Patented interlock base design for high reliability
-  Compliant with IEEE 802.3u and ANSI X3.263 standards including 350 μ H OCL with 8 mA bias from 0°C to 70°C
-  Designed for optimal single and double stacked RJ-45 layouts
-  IC grade, transfer-molded package withstands 235°C peak temperature profile

Electrical Specifications @ 25°C — Operating Temperature 0°C to 70°C

Part Number	Insertion Loss (dB TYP)	Return Loss (dB TYP)					Crosstalk (dB MIN)				Common to Common Rejection Ratio 0.1-60 MHz (dB MIN)		Differential to Common Mode Rejection (dB MIN)	
	0.1-100 MHz	2-30 MHz	40 MHz	50 MHz	60-80 MHz	1 MHz	30 MHz	60 MHz	100 MHz		Transmit	Receive	1-60 MHz	60-200 MHz
H1068	-0.5	-21	-17	-14.5	-12	-60	-50	-40	-35		-30	-30	-40	-30
H1069	-0.5	-21	-17	-14.5	-12	-60	-50	-40	-35		-30	-30	-40	-30
H1074	-0.5	-21	-17	-14.5	-12	-60	-50	-40	-35		-30	-30	-40	-30


NOTES:

1. All product meets input/output breakdown (HiPot) of 1500 Vrms.
2. Transfer molding material is UL-94V0 flammability rated.

U.S. Patent No. 5,015,981

Mechanical

H10XX



Dimensions: Inches Unless otherwise specified, all tolerances are $\pm .010$
mm 0,25

10/100BASE-TX QUAD PORT TRANSFORMER MODULES


For Use with Level One's LXT974, LXT975 and LXT980 Series of PHY Solutions




Pulse
A TECHNITROL COMPANY

Schematics

H1068



H1069




10/100BASE-TX QUAD PORT TRANSFORMER MODULES

For Use with Level One's LXT974, LXT975 and LXT980 Series of PHY Solutions




Schematic

H1074



Tape and Reel Specifications



10/100BASE-TX QUAD PORT TRANSFORMER MODULES

For Use with Level One's LXT974, LXT975
and LXT980 Series of PHY Solutions



Pulse
A TECHNITROL COMPANY

For More Information :

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (China/Hong Kong)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 6287 8998 FAX: 65 6280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	9/F, Phase 2, Tai Sang Shatin Warehouse Centre 6 Wong Chuk Yeung Street Fotan Shatin, Hong Kong TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

♻️ Printed on recycled paper. ©Copyright, 2003. Pulse Engineering, Inc. All rights reserved.

H321.A (4/03)