



SAW Components

SAW GPS + GLONASS filter

Series/type:	B9474
Ordering code:	B39162B9474P810
Date:	October 19, 2010
Version:	2.1



SAW Components

B9474

SAW GPS + GLONASS filter

1585.655 MHz

Data sheet




Application

- Low-loss RF GPS+GLONASS filter
- Simultaneous usage of GPS band and GLONASS band
- Usable passbands: 2.0 MHz for GPS (20.0 MHz for wide-band GPS) and 8.34 MHz for GLONASS
- Very low insertion attenuation
- Impedance transformation from 50 Ω to 100 Ω
- Unbalanced to balanced operation
- No matching network required for operation at 50 Ω




Features

- Package size 1.4 x 1.1 x 0.4 mm³
- Package code QCS51
- RoHS compatible
- Approximate weight 0.003 g
- Package for **Surface Mount Technology (SMT)**
- Ni, gold-plated terminals
- **Electrostatic Sensitive Device (ESD)**



Pin configuration

- 1 Input unbalanced
- 3,4 Output balanced
- 2,5 To be grounded





SAW Components

B9474

SAW GPS + GLONASS filter

1585.655 MHz

Data sheet



Characteristics of Filter

Temperature range for specification: $T = -30\text{ °C to }+85\text{ °C}$
Terminating source impedance: $Z_S = 50\ \Omega$
Terminating load impedance: $Z_L = 100\ \Omega$

		B9474			
		min.	typ. @ 25 °C	max.	
Center frequency	f_C	—	1585.65		MHz
Maximum insertion attenuation	S_{ds21}				
1574.42 ... 1576.42 MHz		—	0.9	1.4	dB
1565.42 ... 1585.42 MHz		—	1.3	1.8	dB
1597.55 ... 1605.89 MHz		—	1.2	2.0	dB
VSWR Input					
1574.42 ... 1576.42 MHz		—	1.2	2.0	
1597.55 ... 1605.89 MHz		—	1.4	2.0	
VSWR Output					
1574.42 ... 1576.42 MHz		—	1.2	2.0	
1597.55 ... 1605.89 MHz		—	1.5	2.1	
Group delay ripple¹⁾ (p-p)	$\Delta\tau$				
1597.55 ... 1605.89 MHz			4.5	15	ns
Output amplitude balance (S_{31}/S_{21})					
1574.42 ... 1576.42 MHz		-1.5	-0.6/-0.5	1.5	dB
1597.55 ... 1606.45 MHz		-1.5	-0.5/0.2	1.5	dB
Output phase balance ($\phi(S_{31})-\phi(S_{21})+180^\circ$)					
1574.42 ... 1576.42 MHz		-10	1 / 2	10	°
1597.55 ... 1606.45 MHz		-10	-3 / 2	10	°
Attenuation	S_{ds21}				
0.1 ... 725.0 MHz		50	62		dB
725.0 ... 925.0 MHz		50	60		dB
925.0 ... 1427.0 MHz		35	51		dB
1427.0 ... 1463.0 MHz		35	60		dB
1463.0 ... 1525.0 MHz		20	42		dB
1675.0 ... 1710.0 MHz		20	34		dB
1710.0 ... 1785.0 MHz		35	42		dB
1850.0 ... 1980.0 MHz		40	48		dB
1980.0 ... 2400.0 MHz		32	44		dB
2400.0 ... 2500.0 MHz		45	60		dB
2500.0 ... 2570.0 MHz		35	60		dB

Please read *cautions and warnings* and *important notes* at the end of this document.



SAW Components	B9474
SAW GPS + GLONASS filter	1585.655 MHz

Data sheet



				B9474			
				min.	typ. @ 25 °C	max.	
2570.0	...	3155.0	MHz	40	57		dB
3155.0	...	4000.0	MHz	35	50		dB
4000.0	...	6000.0	MHz	33	46		dB
Common mode suppression							dB
			S_{cs21}				dB
0.1	...	960.0	MHz	45	51		dB
1427.0	...	1463.0	MHz	33	42		dB
1710.0	...	1785.0	MHz	35	47		dB
1850.0	...	1910.0	MHz	39	44		dB
1920.0	...	1980.0	MHz	38	43		dB
2401.0	...	2483.0	MHz	32	37		dB
2500.0	...	2570.0	MHz	31	36		dB

1) Averaged over 1 MHz



SAW Components	B9474
SAW GPS + GLONASS filter	1585.655 MHz

Data sheet



Maximum ratings of Filter

Operable temperature range	T	−30/+85	°C	
Storage temperature range	T _{stg}	−40/+85	°C	
DC voltage	V _{DC}	3	V	
ESD voltage	V _{ESD}	50 ¹⁾	V	machine model
Input power (5000 h, 50°C)				
@ 915 MHz	P _{IN}	23	dBm	1/8 duty cycle
@ 1710 MHz	P _{IN}	15	dBm	cw
@ 1453 MHz	P _{IN}	15	dBm	cw

¹⁾ acc. to JESD22-A115A (machine model).



SAW Components

B9474


SAW GPS + GLONASS filter

1585.655 MHz


Data sheet



Transfer function (passband, differential mode, S_{ds21})



Transfer function (wideband, differential mode, S_{ds21})



Please read *cautions and warnings* and *important notes* at the end of this document.



SAW Components

B9474


SAW GPS + GLONASS filter

1585.655 MHz

Data sheet



Transfer function (common mode, S_{CS21})





SAW Components

B9474

SAW GPS + GLONASS filter



1585.655 MHz

Data sheet





Smith chart / VSWR

S_{11} function



S_{22} function



Please read *cautions and warnings* and *important notes* at the end of this document.

**SAW Components****B9474****SAW GPS + GLONASS filter****1585.655 MHz**

Data sheet



Type	B9474
Ordering code	B39162B9474P810
Marking and package	C61157-A8-A3
Packaging	F61074-V8237-Z000
Date codes	L_1126
S-parameters	B9474_NB.s3p see file header for port/pin assignment table
Soldering profile	S_6001
RoHS compatible	defined as compatible with the following documents: "DIRECTIVE 2002/95/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 27 January 2003 on the restriction of the use of certain hazardous substances in electrical and electronic equipment. 2005/618/EC from April 18th, 2005, amending Directive 2002/95/EC of the European Parliament and of the Council for the purposes of establishing the maximum concentration values for certain hazardous substances in electrical and electronic equipment."
Moldability	Before using in overmolding environment, please contact your EPCOS sales office.
Matching coils	See Inductor pdf-catalog http://www.tdk.co.jp/tefe02/coil.htm#aname1 and Data Library for circuit simulation http://www.tdk.co.jp/etvcl/index.htm

For further information please contact your local EPCOS sales office or visit our webpage at www.epcos.com.

Published by EPCOS AG
Surface Acoustic Wave Components Division
P.O. Box 80 17 09, 81617 Munich, GERMANY

© EPCOS AG 2010. This brochure replaces the previous edition.

For questions on technology, prices and delivery please contact the Sales Offices of EPCOS AG or the international Representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our Sales Offices.

Please read *cautions and warnings and important notes* at the end of this document.



Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI)**.
7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FormFit, MiniBlue, MiniCell, MKD, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.