

SmartRack 12U Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRW12U**



Description

The SRW12U 12U Wall-Mount Rack Enclosure Cabinet is designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable rack rails with square mounting holes accommodate up to 12U of standard 19" rackmount equipment. Supports up to 200 lbs of equipment. A sturdy wall-mount bracket allows the cabinet to quickly be hung on the wall.

Features

- 12U wall-mounted enclosure
- Adjustable mounting depths up to 17" by 2 front vertical rackmount rails
- Ventilated front door and side panels for increased airflow
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Specifications

General Info	
Product Group	RACKS
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	16.5
Installed Whole System Maximum Rack Depth (cm)	41.9

Highlights

- Designed for IT and education environments where equipment needs to be secure and out of the way
- 12U with adjustable front vertical rackmount rails
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Applications

IT network environments with limited floor space and classrooms where equipment needs to be secure and out of the way of students.

Package Includes

- SRW12U Wallmount Rack Enclosure
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 washers
- (2) Keys
- Owner's Manual

Installed Whole System Minimum Rack Depth (in.)	3
Rack Height	12U
Shipping Dimensions (hwd / in.)	27.95 x 26.38 x 20.67
Shipping Dimensions (hwd / cm)	71 x 67 x 52.5
Shipping Weight (lbs.)	55.1
Shipping Weight (kg)	25
Unit Dimensions (in.)	25.08 x 23.63 x 17.69
Unit Weight (lbs.)	48.5
Unit Weight (kg)	22
Unit Dimensions (cm)	63.7 x 60 x 44.93
Color	Black
Style	Wall Mounted
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.