

Inductors, Epoxy Conformal Coated, Uniform Roll Coated, Axial Leded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 1\%$, $\pm 3\%$, $\pm 5\%$, $\pm 10\%$, $\pm 20\%$
Other tolerances available on request

Insulation Resistance: 1000 M Ω minimum per MIL-STD-202, method 302, test condition B

Dielectric Strength: 1000 V_{AC} per MIL-STD-202, method 301

MATERIAL SPECIFICATIONS

Coating: Epoxy-uniform roll coated

Lead: Tinned copper

MECHANICAL SPECIFICATIONS

Terminal Strength: 5 pounds pull per MIL-STD-202, method 211, test condition A

Weight: IR-2 = 0.30 g maximum
IR-4 = 0.65 g maximum

FEATURES

- Flame-retardant coating
- Color band identification
- Excellent environmental characteristics
- Uniform coating is excellent for automatic insertion
- Comparable in quality to molded chokes at a lower price
- Epoxy coating is more durable than lacquer coated models, yet is priced comparably
- Compliant to RoHS directive 2002/95/EC




RoHS
COMPLIANT

TEST EQUIPMENT (1)

- H/P 4342A Q-meter
- Measurements corporation megacycle meter, model 59
- Whearstone bridge

Note

(1) Test procedures per MIL-PRF-15305

DIMENSIONS in inches [millimeters]				
				
MODEL	A (MAX.)	B (MAX.)	C (MAX.)	D
IR-2	0.260 [6.60]	0.120 [3.05]	0.330 [8.38]	0.0200 $\pm$ 0.0015 [0.508 $\pm$ 0.038]
IR-4	0.385 [9.78]	0.180 [4.57]	0.440 [11.18]	0.025 $\pm$ 0.002 [0.635 $\pm$ 0.051]

ENVIRONMENTAL PERFORMANCE		
TEST	CONDITIONS	SPECIFICATIONS
Barometric Pressure	C	MIL-STD-202, method 105
Thermal Shock	A-1	MIL-STD-202, method 107
Flammability	-	MIL-STD-202, method 111
Overload	-	MIL-PRF-15305
Low Temperature Storage	-	MIL-PRF-15305
Resistance to Soldering Heat	A	MIL-STD-202, method 210
Resistance to Solvents	-	MIL-STD-202, method 215

MAXIMUM TEMPERATURE RISE		
MODEL		OPERATING TEMPERATURE RANGE
IR-2	0.1 μ H to 1.0 μ H = + 35 °C at + 90 °C ambient	- 55 °C to 125 °C
	1.2 μ H to 27 μ H = + 15 °C at + 90 °C ambient	- 55 °C to 105 °C
	33 μ H to 1000 μ H = + 15 °C at + 90 °C ambient	- 55 °C to 105 °C
IR-4	0.15 μ H to 4.7 μ H = + 35 °C at + 90 °C ambient	- 55 °C to 125 °C
	5.6 μ H to 33 μ H = + 15 °C at + 90 °C ambient	- 55 °C to 105 °C
	36 μ H to 240 μ H = + 15 °C at + 90 °C ambient	- 55 °C to 105 °C
	270 μ H to 1800 μ H = + 35 °C at + 90 °C ambient	- 55 °C to 125 °C



STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY L AND Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IR-2	0.10	± 10	40	25.0	680.0	0.08	1350	PHENOLIC CORE
IR-2	0.12	± 10	40	25.0	640.0	0.09	1270	
IR-2	0.15	± 10	38	25.0	600.0	0.10	1200	
IR-2	0.18	± 10	35	25.0	550.0	0.12	1105	
IR-2	0.22	± 10	33	25.0	510.0	0.14	1025	
IR-2	0.27	± 10	33	25.0	430.0	0.16	960	
IR-2	0.33	± 10	30	25.0	410.0	0.22	815	
IR-2	0.39	± 10	30	25.0	365.0	0.30	700	
IR-2	0.47	± 10	30	25.0	330.0	0.35	650	
IR-2	0.56	± 10	30	25.0	300.0	0.50	545	
IR-2	0.68	± 10	28	25.0	275.0	0.60	495	
IR-2	0.82	± 10	28	25.0	250.0	0.85	415	
IR-2	1.0	± 10	25	25.0	230.0	1.00	385	
IR-2	1.2	± 10	25	7.9	150.0	0.18	590	IRON CORE
IR-2	1.5	± 10	28	7.9	140.0	0.22	535	
IR-2	1.8	± 10	30	7.9	125.0	0.30	455	
IR-2	2.2	± 10	30	7.9	115.0	0.40	395	
IR-2	2.7	± 10	37	7.9	100.0	0.55	355	
IR-2	3.3	± 10	45	7.9	90.0	0.85	270	
IR-2	3.9	± 10	45	7.9	80.0	1.0	250	
IR-2	4.7	± 10	45	7.9	75.0	1.2	230	
IR-2	5.6	± 10	50	7.9	65.0	1.8	185	
IR-2	6.8	± 10	50	7.9	60.0	2.0	175	
IR-2	8.2	± 10	55	7.9	55.0	2.7	155	
IR-2	10.0	± 10	55	7.9	50.0	3.7	130	
IR-2	12.0	± 10	45	2.5	40.0	2.7	155	
IR-2	15.0	± 10	40	2.5	35.0	2.8	150	
IR-2	18.0	± 10	50	2.5	30.0	3.1	145	
IR-2	22.0	± 10	50	2.5	25.0	3.3	140	
IR-2	27.0	± 10	50	2.5	20.0	3.5	135	
IR-2	33.0	± 10	45	2.5	24.0	3.4	130	FERRITE CORE
IR-2	39.0	± 10	45	2.5	22.0	3.6	125	
IR-2	47.0	± 10	45	2.5	20.0	4.5	110	
IR-2	56.0	± 10	45	2.5	18.0	5.7	100	
IR-2	68.0	± 10	50	2.5	15.0	6.7	92	
IR-2	82.0	± 10	50	2.5	14.0	7.3	88	
IR-2	100.0	± 10	50	2.5	13.0	8.0	84	
IR-2	120.0	± 10	30	0.79	12.0	13.0	66	
IR-2	150.0	± 10	30	0.79	11.0	15.0	61	
IR-2	180.0	± 10	30	0.79	10.0	17.0	57	
IR-2	220.0	± 10	30	0.79	9.0	21.0	52	
IR-2	270.0	± 10	30	0.79	8.0	25.0	47	
IR-2	330.0	± 10	30	0.79	7.0	28.0	45	
IR-2	390.0	± 10	30	0.79	6.5	35.0	40	
IR-2	470.0	± 10	30	0.79	6.0	42.0	36	
IR-2	560.0	± 10	30	0.79	5.0	46.0	35	
IR-2	680.0	± 10	30	0.79	4.0	60.0	30	
IR-2	820.0	± 10	30	0.79	3.8	65.0	29	
IR-2	1000.0	± 10	30	0.79	3.4	72.0	28	
IR-4	0.15	± 20	50	25.0	525.0	0.03	2450	PHENOLIC CORE
IR-4	0.22	± 20	50	25.0	450.0	0.055	1810	
IR-4	0.33	± 20	45	25.0	360.0	0.09	1400	
IR-4	0.47	± 20	45	25.0	310.0	0.12	1225	
IR-4	0.56	± 10	50	25.0	280.0	0.135	1150	
IR-4	0.68	± 10	50	25.0	250.0	0.15	1100	
IR-4	0.82	± 10	50	25.0	220.0	0.22	900	
IR-4	1.0	± 10	50	25.0	200.0	0.29	785	
IR-4	1.2	± 10	33	7.9	180.0	0.42	650	
IR-4	1.5	± 10	33	7.9	160.0	0.50	600	
IR-4	1.8	± 10	33	7.9	150.0	0.65	525	
IR-4	2.2	± 10	33	7.9	135.0	0.95	435	
IR-4	2.7	± 10	33	7.9	120.0	1.20	385	
IR-4	3.3	± 10	33	7.9	110.0	2.00	300	
IR-4	3.9	± 10	33	7.9	100.0	2.30	280	
IR-4	4.7	± 10	33	7.9	90.0	2.60	260	

Notes⁽¹⁾ Measured with full length lead⁽²⁾ Rated DC current based on maximum temperature rise as shown in table

STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY L AND Q (MHz)	SRF MIN. (MHz) ⁽¹⁾	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽²⁾	
IR-4	5.6	± 10	45	7.9	60.0	32.0	495	IRON CORE
IR-4	6.8	± 10	50	7.9	55.0	0.50	395	
IR-4	8.2	± 10	50	7.9	50.0	0.60	360	
IR-4	10.0	± 10	55	7.9	45.0	0.90	290	
IR-4	12.0	± 10	65	2.5	42.0	1.10	265	
IR-4	15.0	± 10	65	2.5	40.0	1.40	240	
IR-4	18.0	± 10	75	2.5	34.0	2.25	185	
IR-4	22.0	± 10	75	2.5	30.0	2.50	175	
IR-4	27.0	± 10	60	2.5	25.0	2.60	170	
IR-4	33.0	± 10	65	2.5	19.0	3.0	165	
IR-4	36.0	± 5	60	2.5	15.5	2.50	180	
IR-4	39.0	± 5	60	2.5	14.5	2.60	176	
IR-4	43.0	± 5	60	2.5	13.7	2.70	172	
IR-4	47.0	± 5	55	2.5	13.0	2.75	170	
IR-4	51.0	± 5	55	2.5	12.7	2.85	167	
IR-4	56.0	± 5	55	2.5	12.0	3.0	164	
IR-4	62.0	± 5	55	2.5	11.5	3.15	160	
IR-4	68.0	± 5	55	2.5	11.0	3.30	156	
IR-4	75.0	± 5	55	2.5	10.5	3.70	147	
IR-4	82.0	± 5	50	2.5	10.3	3.90	143	
IR-4	91.0	± 5	50	2.5	10.0	4.30	136	
IR-4	100.0	± 5	50	2.5	9.5	4.50	133	
IR-4	110.0	± 5	60	0.79	8.9	4.90	128	
IR-4	120.0	± 5	65	0.79	8.7	5.20	124	
IR-4	130.0	± 5	65	0.79	8.5	5.45	121	
IR-4	150.0	± 5	65	0.79	8.0	6.05	114	
IR-4	160.0	± 5	65	0.79	7.5	6.40	111	
IR-4	180.0	± 5	65	0.79	7.0	6.75	108	
IR-4	200.0	± 5	65	0.79	6.5	7.10	106	
IR-4	220.0	± 5	65	0.79	6.2	7.45	103	
IR-4	240.0	± 5	65	0.79	5.9	7.80	101	
IR-4	270.0	± 5	65	0.79	5.7	11.0	129	
IR-4	300.0	± 5	65	0.79	5.4	11.5	125	
IR-4	330.0	± 5	65	0.79	5.1	12.0	123	
IR-4	360.0	± 5	65	0.79	4.8	15.5	108	
IR-4	390.0	± 5	65	0.79	4.5	16.3	105	
IR-4	430.0	± 5	65	0.79	4.2	17.1	102	
IR-4	470.0	± 5	65	0.79	3.9	17.9	100	
IR-4	510.0	± 5	65	0.79	3.7	18.8	98	
IR-4	560.0	± 5	65	0.79	3.5	24.7	85	
IR-4	620.0	± 5	65	0.79	3.3	25.9	83	
IR-4	680.0	± 5	55	0.79	3.1	27.2	81	
IR-4	750.0	± 5	55	0.79	2.9	28.6	79	
IR-4	820.0	± 5	55	0.79	2.7	30.0	77	
IR-4	910.0	± 5	55	0.79	2.5	31.5	76	
IR-4	1000.0	± 5	55	0.79	2.3	33.1	74	
IR-4	1100.0	± 5	30	0.25	2.1	43.5	64	
IR-4	1200.0	± 5	30	0.25	2.0	45.7	63	
IR-4	1300.0	± 5	30	0.25	1.9	49.0	61	
IR-4	1500.0	± 5	30	0.25	1.8	52.5	59	
IR-4	1600.0	± 5	30	0.25	1.7	54.0	58	
IR-4	1800.0	± 5	30	0.25	1.6	56.7	56	

Notes

(1) Measured with full length lead

(2) Rated DC current based on maximum temperature rise as shown in table

ORDERING INFORMATION

IR-2	10 μ H	$\pm 10\%$	ER	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I	R	0	2	E	R	1	0	0	K
MODEL				PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.