

Cable Clips


Self Adhesive Aluminium

PRO-POWER
Quality Cables


Self-Adhesive Coated Aluminium General Purpose Hook

Features:

- White gloss polyester coating.
- Self-adhesive foam pad.
- Operating temperature -10°C to +65°C.



ACC07



Dimensions : Millimetres

Specifications

Bundle Diameter	Base Size	Quantity per Pack	Part Number
17	25.4 x 25.4	100	ACC07

Dimensions : Millimetres

PRO-POWER
Quality Cables

Cable Clips

Self Adhesive Aluminium

PRO-POWER
Quality Cables


Self-Adhesive Aluminium Buckle

Features:

- Easily formed buckle.
- Self-adhesive foam pad.
- Available in two sizes.
- Operating temperature -40°C to +70°C.




ACC05



Dimensions : Millimetres

Maximum Bundle Diameter 13mm

ACC06



Dimensions : Millimetres

Maximum Bundle Diameter 19mm

Specifications

Bundle Diameter	Base Size	Quantity per Pack	Part Number
13	11.5 x 25.4	250	ACC05
19	16.3 x 25.4		ACC06

Dimensions : Millimetres

PRO-POWER
Quality Cables

Cable Clips

Self Adhesive Aluminium

PRO-POWER
Quality Cables


Self-Adhesive Aluminium Clips for Ribbon Cable



Features:

- Fast, easy installation.
- Self-adhesive foam pad.
- Wide range of sizes.
- Operating temperature -40°C to +70°C.

Adhesive Clips For Ribbon Cables



Specifications

Conductors	Ribbon Width	Quantity per Pack	Part Number
10	12.7	100	ACC10
20	25.4		ACC20
26	33.1		ACC26
34	43.3		ACC34
40	50.8		ACC40
50	63.5		ACC50

Dimensions : Millimetres


PRO-POWER
Quality Cables

Cable Clips

Self Adhesive Aluminium

PRO-POWER
Quality Cables

Self-Adhesive Aluminium



Features:

- Self-adhesive cable clips, manufactured in malleable aluminium.
- To fix, remove adhesive backing and position. Insert cable harness and bend over tabs.
- Available in 2 sizes.
- Operating temperature -40°C to +70°C.


General Description:

These patent adhesive aluminium cable clips are a quick, easy to apply and inexpensive method of fixing round, or flat ribbon cables without damage, to clean dry surfaces.

ACC 01 and 02 are suitable for a bundle diameter of upto 6.3mm and 10mm respectively.

ACC 01


Maximum
Bundle
Diameter
6.3mm



Dimensions in mm

ACC 02

Maximum
Bundle
Diameter
10mm



Dimensions in mm

Specifications

Bundle Diameter	Base Size	Quantity per Pack	Part Number
2 - 6.3	11 x 16	250	ACC01
4 - 10	16 x 19		ACC02

Dimensions : Millimetres

PRO-POWER
Quality Cables

Cable Clips

Self Adhesive Aluminium

PRO-POWER
Quality Cables

Notes:

International Sales Offices:

	AUSTRALIA – Farnell InOne Tel No: ++ 61 2 9645 8888 Fax No: ++ 61 2 9644 7898		FINLAND – Farnell InOne Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		NETHERLANDS – Farnell InOne Tel No: ++ 31 30 241 7373 Fax No: ++ 31 30 241 7333		SWITZERLAND – Farnell InOne Tel No: ++ 41 1 204 64 64 Fax No: ++ 41 1 204 64 54
	AUSTRIA – Farnell InOne Tel No: ++ 43 662 2180 680 Fax No: ++ 43 662 2180 670		FRANCE – Farnell InOne Tel No: ++ 33 474 68 99 99 Fax No: ++ 33 474 68 99 90		NEW ZEALAND – Farnell InOne Tel No: ++ 64 9 357 0646 Fax No: ++ 64 9 357 0656		UK – Farnell InOne Tel No: ++ 44 8701 200 200 Fax No: ++ 44 8701 200 201
	BELGIUM – Farnell InOne Tel No: ++ 32 3 475 2810 Fax No: ++ 32 3 227 3648		GERMANY – Farnell InOne Tel No: ++ 49 89 61 39 39 39 Fax No: ++ 49 89 613 59 01		NORWAY – Farnell InOne Tel No: ++ 45 44 53 66 66 Fax No: ++ 45 44 53 66 02		UK – BuckHickman InOne ++ 44 8450 510 150 ++ 44 8450 510 130
	BRAZIL – Farnell-Newark InOne Tel No: ++ 55 11 4066 9400 Fax No: ++ 55 11 4066 9410		HONG KONG – Farnell-Newark InOne Tel No: ++ 852 2268 9888 Fax No: ++ 852 2268 9899		PORTUGAL – Farnell InOne Tel No: ++ 34 93 475 8804 Fax No: ++ 34 93 474 5288		UK – CPC ++ 44 8701 202 530 ++ 44 8701 202 531
	CHINA – Farnell-Newark InOne Tel No: ++86 10 6238 5152 Fax No: ++86 10 6238 5022		IRELAND – Farnell InOne Tel No: ++ 353 1 830 9277 Fax No: ++ 353 1 830 9016		SINGAPORE – Farnell-Newark InOne Tel No: ++ 65 6788 0200 Fax No: ++ 65 6788 0300	 EXPORT – Farnell InOne Tel No: ++ 44 8701 200 208 Fax No: ++ 44 8701 200 209 For enquiries from all other markets	
	DENMARK – Farnell InOne Tel No: ++ 45 44 53 66 44 Fax No: ++ 45 44 53 66 06		ITALY – Farnell InOne Tel No: ++ 39 02 93 995 200 Fax No: ++ 39 02 93 995 300		SPAIN – Farnell InOne Tel No: ++ 34 93 475 8805 Fax No: ++ 34 93 474 5107		
	ESTONIA – Farnell InOne Tel No: ++ 358 9 560 7780 Fax No: ++ 358 9 345 5411		MALAYSIA – Farnell-Newark InOne Tel No: ++ 60 3 7873 8000 Fax No: ++ 60 3 7873 7000		SWEDEN – Farnell InOne Tel No: ++ 46 8 730 50 00 Fax No: ++ 46 8 83 52 62		

<http://www.farnellinone.com>

<http://www.buckhickmaninone.com>

<http://www.cpc.co.uk>

Disclaimer This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-Power is the registered trademark of the Group. © Premier Farnell plc 2004.

PRO-POWER
Quality Cables