




REV	DESCRIPTION	DATE
-----	-------------	------

NOTE :

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	22	20	18	16
AMP.	3	4	7	10
2. MAXIMUM ELECTRICAL RATING : 300 VOLTS MAX.
3. SHRINK TEMP. : 150°C
4. OPERATING TEMP. : -10°C~+105°C
5. INSULATION MATERIAL : NYLON & HIGH DENSITY PE.
6. INSULATED COLOR : RED
7. WIRE RANGE : 22-16 A.W.G. (0.5-1.5 mm²)
8. TERMINAL MATERIAL : BRASS
9. TERMINAL SURFACE TREATMENT : TIN PLATED
10. TERMINAL THICKNESS : 0.80 mm
11. NEMA TAB : 0.032 * 0.250 (0.8 * 6.35)

Tolerance Unless Otherwise Specified	
0 > 6 mm ± 0.20	ANGLE
6 > 18 mm ± 0.30	0° > ° REF ±
18 > 30 mm ± 0.40	° > ° ±
30 > 75 mm ± 0.50	° > ° ±

NAME	HEAT SHRINKABLE-FULLY NYLON "H"(SINGLE CRIMP TYPE)	MALE DISCONNECTORS	UNIT	1/1
PART NO.	MDFNYH1-250	MATERIAL	-----	APPROVE
NUMBER	KA-94683-C	SCALE	SHEET	PAGE
DATE	2005/12/30	3/1	1-0	10F1
			DRAWN	柯明發

KST. K.S. TERMINALS INC.