





- 1 CONTINUOUS STRIP ON REELS.
- 2 (1) 0.8mm²[#18] AWG - 2.84 [.112] AND
(1) 1.3mm²[#16] AWG - 3.12 [.123] MAX DIA.
- 3 0.003302 [.000130] MAX PRE-TIN PLATE.
- 4 SPECIAL LUBRICANT.
- 5 PRELIMINARY - NOT FOR PRODUCTION.
- 6 NICKEL PLATED.
- 7 PRODUCT SPECIFICATION DOES NOT APPLY TO PART NUMBER 770642-3



6	4	2	0.5 -2.0mm [20-14] AWG	770642-3
3	4	2	0.5 -2.0mm ² [20-14] AWG	5 770642-2
3	-	2	0.5 -2.0mm ² [20-14] AWG	770642-1
FINISH	LUBRICANT	INSULATION RANGE	WIRE RANGE	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER CHK DONALD F. DECKER APVD DONALD F. DECKER	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-1271 APPLICATION SPEC 114-49003	NAME TERMINAL, TIMER CONNECTOR -	
MATERIAL H06 BRASS	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1	REV H3