


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	LABELS SIZE inches [mm]	"A"	"B"	LABELS PER ROW	LABELS PER PKG.
N050X075CBT	GMC	0.500 [12.7] X 0.750 [19.1]	0.750 [19.1]	0.850 [21.6]	7	10000
N050X100CBT	GMC	0.500 [12.7] X 1.000 [25.4]	1.000 [25.4]	1.100 [27.9]	7	10000

Diagram illustrating the label tape layout and dimensions:

- Overall width: 4.15 [105.41]
- Label width: .575 [14.60] TYP. 6 PLCS.
- Label width: .500 [12.70] TYP. 7 PLCS.
- Dimensions "A" and "B" are indicated for the label size and spacing.

NOTES:
 1. SEE MFG. DRAWING NO. A61261.
 2. MILLIMETER ARE IN [].



										CAD FILENAME/LAYERS		100472JV_C10298_N050XNUMCBT_00.PR	
										PANDUIT			
										CORP. TINLEY PARK, ILLINOIS			
										OPTIMUM N050X***CBT			
										THERMAL TRANSFER LABELS			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN	
										(X) ± .031 (XXX) ± .005		IN INCHES, THIRD ANGLE PROJECTION.	
										(XX) ± .015 ANGLES ±			
										DRAWN BY	MAT'L:		SCALE
										RVU	SEE TABLE		NTS
0	10-1-04	RVU		DRAWING RELEASED.			0000	R	DATE	DRAWING NO.			DWG
REV	DATE	BY	CHK	DESCRIPTION			ECN	- R	CUST	SUP			SIZE
										10-1-04		C10298	A
										CHK'D			

O	10-1-04	RVU		DRAWING RELEASED.	0000	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	