

Features

- Operating voltage: 2.7V~5.5V
- Low power consumption
 - Operation: 25mA max. ($V_{CC}=5V$)
10mA max. ($V_{CC}=3V$)
 - Standby: 30 μ A max. ($V_{CC}=5V$)
10 μ A max. ($V_{CC}=3V$)
- Access time: 150ns max. ($V_{CC}=5V$)
250ns max. ($V_{CC}=3V$)
- 16384×8-bit of mask ROM
- Mask options: chip enable $\overline{CE}/\overline{OE2}/\overline{OE2}$ and output enable $\overline{OE}/\overline{OE}/\overline{NC}$ and $\overline{OE1}/\overline{OE1}/\overline{NC}$
- TTL compatible inputs and outputs
- Tristate outputs
- Fully static operation
- 28-pin DIP/SOP package


General Description


The HT23C128 is a read-only memory with high performance CMOS storage device whose 128K of memory is arranged into 16384 words by 8 bits.

For application flexibility, the chip enable and output enable control pins can be selected as active high or active low. This flexibility not only allows easy interface with most microproces-

sors, but also eliminates bus contention in multiple bus microprocessor systems. An additional feature of the HT23C128 is its ability to enter the standby mode whenever the chip enable ($\overline{CE}/\overline{OE}$) is inactive, thus reducing current consumption to below 30 μ A. The combination of these functions makes the chip suitable for high density low power memory applications.

Block Diagram



Pin Assignment

Pin Description

Pin Name	I/O	Description
NC	—	No connection
A0~A13	I	Address inputs
D0~D7	O	Data outputs
VSS	I	Negative power supply
CE/ $\overline{\text{CE}}$ /OE2/ $\overline{\text{OE2}}$	I	Chip enable/Output enable input
OE/ $\overline{\text{OE}}$ /NC	I	Output enable input
OE1/ $\overline{\text{OE1}}$ /NC	I	Output enable input
VCC	I	Positive power supply

Absolute Maximum Ratings

Supply Voltage.....-0.3V to 6V Storage Temperature-50°C to 125°C
 Input Voltage-0.3V to $V_{CC}+0.3V$ Operating Temperature-40°C to 85°C

Note: These are stress ratings only. Stresses exceeding the range specified under "Absolute Maximum Ratings" may cause substantial damage to the device. Functional operation of this device at other conditions beyond those listed in the specification is not implied and prolonged exposure to extreme conditions may affect device reliability.

D.C. Characteristics
Supply voltage: 2.7V~3.6V

Ta=-40°C to 85°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{CC}	Conditions				
V _{CC}	Operating Voltage	—	—	2.7	—	3.6	V
I _{CC}	Operating Current	3V	O/P Unload, f=5MHz	—	—	10	mA
V _{IL}	Input Low Voltage	3V	—	V _{SS}	—	0.4	V
V _{IH}	Input High Voltage	3V	—	2.0	—	V _{CC}	V
V _{OL}	Output Low Voltage	3V	I _{OL} =2.1mA	—	—	0.4	V
V _{OH}	Output High Voltage	3V	I _{OH} =-0.4mA	2.4	—	V _{CC}	V
I _{LI}	Input Leakage Current	3V	V _{IN} =0 to V _{CC}	—	—	10	μA
I _{LO}	Output Leakage Current	3V	V _{OUT} =0 to V _{CC}	—	—	10	μA
I _{STB1}	Standby Current	3V	$\frac{CE}{CE} = \frac{V_{IL}}{V_{IH}}$	—	—	500	μA
I _{STB2}	Standby Current	3V	$\frac{CE}{CE} \leq 0.2V$ $\frac{CE}{CE} \geq V_{CC}-0.2V$	—	—	10	μA
C _{IN}	Input Capacitance (See Note)	—	f=1MHz	—	—	10	pF
C _{OUT}	Output Capacitance (See Note)	—	f=1MHz	—	—	10	pF

Note: These parameters are periodically sampled but not 100% tested.

Supply voltage: 4.5V~5.5V

Ta= 40 °C to 85°C

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{CC}	Conditions				
V _{CC}	Operating Voltage	—	—	4.5	—	5.5	V
I _{CC}	Operating Current	5V	O/P Unload, f=5MHz	—	—	25	mA
V _{IL}	Input Low Voltage	5V	—	V _{SS}	—	0.8	V
V _{IH}	Input High Voltage	5V	—	2.2	—	V _{CC}	V
V _{OL}	Output Low Voltage	5V	I _{OL} =3.2mA	—	—	0.4	V
V _{OH}	Output High Voltage	5V	I _{OH} =-1mA	2.4	—	V _{CC}	V
I _{LI}	Input Leakage Current	5V	V _{IN} =0 to V _{CC}	—	—	10	μA
I _{LO}	Output Leakage Current	5V	V _{OUT} =0 to V _{CC}	—	—	10	μA

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
		V _{CC}	Conditions				
I _{STB1}	Standby Current	5V	$\frac{CE=V_{IL}}{CE=V_{IH}}$	—	—	1.5	mA
I _{STB2}	Standby Current	5V	$\frac{CE \leq 0.2V}{CE \geq V_{CC}-0.2V}$	—	—	30	μA
C _{IN}	Input Capacitance (See Note)	—	f=1MHz	—	—	10	pF
C _{OUT}	Output Capacitance (See Note)	—	f=1MHz	—	—	10	pF

Note: These parameters are periodically sampled but not 100% tested.

A.C. Characteristics

T_a=-40°C to 85°C

Symbol	Parameter	V _{CC} =2.7V~3.6V		V _{CC} =4.5V~5.5V		Unit
		Min.	Max.	Min.	Max.	
t _{CYC}	Cycle Time	250	—	150	—	ns
t _{AA}	Address Access Time	—	250	—	150	ns
t _{ACE}	Chip Enable Access Time	—	250	—	150	ns
t _{AOE}	Output Enable Access Time	—	150	—	80	ns
t _{OH}	Output Hold Time	—	—	10	—	ns
t _{OD}	Output Disable Time (See Note)	—	—	—	70	ns
t _{OE}	Output Enable Time (See Note)	—	—	10	—	ns

Note: These parameters are periodically sampled but not 100% tested.


A.C. test conditions

Output load: see figure right

Input rise and fall time: 10ns

Input pulse levels: 0.4V to 2.4V

Input and output timing reference levels:
0.8V and 2.0V (V_{CC}=5V), 1.5V (V_{CC}=3V)



* Including scope and jig

Output load circuit

Functional Description

The HT23C128 has two modes, namely data read mode and standby mode, controlled by $\overline{CE}/\overline{CE2}/\overline{OE2}$, $\overline{OE}/\overline{OE1}/\overline{NC}$ and $\overline{OE1}/\overline{OE1}/\overline{NC}$ inputs.

• Standby mode

The HT23C128 has lower current consumption, controlled by the chip enable input ($\overline{CE}/\overline{CE}$). When a low/high level is applied to the $\overline{CE}/\overline{CEB}$ input regardless of the output enable ($\overline{OE}/\overline{OE1}/\overline{NC}$ and $\overline{OE1}/\overline{OE1}/\overline{NC}$) states, the chip will enter the standby mode.

• Data read mode

When both the chip enable ($\overline{CE}/\overline{CE2}/\overline{OE2}$) and the output enable ($\overline{OE}/\overline{OE1}/\overline{NC}$ and $\overline{OE1}/\overline{OE1}/\overline{NC}$) are active, the chip is in data read mode. Otherwise, active $\overline{CE}/\overline{CE}$ and inactive $\overline{OE}/\overline{OE1}/\overline{NC}$ or $\overline{OE1}/\overline{OE1}/\overline{NC}$ result in deselect mode. The output will remain in Hi-Z state.


Operation Truth Table

Mode	$\overline{CE}/\overline{CE}$	$\overline{OE}/\overline{OE}$	$\overline{OE1}/\overline{OE1}$	A0~A13	D0~D7
Read	H/L	H/L	H/L	Valid	Data Out
Deselect	H/L	L/H	X	X	High Z
Deselect	H/L	X	L/H	X	High Z
Standby	L/H	X	X	X	High Z


Note: H= V_{IH} , L= V_{IL} , X= V_{IH} or V_{IL}

Timing Diagrams







- Propagation delay due to address ($\overline{CE}/\overline{CE2}/\overline{OE2}$, $\overline{OE}/\overline{OE}$ and $\overline{OE1}/\overline{OE1}$ are active)







- Propagation delay due to chip enable and output enable (address valid)



Characteristic Curves





HT23C128 MASK ROM ORDERING SHEET

Custom: _____

Input Medium:

EPROM DISK File (Mail Address: romfile@holtek.com.tw) OTHER _____

User No.	Type/Ref. Name	Q'ty	Check Sum	Memory Address	
				Start	End

Control Pin and Package Form Option:

(a) 28 Pin Type Pin 20: _____ (1) CE (2) CE (3) OE2 (4) OE2
 Pin 22: _____ (1) OE (2) OE (3) NC
 Pin 27: _____ (1) OE1 (2) OE1 (3) NC
 (b) Package Form: _____ (1) Chip Form (2) 28 DIP (3) 28 SOP

Companion User No. _____

Package Marking : _____

Delivery Date : _____ Q'ty: _____

CUSTOM CONFIRMED BY:

 (NAME, DATE, POSITION & CO. CHOP)

HOLTEK CONFIRMED BY:

 (SALES)

 (SALES MANAGER)

Holtek Semiconductor Inc. (Headquarters)

No.3, Creation Rd. II, Science-based Industrial Park, Hsinchu, Taiwan, R.O.C.
Tel: 886-3-563-1999
Fax: 886-3-563-1189

Holtek Semiconductor Inc. (Taipei Office)

11F, No.576, Sec.7 Chung Hsiao E. Rd., Taipei, Taiwan, R.O.C.
Tel: 886-2-2782-9635
Fax: 886-2-2782-9636
Fax: 886-2-2782-7128 (International sales hotline)

Holtek Semiconductor (Hong Kong) Ltd.

RM.711, Tower 2, Cheung Sha Wan Plaza, 833 Cheung Sha Wan Rd., Kowloon, Hong Kong
Tel: 852-2-745-8288
Fax: 852-2-742-8657

Holtek Semiconductor (Shanghai) Ltd.

7th Floor, Building 2, No.889, Yi Shan Rd., Shanghai, China
Tel: 021-6485-5560
Fax: 021-6485-0313

Holmate Technology Corp.

48531 Warm Springs Boulevard, Suite 413, Fremont, CA 94539
Tel: 510-252-9880
Fax: 510-252-9885

Copyright © 2000 by HOLTEK SEMICONDUCTOR INC.

The information appearing in this Data Sheet is believed to be accurate at the time of publication. However, Holtek assumes no responsibility arising from the use of the specifications described. The applications mentioned herein are used solely for the purpose of illustration and Holtek makes no warranty or representation that such applications will be suitable without further modification, nor recommends the use of its products for application that may present a risk to human life due to malfunction or otherwise. Holtek reserves the right to alter its products without prior notification. For the most up-to-date information, please visit our web site at <http://www.holtek.com.tw>.