

046001.5 - 460 Series



Series: 460

 Fuse 460 PICO SMF Datasheet

The 460 Series Slo-Blo® SMF is based on Littelfuse PICO® fuse through-hole technology, though offered in a surface mount package.

This series of devices meets the requirements of the RoHS directive.

Features:

- Slow-Blow
- High inrush current withstand capability
- Wide current rating range: 0.375A to 5A
- Wide operating temperature range
- RoHS compliant

Applications:

- Wireless basestation
- Network equipment
- Telecom equipment

Questions? [Contact Littelfuse Support](#)

 Check Stock

 Order Samples



NEW!
Product
Selection
Guide
eCatalog
[Read Now](#)



Electronics
News and Information
[SIGN UP NOW](#)

Feedback

Electrical Characteristics	Technical Resources	Environmental Info
Property (Mouseover for details)	Value	
Ampere Rating (A)	1.5	
Body	Glass Body	
Nominal Melting I²t (A²sec)	3.94	
Interrupting Rating	50A@125VDC	
Moisture Sensitivity Level	MIL-STD-202 Method 106 High Humidity (90-98 RH) Heat (65&).	
Min Operating Temp °C	-55	
Max Operating Temp (°C)	125	
Nominal Voltage Drop (mV)	0.208	
Nominal Cold Resistance (Ohms)	0.1151	
Opening	Slo-Blo/Time Lag (T)/Time Delay	
Package Size	7.24 x 4.32mm	
VAC (V)	125	
VDC (V)	125	

Connect with Littelfuse

Sign up to receive special offers and news

Submit

For more details about how we use your information, check our [Privacy Statement](#).



 Mobile Site

About Littelfuse

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

Explore Littelfuse

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

Technical Resources

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents

