D Series



-.14[3,6]

that

12 Volt Input Dc to Ac Inverter

D12LD60J

The D12LD60J is a generic dc to ac inverter designed to generate 6 mArms into a 500 - 700 volt load (CCFL) from a nominal 12 Vdc source. It can be easily dimmed using an external analog control signal.

1.03 [26,2]

FEATURES

Low Profile Display compatible connector High efficiency

PHYSICAL SPECIFICATIONS

6.15" x 1.03" x .32" Size:

(without input connector) (156,2mm x 26,2mm x 8mm)

Weight: 26 grams

Component Surface Temperature: -20° to +80°C Storage Temperature: -20° to +85°C Humidity: 95% RH Max

Characteristics	Value	Units	Note(s)
Input Voltage	10.8 - 12.6	Vdc	
Input Current	0.8 typ	Adc	R _L = 100 kOhms
Minimum No Load Output Voltage	1500	Vrms	Vin = 12.00 Vdc
Frequency	37 typ	kHz	Vin = 12.00 Vdc
Output Current	6.0	mArms	R _L = 100 kOhms
Efficiency	75	%	Typical

The maximum input current (which indicates an overload condition) is 1.0 Adc maximum.

Input Connector: J2 Molex 53261-0871

Output Connector: J1,J3 JST SM02(8.0)B-BHS-1-TB

product may differ from 6.15 [156,2] Actual MAX 5.850 S [148,59] only. reference for components are shown J3 .12 [3,0] .14 [3,6] --

Dia. (2x)

Inverters specifically designed to match most popular LCD modules are also available. Contact your authorized distributor or ERG direct.

Endicott Research Group, Inc. 2601 Wayne St., Endicott, NY 13760 607-754-9187 Fax 607-754-9255 http://www.ergpower.com

Pin Descriptions						
J2-1	+Vin					
J2-2	+Vin	J1-1 ACout				
J2-3	GND	J1-2 ACreturn				
J2-4	GND					
J2-5	Enable					
J2-6	Control	J3-1 ACout				
J2-7	N/C	J3-2 ACreturn				
J2-8	N/C					

 $\oplus \Box$





12 Volt Input Dc to Ac Inverter

D12LD60J

Absolute Maximum Ratings

Rating	Symbol	Value	Units	
Input Voltage Range	V _{in}	-0.3 to +13.2	Vdc	
Storage Temperature	T stg	-40 to +85	°C	

Operating Characteristics

With a resistive load simulating the referenced display and lamp warm-up of 5 minutes. Unless otherwise noted Vin = 12.00 Volts dc and Ta = 25° C.

Characteristic	Symbol	Min	Тур	Max	Units	
Input Voltage	V in	+10.8	+12.0	+12.6	Vdc	
Component Surface Temperature (note 1)	Ts	-20	-	+80	°C	
Input Current (note 2)	I in	-	0.8	-	Adc	
Input Ripple Current	I _{rip}	-	20	-	mA _{pk-pk}	
Operating Frequency	F _o	32	37	42	kHz	
Minimum Output Voltage (note 3)	V _{out} (min)	1500	-	-	Vrms	
Efficiency	η	-	75	-	%	
Output Current (per lamp)	I _{out}	-	6.0	-	mArms	
Output Voltage	V _{out}	-	600	-	Vrms	
Enable Pin						
Turn-off Threshold	V _{thoff}	GND	-	0.5	Vdc	
Turn-on Threshold	V _{thon}	2.5	-	Vin	Vdc	
Impedance to Vin	R _{Enable}	-	10	-	kOhms	

Specifications subject to change without notice.

- (Note 1) Surface temperature must not exceed 80 degrees C; thermal management actions may be required.
- (Note 2) Input current in excess of maximum may indicate a load/inverter mismatch condition, which can result in reduced reliability. Please contact ERG technical support.
- (Note 3) Provided data is not tested but guaranteed by design.

Application Notes:

- 1) The minimum distance from high voltage areas of the inverter to any conductive material should be .12 inches per kilovolt of starting voltage.
- 2) Mounting hardware to be non-conductive.
- 3) Open framed inverters should not be used in applications at altitudes over 10,000 feet.
- 4) ACreturn should be left floating, not grounded.
- 5) Contact ERG for possible exceptions.





12 Volt Input Dc to Ac Inverter

D12LD60J

Onboard PWM

Unless otherwise noted Vin = 12.00 Volts DC, T_a = 25 °C and unit has been running for 5 minutes.

Characteristic	Symbol	Min	Тур	Max	Units
Frequency	f pwm	-	160	-	Hz
Control Input Bias Current	I cbias	-	-	10	uA

Pin Descriptions

Vin Input voltage to the inverter. The two pins should be connected for optimum reliability and efficiency.

GND Inverter ground. The two pins should be connected for optimum reliability and efficiency.

Control Analog voltage input to the onboard pulse width modulator. Increasing this voltage increases the OFF

time of the onboard PWM resulting in decreased brightness. The inverter is full ON when this voltage is

near inverter ground.

Enable Inverter Enable. Pull this pin low to disable inverter operation. This pin must be high to enable the

inverter. The onboard PWM is always utilized.


Application information

The LD series of inverters is designed to power up to two cold cathode fluorescent lamps with a combined power of twelve watts. An external analog control interfaces with an onboard pulse width modulator to provide dimming control. The LD inverter can reliably dim to less than 5% duty cycle.


External shutdown of the inverter is accomplished using the Enable pin. Pulling this pin low (below Vthoff) disables the inverter. Enabling the inverter is accomplished by pulling this pin high (above Vthon).

If analog voltage dimming is required, the analog voltage is applied to the Control pin. Figure 1 shows how to connect the inverter for onboard PWM operation. Graph 1 shows the relationship of PWM duty cycle to input control voltage.

If an external PWM is used, simply connect the Enable pin to the PWM source and connect the Control pin to inverter GROUND. If the onboard PWM is used, connect the analog voltage to the Control pin.



Graph 1





Endicott Research Group, Inc. 2601 Wayne St., Endicott, NY 13760 607-754-9187 Fax 607-754-9255 http://www.ergpower.com Specifications are subject to change without notice.

