




PRODUCT NO.	DIM "A"	PCB THICKNESS
62525-101	2.8	1.6mm
-101LF		
62525-102	3.8	2.4mm
-102LF		
62525-103	4.5	3.2mm
-103LF		



- NOTES
- MATERIAL : CONTACT AREA BeCu
 SPRING CLIP BeCu
 INSULATOTR PTFE
 OTHERS BRASS
 - PLATING : CONTACT AREA Au 0.8um MIN. UNDER Ni 1.27um MIN.
 SPRING CLIP Ni 1.27um MIN.
 BODY Ni 1.27um MIN.
 INSERT CAP Ni 1.27um MIN.
 OTHERS Au FLASH UNDER Ni 1.27um MIN.
 - FOR LEAD FREE P/N, THE PRODUCT MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code					surface	tolerance	projection	product family	CODE
---					ISO 1302	ISO 406	ISO 1101	METRAL	JP
ltr	description	ecn no	dr	date	tolerances unless otherwise specified			title METRAL MINI COAX RECE. R/A ASS'Y	
A	RELEASED	J90148	Y.K	5/10/'99	angles	linear			
B	REVISED	J90200	Y.K	6/7/'99					
C	REVISED	J20641	Y.K	12/16/'02	0°±2'				
D	REVISED	J05-0673	Y.K	10/21/'05	dr	Y.KODAIRA	5/10/'99	dwg no	sheet 1 of 1
E	REVISED	J07-0030	S.D	1/18/'07	engr	S.OKUDAIRA	1/18/'07	62525	A3
					chr	R. S. S. S. S.	1/18/'07	type Customer Drawing	
					appd	S. S. S. S. S.	1/18/'07		
sheet index	revision sheet	E						Rev. E	
		1							