

# EC2645TTS-53.90336M



## ITEM DESCRIPTION


Quartz Crystal Clock Oscillators XO (SPXO) LVCMOS (CMOS) 3.3Vdc 4 Pad 5.0mm x 7.0mm Ceramic Surface Mount (SMD) 53.90336MHz  $\pm 50$ ppm -10°C to +70°C

## ELECTRICAL SPECIFICATIONS

|                                       |                                                                                                                                                                                                                                        |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                     | 53.90336MHz                                                                                                                                                                                                                            |
| Frequency Tolerance/Stability         | $\pm 50$ ppm Maximum (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration) |
| Aging at 25°C                         | $\pm 5$ ppm/year Maximum                                                                                                                                                                                                               |
| Operating Temperature Range           | -10°C to +70°C                                                                                                                                                                                                                         |
| Supply Voltage                        | 3.3Vdc $\pm 10\%$                                                                                                                                                                                                                      |
| Input Current                         | 20mA Maximum                                                                                                                                                                                                                           |
| Output Voltage Logic High (Voh)       | 90% of Vdd Minimum (IOH=-8mA)                                                                                                                                                                                                          |
| Output Voltage Logic Low (Vol)        | 10% of Vdd Maximum (IOL=+8mA)                                                                                                                                                                                                          |
| Rise/Fall Time                        | 3nSec Maximum (Measured at 20% to 80% of waveform)                                                                                                                                                                                     |
| Duty Cycle                            | 50 $\pm 5\%$ (Measured at 50% of waveform)                                                                                                                                                                                             |
| Load Drive Capability                 | 15pF Maximum                                                                                                                                                                                                                           |
| Output Logic Type                     | CMOS                                                                                                                                                                                                                                   |
| Pin 1 Connection                      | Tri-State (High Impedance)                                                                                                                                                                                                             |
| Tri-State Input Voltage (Vih and Vil) | +0.7Vdd Minimum or No Connect to Enable Output, +0.3Vdd Maximum to Disable Output (High Impedance)                                                                                                                                     |
| Standby Current                       | 10 $\mu$ A Maximum (Disabled Output: High Impedance)                                                                                                                                                                                   |
| RMS Phase Jitter                      | 1pSec Maximum (12kHz to 20MHz offset frequency)                                                                                                                                                                                        |
| Start Up Time                         | 10mSec Maximum                                                                                                                                                                                                                         |
| Storage Temperature Range             | -55°C to +125°C                                                                                                                                                                                                                        |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS


|                              |                                               |
|------------------------------|-----------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 1, HBM: 1500V |
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A         |
| Flammability                 | UL94-V0                                       |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C         |
| Mechanical Shock             | MIL-STD-883, Method 2002, Condition B         |
| Moisture Resistance          | MIL-STD-883, Method 1004                      |
| Moisture Sensitivity         | J-STD-020, MSL 1                              |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K          |
| Resistance to Solvents       | MIL-STD-202, Method 215                       |
| Solderability                | MIL-STD-883, Method 2003                      |
| Temperature Cycling          | MIL-STD-883, Method 1010, Condition B         |
| Vibration                    | MIL-STD-883, Method 2007, Condition A         |




| PIN | CONNECTION         |
|-----|--------------------|
| 1   | Tri-State          |
| 2   | Ground/Case Ground |
| 3   | Output             |
| 4   | Supply Voltage     |


| LINE | MARKING                                               |
|------|-------------------------------------------------------|
| 1    | ECLIPTEK                                              |
| 2    | 53.903M                                               |
| 3    | XXXXXX<br>XXXXXX=Ecliptek<br>Manufacturing Identifier |

All Dimensions in Millimeters



All Tolerances are  $\pm 0.1$

**OUTPUT WAVEFORM & TIMING DIAGRAM**


**EC2645TTS-53.90336M****Test Circuit for CMOS Output**

Note 1: An external  $0.1\mu\text{F}$  low frequency tantalum bypass capacitor in parallel with a  $0.01\mu\text{F}$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance ( $<12\text{pF}$ ), 10X attenuation factor, high impedance ( $>10\text{Mohms}$ ), and high bandwidth ( $>300\text{MHz}$ ) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.


## Recommended Solder Reflow Methods



### High Temperature Infrared/Convection

|                                            |                                                   |
|--------------------------------------------|---------------------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 3°C/Second Maximum                                |
| <b>Preheat</b>                             |                                                   |
| - Temperature Minimum (Ts MIN)             | 150°C                                             |
| - Temperature Typical (Ts TYP)             | 175°C                                             |
| - Temperature Maximum (Ts MAX)             | 200°C                                             |
| - Time (ts MIN)                            | 60 - 180 Seconds                                  |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 3°C/Second Maximum                                |
| <b>Time Maintained Above:</b>              |                                                   |
| - Temperature (Tl)                         | 217°C                                             |
| - Time (tL)                                | 60 - 150 Seconds                                  |
| <b>Peak Temperature (Tp)</b>               | 260°C Maximum for 10 Seconds Maximum              |
| <b>Target Peak Temperature (Tp Target)</b> | 250°C +0/-5°C                                     |
| <b>Time within 5°C of actual peak (tp)</b> | 20 - 40 Seconds                                   |
| <b>Ramp-down Rate</b>                      | 6°C/Second Maximum                                |
| <b>Time 25°C to Peak Temperature (t)</b>   | 8 Minutes Maximum                                 |
| <b>Moisture Sensitivity Level</b>          | Level 1                                           |
| <b>Additional Notes</b>                    | Temperatures shown are applied to body of device. |

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 240°C

**Ts MAX to Tl (Ramp-up Rate)** 5°C/Second Maximum

#### Preheat

- Temperature Minimum (Ts MIN) N/A
- Temperature Typical (Ts TYP) 150°C
- Temperature Maximum (Ts MAX) N/A
- Time (ts MIN) 60 - 120 Seconds

**Ramp-up Rate (Tl to Tp)** 5°C/Second Maximum

#### Time Maintained Above:

- Temperature (Tl) 150°C
- Time (tL) 200 Seconds Maximum

**Peak Temperature (Tp)** 240°C Maximum

**Target Peak Temperature (Tp Target)** 240°C Maximum 2 Times / 230°C Maximum 1 Time

**Time within 5°C of actual peak (tp)** 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time

**Ramp-down Rate** 5°C/Second Maximum

**Time 25°C to Peak Temperature (t)** N/A

**Moisture Sensitivity Level** Level 1

**Additional Notes** Temperatures shown are applied to body of device.

### Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)

### High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures shown are applied to body of device.)