

ROV07, ROV07H

7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

GENERAL DESCRIPTION

The ROV07-XXX (**R**adial-leaded Metal **O**xide **V**aristor) products are 7mm radial leaded varistor devices suitable for protection of overvoltage transients.

ROV devices can provide protection for a wide variety of power systems against overvoltage faults such as lightning, power contact and power induction. Suitable for a broad range of applications including, but not limited to security, power supplies, surge strips, etc., the ROV device helps to protect valuable equipment from potential power surge damage by clamping high energy, short duration impulses. The ROV devices have high current handling and energy absorption capability and fast response times to help protect against transient faults.


FEATURES

- Radial leaded
- Broad Varistor voltage and V_{rms} range
 - Varistor voltage : 18V - 820V
 - V_{rms} voltage : 11V - 510V
- Two surge capability series
 - Standard series, High surge series
- Various lead types
 - Straight, Kinked, Other
- Various packaging options
 - Bulk, Tape & Reel, Ammo Pack
- Helps designers meet the following standards
 - UL, CSA, VDE
- Fast response time
- High current and energy absorption capability

APPLICATIONS

- Power supplies and power systems
- Line voltage
- Telecommunications systems
- Automotive systems
- Appliances

TYPICAL APPLICATION SCHEMATIC



*In some applications, a polymeric PTC device such as a Tyco Electronics PolySwitch device may be used instead of a fuse to provide a preferred solution.


ROV07, ROV07H

7mm Series Metal Oxide Varistors



www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

PART NUMBERING



DEVICE MARKING



GENERAL CHARACTERISTICS

Storage temperature:	-40°C ... +125°C
Maximum operating temperature:	-40°C ... +125°C
Maximum working surface temperature:	+115°C
Temperature coefficient of voltage:	0 ... +0.05% / °C max.
Insulation resistance of coating (@ 500 VDC):	Over 1000MΩ
Maximum response time:	25ns
Lead Material:	22 AWG Sn/Pb Plated Copper

AGENCY RECOGNITION

Device Ratings and Characteristics Tables contain specific recognition information for each individual part. The table below details marking symbols for each agency recognition type.

UL1414	UL1449 (2nd Edition)	CSA	VDE
◆	●	▲	■

ROV07, ROV07H

7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

DEVICE RATINGS AND CHARACTERISTICS

STANDARD SERIES

Part Number	Varistor Voltage V@1.0mA		Maximum Allowable Voltage		Maximum Clamping Voltage V@10A	Maximum Surge Current (8x20us)		Rated Wattage	Energy (10x1000us)	Capacitance (Typical)	Certifications
	(V _{DC})	Tolerance	V _{rms} (V _{AC})	(V _{DC})	(V _{DC})	1 Time (A)	2 Times (A)	(W)	(J)	@1kHz (pF)	
ROV07-180M	18	± 20%	11	14	36 ¹⁾	250	125	0.02	1.2	2918	●
ROV07-220L	22	± 15%	14	18	43 ¹⁾				1.4	2933	●
ROV07-270K	27	± 10%	17	22	53 ¹⁾				1.7	2344	●
ROV07-330K	33		20	26	65 ¹⁾				2.2	1840	●
ROV07-390K	39		25	31	77 ¹⁾				2.4	1817	●
ROV07-470K	47		30	38	93 ¹⁾				3.0	1595	●
ROV07-560K	56		35	45	110 ¹⁾				3.5	1333	●
ROV07-680K	68		40	56	135 ¹⁾				4.3	1119	●
ROV07-820K	82		50	65	135	1200	600	0.25	5.5	643	● ■
ROV07-101K	100		60	85	165				7.0	535	● ■
ROV07-121K	120		75	100	200				8.0	457	● ■
ROV07-151K	150		95	125	250				11.0	371	● ■
ROV07-181K	180		115	150	300				13.0	215	● ■
ROV07-201K	200		130	170	340				14.3	224	◆ ● ▲ ■
ROV07-221K	220		140	180	360				15.5	190	◆ ● ▲ ■
ROV07-241K	240		150	200	395				16.8	185	◆ ● ▲ ■
ROV07-271K	270		175	225	455				19.8	161	◆ ● ▲ ■
ROV07-301K	300		195	250	505				21.0	135	◆ ● ▲ ■
ROV07-331K	330		210	275	550				23.0	141	◆ ● ▲ ■
ROV07-361K	360		230	300	595				26.0	117	◆ ● ▲ ■
ROV07-391K	390		250	320	650				30.0	110	◆ ● ▲ ■
ROV07-431K	430		275	350	710				33.0	111	◆ ● ▲ ■
ROV07-471K	470		300	385	775				35.0	102	◆ ● ▲ ■
ROV07-511K	510		320	418	842				37.0	100	◆ ● ▲
ROV07-561K	560		350	460	920				39.0	87	◆ ● ▲
ROV07-621K	620		385	505	1025				41.0	80	◆ ● ▲
ROV07-681K	680		420	560	1120				43.0	82	◆ ● ▲
ROV07-751K	750		460	615	1240				45.0	74	◆ ● ▲
ROV07-781K	780		485	640	1290				46.0	70	◆ ● ▲
ROV07-821K	820		510	670	1355				47.0	70	◆ ● ▲

1). The clamping voltage for devices ROV07-180M to ROV07-680K is tested with 2.5A current.

ROV07, ROV07H

7mm Series Metal Oxide Varistors


www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

PULSE LIFETIME RATING CURVES

STANDARD SERIES

ROV07-180M – ROV07-680K




Rectangular Wave (μ s)

V-I CHARACTERISTIC CURVES


STANDARD SERIES

ROV07-180M – ROV07-680K




Current (A)

ROV07-820K – ROV07-821K



Rectangular Wave (μ s)

ROV07-820K – ROV07-821K



Current (A)

ROV07, ROV07H

7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

DEVICE RATINGS AND CHARACTERISTICS

HIGH SURGE SERIES

Part Number	Varistor Voltage V@1.0mA		Maximum Allowable Voltage		Maximum Clamping Voltage V@10A	Maximum Surge Current (8x20us)		Rated Wattage	Energy (10x1000us)	Capacitance (Typical)	Certifications
	(V _{DC})	Tolerance	V _{rms} (V _{AC})	(V _{DC})	(V _{DC})	1 Time (A)	2 Times (A)	(W)	(J)	@1kHz (pF)	
ROV07H180M	18	± 20%	11	14	36 ¹⁾	500	250	0.02	1.5	2920	●
ROV07H220L	22	± 15%	14	18	43 ¹⁾				1.7	2930	●
ROV07H270K	27	± 10%	17	22	53 ¹⁾				2.1	2340	●
ROV07H330K	33		20	26	65 ¹⁾				2.8	1840	●
ROV07H390K	39		25	31	77 ¹⁾				3.0	1820	●
ROV07H470K	47		30	38	93 ¹⁾				3.8	1600	●
ROV07H560K	56		35	45	110 ¹⁾				4.4	1330	●
ROV07H680K	68		40	56	135 ¹⁾				5.4	1120	●
ROV07H820K	82		50	65	135	1750	1250	0.25	7.0	640	●
ROV07H101K	100		60	85	165				9.0	540	●
ROV07H121K	120		75	100	200				11.0	460	●
ROV07H151K	150		95	125	250				13.0	370	●
ROV07H181K	180		115	150	300				16.0	220	●
ROV07H201K	200		130	170	340				17.5	220	◆ ● ▲
ROV07H221K	220		140	180	360				19.0	190	◆ ● ▲
ROV07H241K	240		150	200	395				21.0	190	◆ ● ▲
ROV07H271K	270		175	225	455				24.0	160	◆ ● ▲
ROV07H301K	300		195	250	505				26.0	140	◆ ● ▲
ROV07H331K	330		210	275	550				28.0	140	◆ ● ▲
ROV07H361K	360		230	300	595				32.0	120	◆ ● ▲
ROV07H391K	390		250	320	650				35.0	110	◆ ● ▲
ROV07H431K	430		275	350	710				40.0	110	◆ ● ▲
ROV07H471K	470		300	385	775				42.0	100	◆ ● ▲
ROV07H511K	510		320	418	842				45.0	100	◆ ● ▲
ROV07H561K	560		350	460	920				51.0	85	◆ ● ▲
ROV07H621K	620		385	505	1025				54.0	80	◆ ● ▲
ROV07H681K	680		420	560	1120				56.0	80	◆ ● ▲
ROV07H751K	750		460	615	1240				58.0	75	◆ ● ▲
ROV07H781K	780		485	640	1290				59.0	70	◆ ● ▲
ROV07H821K	820		510	670	1355				60.0	70	◆ ● ▲

1). The clamping voltage for devices ROV07H180M to ROV07H680K is tested with 2.5A current.



ROV07, ROV07H 7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003



PULSE LIFETIME RATING CURVES

HIGH SURGE SERIES



V-I CHARACTERISTIC CURVES

HIGH SURGE SERIES




ROV07, ROV07H

7mm Series Metal Oxide Varistors

www.tycopowercomponents.com


Document: SCD 25481
Status: Released
Rev. A June 30, 2003

DIMENSIONS



KINKED LEAD TYPE
Dimension Table

A max.	9.0
$l \pm 0.05$	0.6
$E \pm 1.0$	5.0
B max.	13.0
D_1 min.	25.0
D min.	24.0



STRAIGHT LEAD TYPE (-S)
Table of C max., F, and B₁ max.

Type No.	C max.	F±0.8	B ₁ max.
180M	4.5	0.8	12.0
220L	4.5	0.9	12.0
270K	4.7	0.9	12.0
330K	4.7	1.0	12.0
390K	4.7	1.2	12.0
470K	5.0	1.2	12.0
560K	5.0	1.4	12.0
680K	5.5	1.7	12.0
820K	3.8	0.8	12.0
101K	3.9	0.8	12.0
121K	4.1	0.9	12.0
151K	4.5	1.2	12.0
181K	4.1	1.0	12.0
201K	4.2	1.0	12.0
221K	4.3	1.1	12.0
241K	4.4	1.3	12.0
271K	4.6	1.4	12.0
301K	4.8	1.5	12.0
331K	4.9	1.5	12.0
361K	5.1	1.9	12.0
391K	5.3	2.0	12.5
431K	6.1	2.3	12.5
471K	6.4	2.3	12.5
511K	6.6	2.5	13.0
561K	6.9	2.8	13.0
621K	7.2	3.1	13.0
681K	7.5	3.4	13.0
751K	7.9	3.7	13.0
781K	8.1	3.9	13.0
821K	8.3	4.1	13.0

ROV07, ROV07H


7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

 Document: SCD 25481
 Status: Released
 Rev. A June 30, 2003

PACKAGING

in mm





Packaging	Bulk (box)	Reel	Ammo
Box size (mm)	290 x 155 x 110	350 x 350 x 108	330 x 240 x 45
Carton size (mm)	310 x 328 x 250	371 x 371 x 590	354 x 515 x 258
One carton with	4 Boxes	5 Boxes (10 reels)	10 Boxes

Part Number	Bulk (box)	Reel	Ammo
ROV07-180M to ROV07-470K ROV07H180M to ROV07H470K	5000	1500	1500
ROV07-560K to ROV07-680K ROV07H560K to ROV07H680K	5000	1500	1000
ROV07-820K to ROV07-331K ROV07H820K to ROV07H331K	5000	1500	1500
ROV07-361K to ROV07-391K ROV07H361K to ROV07H391K	5000	1500	1000
ROV07-431K to ROV07-471K ROV07H431K to ROV07H471K	5000	1000	1000
ROV07-511K to ROV07-751K ROV07H511K to ROV07H751K	4000	1000	1000
ROV07-781K to ROV07-821K ROV07H781K to ROV07H821K	4000	1000	1000

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

1/2" Pitch



Tyco Electronics Corporation 308 Constitution Drive, Menlo Park, CA 94025 Tel: (800) 227-4856 Fax: (800) 227-4866

ROV07, ROV07H

7mm Series Metal Oxide Varistors

www.tycopowercomponents.com

Document: SCD 25481
Status: Released
Rev. A June 30, 2003

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of each product for their applications. Tyco Electronics Corporation assumes no responsibility for the use of its product or for any infringement of patents or other rights of third parties resulting from the use of its product. No license is granted by implication or otherwise under any patent or proprietary right of Tyco Electronics except the right to use such product for the purpose for which it is sold. Tyco Electronics reserves the right to change or update, without notice, any information contained in this publication; to change, without notice, the design, construction, processing, or specification of any product; and to discontinue or limit production or distribution of any product. This publication supersedes and replaces all information previously supplied. Without express written consent by an officer of Tyco Electronics, Tyco Electronics does not authorize the use of any its products as components in nuclear facility applications, aerospace, or in critical life support devices or systems. Tyco Electronics' only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale and in no case will Tyco Electronics be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products.

Raychem is a trademark of Tyco Electronics Corporation

© 2003 Tyco Electronics Corporation