


SMD Power Inductor


CDRH50D18R/LD



Dimension - [mm]



Land pattern and Schematics - [mm]



Description

- Ferrite drum core construction.
- Magnetically shielded.
- $L \times W \times H$: $5.2 \times 5.2 \times 2.0$ mm Max.
- Product weight: 0.16g(Ref.)
- Moisture Sensitivity Level: 1
- RoHS compliance.

Environmental Data

- Operating temperature range: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (including coil's self temperature rise)
- Storage temperature range: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
- Solder reflow temperature: 260°C peak.

Packaging


- Carrier tape and reel packaging.
- 13.0" diameter reel
- 3000pcs per reel

Applications

- Ideally used in digital single-lens reflex camera etc.

SMD Power Inductor

CDRH50D18R/LD



Electrical Characteristics

Part No.	Stamp	Inductance (μH) [Within] ※1	D.C.R. (mΩ) [Within] (at 20℃)	Saturation current (A) ※2		Temperature rise current (A) ※3
				(at 20℃)	(at 105℃)	
CDRH50D18RLDNP-1R1NC	A	1.1±30%	17±25%	2.10	1.72	4.40
CDRH50D18RLDNP-1R6NC	B	1.6±30%	20±25%	1.75	1.46	3.95
CDRH50D18RLDNP-2R2NC	C	2.2±30%	24±25%	1.50	1.24	3.45
CDRH50D18RLDNP-3R6NC	D	3.6±30%	31±25%	1.17	0.98	3.15
CDRH50D18RLDNP-4R7MC	E	4.7±20%	34±25%	1.00	0.83	2.98
CDRH50D18RLDNP-6R8MC	F	6.8±20%	52±25%	0.85	0.70	2.22
CDRH50D18RLDNP-100MC	G	10±20%	79±25%	0.72	0.58	1.80
CDRH50D18RLDNP-150MC	H	15±20%	120±20%	0.58	0.47	1.40
CDRH50D18RLDNP-220MC	J	22±20%	178±20%	0.48	0.40	1.17
CDRH50D18RLDNP-330MC	K	33±20%	255±20%	0.38	0.30	0.97
CDRH50D18RLDNP-470MC	L	47±20%	355±20%	0.32	0.26	0.77
CDRH50D18RLDNP-680MC	M	68±20%	600±20%	0.28	0.23	0.54
CDRH50D18RLDNP-101MC	N	100±20%	760±20%	0.22	0.20	0.50
CDRH50D18RLDNP-151MC	P	150±20%	1420±20%	0.18	0.15	0.34


※1. Measuring condition: at 100kHz.

※2. Saturation current: The value of D.C. current when the inductance decreases to 70% of it's nominal value.

※3. Temperature rise current: The value of D.C. current when the temperature rise is $\Delta t=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).













SMD Power Inductor

CDRH50D18R/LD



Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) — ΔT





SMD Power Inductor CDRH50D18R/LD





Saturation Current & Temperature Rise Graph

— L (20°C) — L (105°C) — ΔT



Solder Reflow Condition



Please refer to the sales offices on our website - <http://www.sumida.com>

Hong Kong

Tel.+852-2880-6781
FAX.+852-2565-9600
sales@hk.sumida.com

Saitama(Japan)

Tel.+81-48-691-7300
FAX.+81-48-691-7340
sales@jp.sumida.com

Chicago

Tel.+1-847-545-6700
FAX. +1-847-545-6720
sales@us.sumida.com

Shanghai

Tel.+86-21-5836-3299
FAX.+86-21-5836-3266
shanghai.sales@cn.sumida.com

Seoul

Tel.+82-2-6237-0777
FAX.+82-2-6237-0778
sales@kr.sumida.com

Obernzell

Tel.+49-8591-937-0
FAX. +49-8591-937-103
contact@eu.sumida.com

Shenzhen

Tel.+86-755-8291-0228
FAX.+86-755-8291-0338
shenzhen.sales@cn.sumida.com

Singapore

Tel.+65-6296-3388
FAX.+65-6841-4426
sales@sg.sumida.com

Neumarkt

Tel.+49-9181-4509-110
FAX. +49-9181-4509-310
infocomp@eu.sumida.com

Taipei

Tel.+886-2-8751-2737
FAX.+886-2-8751-2738
sales@tw.sumida.com

San Jose

Tel.+1-408-321-9660
FAX.+1-408-321-9308
sales@us.sumida.com