


LOC	DIST	ZONE	LTR	DESCRIPTION	DATE	APPD
6	14			REVISED PER 0720-0230-93	2/28/93	DAP

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE 12-10 AWG STRAINED	UL E13288 Listed 12-10 AWG STRAINED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5,180-13,100] CIR MILS
STRAINED

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN INCHES
TOLERANCES ON:
2 PLC DEC ± .
3 PLC DEC ± .
ANGLES
MATERIAL
COPPER PER
ASTM B-152
ANNEALED
FINISH
TIN PLATE
0.00254 [.000100] MIN
THK PER MIL-T-10727

DR 1-29-93 TA BRINKMAN	NAME AMP AMP Incorporated Horsham, PA 17105-3608
CHK 1-29-93 DA PATTERSON	TERMINAL, RECTANGULAR TONGUE, BUDGET
APPD 1-29-93 DE MILLER	SIZE CAGE CODE 00779 DRAWING NO C-331269
APPD 1-29-93 JL HOCKLEY	SCALE 8:1
PRODUCT SPEC	WEIGHT
APPLICATION SPEC	SHEET 1 OF 1