




Proto-Type Board

PSP-110002



Dimensions: In.

Specifications:

- Type: UIB-34 universal interface breadboard
- External body & back plate: ABS polymer
- Internal contact terminal: silver alloy and nickel
- Resistance: $<10\text{m}\Omega$ ($\varnothing 0.6\text{mm}$ lead @ 1KHz)
- Capacitance: $<10\text{pF}$ ($\varnothing 0.6\text{mm}$ lead @ 1KHz)
- Insulation: $>10\text{T}\Omega$ (500VDC for 1 minute)
- Hi-Pot test: 1500VDC for 1 minute
- Breakdown current: 30mA
- Contact current: 3A ($\varnothing 0.6\text{mm}$ lead)
- Wire size acceptability: $\varnothing 0.3\text{mm} \sim 0.8\text{mm}$
- Warning: do not use high voltage (AC $>50\text{V}$, DC $>75\text{V}$)
- Tie point: 5 point x 128 row (640) x 3 pcs. (base socket);
5 point x 20 row (100) x 4 pcs. (bus strip); 2320 total
- Weight: 600gm
- Height with UC-02: 1.18"
- Accessories: 1 edge plate (EP-3), 1 universal connector,
& 4 bind posts

Updated: 5-11-05

383-K2300-1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

PSP:

[383-K2300-1](#)