




1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
- △ MATERIAL:
HOUSING & COVER - THERMOPLASTIC, BLACK.
TERMINALS - PHOS. BRONZE PLATED WITH EITHER .00030 MINIMUM GOLD PLATE OR GOLD FLASH OVER PALLADIUM NICKEL PLATE. .00030 MIN TOTAL ON MATING SURFACE. GOLD FLASH PLATED ON TERMINATING SIDE. .00030 MINIMUM NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
- △ COVER SHOWN LOOSE BUT SHIPPED ASSEMBLED.
4. WIRE RANGE: 26 AWG SOLID THRU 30 AWG SOLID AND 28 AWG STRANDED RIBBON CABLE.
- △ ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
- △ FLAT CABLE SHALL BE FURNISHED BY CUSTOMER.
- △ MATING FACE CONSISTS OF TWO ROWS OF TERMINALS ON .085 CENTERS, TERMINATING SIDE CONSISTS OF TERMINALS ON .100 CENTERS FOR AN EFFECTIVE .050 TERMINATION.
- △ PANEL THICKNESS RANGE:
FRONT PANEL MOUNTING - .125 MAX
REAR PANEL MOUNTING - .062 MAX
9. FOR MORE INFORMATION REFER TO AMP PRODUCT SPECIFICATION 108-6076 & APPLICATION SPEC 114-6030.

.620	.310	.149	1.575	REAR PANEL MOUNTING
.640	.320	.126	1.488	FRONT PANEL MOUNTING
DIM D	DIM C	DIM B	DIM A	DESCRIPTION

AS SHOWN		554103-1
DESCRIPTION	PART NUMBER	
Type Electronics Corporation Hawthorne, CA 91706-3608		
PLUG ASSEMBLY 24 POSITION PANEL MOUNTING LOW PROFILE, CHAMP LATCH		
DATE CODE (PANEL NO) A2 00779 ©-554103		
SHEET	1 of 1	REV
SOCT 2-1		