

NSR2030QMTWG

2A, 30V Schottky Full Bridge

These full bridge Schottky barrier diodes are designed for the rectification of the high speed signal of wireless charging. The NSR2030QMTWG has a very low forward voltage that will reduce conduction loss. It is housed in a UDFN 3.5 x 3.5 x 0.5 mm package that is ideal for space constrained wireless applications.

Features

- Extremely Fast Switching Speed
- Low Forward Voltage – 0.54 V (Typ) @ $I_F = 2$ A
- These Devices are Pb-Free, Halogen Free and are RoHS Compliant

Typical Applications

- Low Voltage Full Bridge Rectification & Wireless Charging

MAXIMUM RATINGS ($T_J = 125^\circ\text{C}$ unless otherwise noted) (Note 1)

Rating	Symbol	Value	Unit
Reverse Voltage	V_R	30	V
Forward Current (DC)	I_F	2.0	A
Forward Current Surge Peak (60 Hz, 1 cycle)	I_{FSM}	12.5	A
Non-Repetitive Peak Forward Current (Square Wave, $T_J = 25^\circ\text{C}$ prior to surge)	I_{FSM}		A
$t = 1\ \mu\text{s}$		40	
$t = 1\ \text{ms}$		10	
$t = 1\ \text{s}$		3.0	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. All specifications pertain to a single diode.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Total Device Dissipation FR-5 Board $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D (Note 2)	2.08	W
		20.8	$\text{mW}/^\circ\text{C}$
Thermal Resistance Junction to Ambient	$R_{\theta JA}$ (Note 2)	48	$^\circ\text{C}/\text{W}$
Total Device Dissipation FR-5 Board $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D (Note 3)	0.75	W
		7.6	$\text{mW}/^\circ\text{C}$
Thermal Resistance Junction to Ambient	$R_{\theta JA}$ (Note 3)	132	$^\circ\text{C}/\text{W}$
Total Device Dissipation FR-5 Board $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D (Note 4)	0.87	W
		8.8	$\text{mW}/^\circ\text{C}$
Thermal Resistance Junction to Ambient	$R_{\theta JA}$ (Note 4)	114	$^\circ\text{C}/\text{W}$
Junction Temperature	T_J	+125	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-55 to +150	$^\circ\text{C}$

2. 4 Layer JEDEC JESD51.7 FR-4 @ 10 mm², 1 oz. copper trace, still air.
3. Single Layer JEDEC JESD51.3 FR-4 @ 100 mm², 1 oz. copper trace, still air.
4. Single Layer JEDEC JESD51.3 FR-4 @ 100 mm², 2 oz. copper trace, still air.



ON Semiconductor®

www.onsemi.com

MARKING DIAGRAM




UDFN4 3.5x3.5
CASE 517DA

1 °
2030
AYWW
▪


2030 = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
▪ = Pb-Free Package

(Note: Microdot may be in either location)

PIN CONNECTIONS



DEVICE SCHEMATIC



ORDERING INFORMATION

Device	Package	Shipping†
NSR2030QMTWG	UDFN4 (Pb-Free)	3000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

NSR2030QMUTWG

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted) (Note 5)

Characteristic	Symbol	Min	Typ	Max	Unit
Reverse Breakdown Voltage ($I_R = 1.0 \text{ mA}$)	$V_{(BR)}$	30	—	—	V
Reverse Leakage ($V_R = 30 \text{ V}$)	I_R	—	5.0	20	μA
Forward Voltage ($I_F = 0.5 \text{ A}$)	V_F	—	0.41	0.455	V
Forward Voltage ($I_F = 1.0 \text{ A}$)	V_F	—	0.46	0.55	V
Forward Voltage ($I_F = 2.0 \text{ A}$)	V_F	—	0.54	0.65	V
Reverse Recovery Time ($I_F = I_R = 10 \text{ mA}$, $I_{R(\text{REC})} = 1.0 \text{ mA}$)	t_{rr}	—	34	—	ns
Input Capacitance (pins 1 to 3) ($V_R = 1.0 \text{ V}$, $f = 1.0 \text{ MHz}$)	C_T	—	102	—	pF

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. All specifications pertain to a single diode.




Figure 1. Recovery Time Equivalent Test Circuit

TYPICAL CHARACTERISTICS




Figure 1. Forward Voltage




Figure 2. Reverse Leakage




Figure 3. Input Capacitance




Figure 4. Forward Surge Current





Figure 5. Thermal Response

PACKAGE DIMENSIONS

UDFN4 3.5x3.5, 1.55P

CASE 517DA


ISSUE A



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION *b* APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.05 AND 0.15 MM FROM THE TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED PADS AS WELL AS THE TERMINALS.
5. POSITIONAL TOLERANCE APPLIES TO ALL OF THE EXPOSED PADS.

DIM	MILLIMETERS	
	MIN	MAX
A	0.45	0.55
A1	0.00	0.05
A3	0.13 REF	
b	0.35	0.45
D	3.50 BSC	
D2	1.15	1.25
D3	1.35	1.45
E	3.50 BSC	
E2	2.25	2.35
E3	0.95	1.05
e	1.55 BSC	
F	0.925 BSC	
G	0.58 BSC	
L	0.35	0.55



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local
Sales Representative