




4

3





2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,-. -,-.

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW				P	LTR	DESCRIPTION	DATE	DWN	APVD
						SEE SHEET 1.			



NOTE:


1. MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: BRASS.

2. FINISH:
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS,
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.

3. REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.2~1.4mm)
(COMPONENT SIDE) TOLERANCE±0.05mm

OBSOLETED	TUBE	1-1734062-2
	TAPE & REEL	1-1734062-1
NOTE	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics		Tyco Electronics Corporation							
		CHK				Taipei, Taiwan							
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		APVD		NAME USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE							
				PRODUCT SPEC									
				QUALIFICATION TEST REPORT									
MATERIAL		FINISH		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
SEE NOTE		SEE NOTE		WEIGHT 4.71 GRAMS		A3		00779		C-1734062		—	
CUSTOMER DRAWING						SCALE —		SHEET 2 OF 22		REV E			

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC

DIST


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			




TE LOGO &
DATE CODE




- NOTE:
- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: BRASS.
 - FINISH:
CONTACT: 0.76μ"m [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μ"m [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAIL,
WITH ENTIRE CONTACT UNDERPLATED 1.27mμ" [50μ"] MIN. NICKEL.
FRONT SHIELD: 0.76μ"m [30μ"] MIN. NICKEL PLATING.
0.76μ"m [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE
SPEC 109-201, CONDITION B.



RECOMMEND P.C.B LAYOUT (THICKNESS 1.2mm)
(COMPONENT SIDE) TOLERANCE±0.05mm



TRAY	2-1734062-2
TUBE	2-1734062-1
PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics		Tyco Electronics Corporation	
		CHK				Taipei, Taiwan	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		0 PLC ± —		PRODUCT SPEC		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
		1 PLC ± 0.35		QUALIFICATION TEST REPORT			
		2 PLC ± 0.25					
		3 PLC ± —					
		4 PLC ± —					
		ANGLES ± 3°					
MATERIAL		FINISH		SIZE		CAGE CODE	
SEE NOTE		SEE NOTE		DRAWING NO		RESTRICTED TO	
				WEIGHT 4.71 GRAMS		A3 00779 C=1734062	
				CUSTOMER DRAWING		SCALE —	
						SHEET 3 OF 22	
						REV E	

4




3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



- NOTES:
- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: STAINLESS.
 - FINISH:
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. MATTE TIN PLATING ON SOLDER TAILS.
1.27μm [50μ"] MIN. NICKEL UNDERPLATED WITH ENTIRE CONTACT .
FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - FINISH:
CONTACT: 0.254μm [10μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. MATTE TIN PLATING ON SOLDER TAILS.
1.27μm [50μ"] MIN. NICKEL UNDERPLATED WITH ENTIRE CONTACT.
FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
SPUTTERING/BLACK PLATING IN FRONT SURFACE.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
GROUNDING STRIP: SPUTTERING/BLACK PLATING IN FRONT SURFACE.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



RECOMMENDED MOUNT DIMENSION

RECOMMEND P.C.B LAYOUT (THICKNESS 1.4~1.6mm)
(COMPONENT SIDE) TOLERANCE±0.05mm

3	TAPE & REEL	3-1734062-4
2	TAPE & REEL	3-1734062-3
	TUBE	3-1734062-2
	TRAY	3-1734062-1
FINISH	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan			
		CHK				
DIMENSIONS: MM		APVD	NAME			
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
		QUALIFICATION TEST REPORT				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		4.71 GRAMS	A3	00779	C=1734062	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING				
FINISH		SCALE				
		SHEET 4 OF 22				
		REV E				

4






3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



RECOMMENDED MOUNT DIMENSION

- NOTES:
- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: SUS.
 - FINISH:
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS.
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

RECOMMEND P.C.B LAYOUT (THICKNESS 1.6mm)
(COMPONENT SIDE) TOLERANCE±0.05mm

TAPE & REEL	4-1734062-2
PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan			
		CHK				
DIMENSIONS: MM		APVD	NAME			
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
		QUALIFICATION TEST REPORT				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		4.71 GRAMS	A3	00779	C-1734062	
		CUSTOMER DRAWING	SCALE	SHEET	REV	
				6 OF 22	E	






4

3

2

1


LOC		DIST		REVISIONS					
DW		P	LTR	DESCRIPTION		DATE	DWN	APVD	
				SEE SHEET 1.					



NOTES:

- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: BRASS.
- FINISH :
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT-TIN PLATING ON SOLDER TAILS.
WITH ENTIRE CONTACT UNDERPLATED 1.27mμ" [50μ"] MIN. NICKEL.
FRONT SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
REAR SHIELD: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
- REFLOW SOLDER CAPABLE TO 260°C PER TE
SPEC 109-201, CONDITION B.

OBSOLETE	TRAY	5-1734062-2
OBSOLETE	TAPE & REEL	5-1734062-1
	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan			
		CHK					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		0 PLC ± -		PRODUCT SPEC		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
		1 PLC ± 0.35		QUALIFICATION TEST REPORT			
		2 PLC ± 0.25				SIZE	
		3 PLC ± -				CAGE CODE	
		4 PLC ± -				DRAWING NO	
		ANGLES ± 3°				RESTRICTED TO	
MATERIAL		FINISH		WEIGHT 4.71 GRAMS		A300779 C-1734062	
SEE NOTE		SEE NOTE		CUSTOMER DRAWING		SCALE —	
						SHEET 7 OF 22	
						REV E	

RECOMMEND P.C.B LAYOUT (THICKNESS 1.0mm)
(COMPONENT SIDE) TOLERANCE±0.05mm

LOC		DIST		REVISIONS					
DW				P	LTR	DESCRIPTION	DATE	DWN	APVD
						SEE SHEET 1.			

D

C

B


A

D

C

B

A



NOTES:

1.MATERIAL:

HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.

SPACER: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.

CONTACT: PHOSPHOR BRONZE.

FRONT SHELL: BRASS.

REAR SHELL: SPCC.

GROUNDING STRIP: STAINLESS.

2.FINISH:

CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.

3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDER TAILS, WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.

FRONT SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.

0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.

REAR SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.


0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.

GROUNDING SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.

0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.

3. REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.

TAPE & REEL	6-1734062-1
PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics		Tyco Electronics Corporation	
		CHK				Taipei, Taiwan	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
		0 PLC ± —		PRODUCT SPEC		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
		1 PLC ± 0.35		QUALIFICATION TEST REPORT			
		2 PLC ± 0.25					
		3 PLC ± —					
		4 PLC ± —					
		ANGLES ± 3°					
MATERIAL		FINISH		SIZE		CAGE CODE	
SEE NOTE		SEE NOTE		DRAWING NO		RESTRICTED TO	
				WEIGHT 4.71 GRAMS		A3 00779 C-1734062	
CUSTOMER DRAWING				SCALE		SHEET	
				—		8 OF 22	
						REV E	


4

3


2

1



LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
		SEE SHEET 1.				




- NOTES:
- MATERIAL:
HOUSING: PA9T WITH 30% GF, UL 94V-0 RATED, BLACK COLOR.
CONTACT: PHOSPHOR BRONZE.
FRONT SHIELD: BRASS.
REAR SHIELD: SPCC.
GROUNDING STRIP: BRASS.
 - FINISH:
CONTACT: 0.762μm [30μ"] MIN. GOLD PLATING ON CONTACT AREA.
3.048μm [120μ"] MIN. BRIGHT TIN PLATING ON SOLDERTAILS.
WITH ENTIRE CONTACT UNDERPLATED 1.27μm [50μ"] MIN. NICKEL.
FRONT SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.
0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.
REAR SHELL: 0.762μm [30μ"] MIN. NICKEL PLATED.
0.762μm [30μ"] MIN. Cu UNDERPLATING OVERALL.
GROUNDING STRIP: 0.762μm [30μ"] MIN. NICKEL PLATING.
0.762μm [30μ"] MIN. Cu UNDER PLATING OVERALL.
 - REFLOW SOLDER CAPABLE TO 260°C PER TE SPEC 109-201, CONDITION B.



RECOMMEND P.C.B LAYOUT (THICKNESS 1.2mm)
(COMPONENT SIDE) TOLERANCE±0.05mm




0.20
ALL PEGS



TAPE & REEL	7-1734062-1
PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan			
		CHK				
DIMENSIONS: MM		APVD	NAME			
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE			
		QUALIFICATION TEST REPORT				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
SEE NOTE		4.3 GRAMS	A3	00779	C-1734062	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING				
0 PLC ± - 1 PLC ± 0.35 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		SCALE				
FINISH		SEE NOTE				
		SHEET 9 OF 22				
		REV E				



4

3

2

1





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


—, — .

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.






LOC	DIST	REVISIONS				
DW		P	LTR	DESCRIPTION	DATE	APVD
				SEE SHEET 1.		



FOLDER PAPER BOARD



SHIPPING BOX



140	7	980	8.60	4.62	1-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	1734062-1
					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan		
		CHK			
		APVD	NAME		
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
		APPLICATION SPEC			
		WEIGHT	SIZE	CAGE CODE	RESTRICTED TO
			A3	00779	—
		CUSTOMER DRAWING	SCALE	SHEET	REV
			—	11 OF 22	E

4

3

2

1





THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


—, — .

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW		P	LTR	DESCRIPTION			DATE	DWN	APVD
				SEE SHEET 1.					



24	40	960	6.10	4.52	3-1734062-2
					1-1734062-2
					1734062-2
PCS/ TUBE	TUBS INNER BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan	
		CHK			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ± —		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
		1 PLC ± —			
		2 PLC ± —			
		3 PLC ± —			
		4 PLC ± —			
		ANGLES ± —			
MATERIAL		FINISH		SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
		WEIGHT		A300779	
				C=1734062	
CUSTOMER DRAWING				SCALE	
				SHEET	
				12 OF 22	
				REV	
				E	

4





3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW				P	LTR	DESCRIPTION	DATE	DWN	APVD
						SEE SHEET 1.			



100	7	700	7.28	3.30	1734062-3
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan				
		CHK						
DIMENSIONS: MM		APVD		NAME USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE				
		PRODUCT SPEC —						
		APPLICATION SPEC —		SIZE A3	CAGE CODE 00779	DRAWING NO C=1734062	RESTRICTED TO —	
MATERIAL —		WEIGHT —						
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		FINISH —						
CUSTOMER DRAWING						SCALE —	SHEET 13 OF 22	REV E

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —








© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DW

DIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



50	20	1000	6.82	4.71	2-1734062-2
PCS/ TRAY	TRAY/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		Tyco Electronics Corporation Taipei, Taiwan	
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD			
MATERIAL		PRODUCT SPEC		NAME	
FINISH		APPLICATION SPEC		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
		WEIGHT		SIZE	CAGE CODE
		CUSTOMER DRAWING		DRAWING NO	
				RESTRICTED TO	
				REV	
				E	


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


—, —.

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW				P	LTR	DESCRIPTION	DATE	DWN	APVD
						SEE SHEET 1.			



25	40	1000	6.27	4.71	4-1734062-1
PCS/TUBE	TUBS INNER BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	2-1734062-1
					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics		Tyco Electronics Corporation					
		CHK				Taipei, Taiwan					
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME							
				PRODUCT SPEC							
				—							
				APPLICATION SPEC							
MATERIAL		FINISH		—		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE					
—		—		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
				A3		00779		C-1734062		—	
				CUSTOMER DRAWING				SCALE		SHEET	
				—		15 OF 22		E			

4




3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC DW	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1.			



LABEL






LABEL



TAPE


LABEL



SHIPPING BOX
7 REELS / SHIPPING BOX

120	7	840	9.05	3.96	3-1734062-4
					3-1734062-3
PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan		
DIMENSIONS: MM		CHK			
		APVD	NAME		
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
MATERIAL		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
		WEIGHT	A3 00779 C-1734062		
		CUSTOMER DRAWING	SCALE	SHEET 16 of 22	REV E



4



3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
		SEE SHEET 1.				




TOP COVER TAPE




PULL OUT DIRECTION




LABEL




FOLDER PAPER BOARD



SHIPPING BOX



LABEL



7.23 Kg	3.2 Kg	100	7	700 PCS	4-1734062-2
GROSS WEIGHT	NET WEIGHT	PCS/REEL	REELS/CARTON	QUANTITY	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NAME		
0 PLC ± -		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
1 PLC ± -		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
2 PLC ± -		WEIGHT	A300779C-1734062		
3 PLC ± -		CUSTOMER DRAWING	SCALE SHEET 19 OF 22 REV E		
4 PLC ± -					
ANGLES ± -					
FINISH					

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .








© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC
DW

DIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



150	7	1050	8.93	4.95	6-1734062-1
PCS/ REEL	REELS/ BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	Tyco Electronics Corporation Taipei, Taiwan		
		CHK			
		APVD	NAME		
		PRODUCT SPEC	USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE		
		APPLICATION SPEC			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO
			A3	00779	C-1734062
		CUSTOMER DRAWING	SCALE	SHEET	REV
			-	20 OF 22	E

4








3

2



1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			



FOLDER PAPER BOARD



130	7	910	7.94	3.91	7-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan	
DIMENSIONS: MM		NAME	
		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC± - 1 PLC± - 2 PLC± - 3 PLC± - 4 PLC± - ANGLES± -		PRODUCT SPEC —	
MATERIAL		APPLICATION SPEC —	
FINISH		WEIGHT—	
		SIZECAGE CODEDRAWING NORESTRICTED TO	
		A300779C-1734062—	
CUSTOMER DRAWING		SCALE—SHEET 21 OF 22REV E	

4



3

2


1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
DW				P	LTR	DESCRIPTION	DATE	DWN	APVD
						SEE SHEET 1.			



180	7	1260	9.40	5.42	8-1734062-1
PCS/REEL	REELS/BOX	QUANTITY (PCS)	G/W (Kg)	N/W (Kg)	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 Tyco Electronics Tyco Electronics Corporation Taipei, Taiwan				
DIMENSIONS: MM		CHK						
		APVD		NAME USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE				
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		WEIGHT —						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
				A3	00779	C-1734062	—	
CUSTOMER DRAWING						SCALE	SHEET	REV
						—	22 OF 22	E

Tyco Electronics Corporation Taipei, Taiwan		USB CONNECTOR, A SERIES, STACKED, OFFSET TYPE	
NAME	SIZE	CAGE CODE	DRAWING NO
	A3	00779	C-1734062
RESTRICTED TO		REV	
		E	