

REVISION AJ


DO NOT SCALE
FROM THIS PRINT

-A:
ALIGNMENT PIN
-N:
NO ALIGNMENT PIN



POSITION PARTS IN TUBE WITH THE LOGO'S ARROW POINTING
TOWARD THE FIRST POSITION INDICATOR AS SHOWN ABOVE

NOTCH TO APPEAR AS SHOWN IN TAPE



PARTS TO BE POSITIONED IN TAPE AS SHOWN

DIMENSIONS ARE IN INCHES			VALUES OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS ± .1 [3]	THREE PLACE DECIMALS ± .005 [13]	ANGLES	± 2°		PLCC ASM.	PLCC-0XX-XX-X-XX
TWO PLACE DECIMALS ± .01 [3]	FOUR PLACE DECIMALS ± .0020 [59]					SHEET 1 OF 1


PLCC-0XX-XX-X-XX

POSITION SPEC.
(SEE TABLE 1 "XX")

PACKAGING OPTION
BLANK = PACKAGING TUBE
(SEE PACKAGE TUBE SPEC.)
-TR = TAPE AND REEL
(SEE TAPE & REEL SPECS.)

PLATING SPEC.
-T: TIN (SEE TABLE 1 "CONTACT")
-F: FLASH GOLD SELECTIVE (SEE TABLE 1 "CONTACT")
-TM: MATTIE TIN (SEE TABLE 1 "CONTACT")
(SEE TABLE 1 "CONTACT")
-FM: FLASH GOLD SELECTIVE, MATTIE TIN TAIL
(SEE TABLE 1 "CONTACT")

OPTION
-A: ALIGNMENT PIN
(SPECIFY -A IN BODY SPEC. -X IN TABLE 1)
-N: NO ALIGNMENT PIN
(SPECIFY -N IN BODY SPEC. -X IN TABLE 1)



- NOTES:
1. .0400 [1.016] DIA X .030 [.76] HIGH
STANDOFFS ON -32 POSITION ONLY
(TYP 4 PLCS)
 2. Ⓢ REPRESENTS A CRITICAL DIM.

TABLE 1															CONTACT
"XX"	BODY SPEC.	TUBE SPEC. \ PLUG SPEC.	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"	"I"	"J"	"K"	"L"	
20	PLCC-20-X	PT-1-24-06-51 \ TP-13	04	04	.555 [14.10]	.555 [14.10]	.500 [12.70]	.675 [17.15]	.600 [15.24]	.600 [15.24]	.410 [10.41]	.410 [10.41]	.370 [9.40]	.370 [9.40]	C-46-XX
28	PLCC-28-X	PT-1-24-01-51 \ TP-13	06	06	.655 [16.64]	.655 [16.64]	.600 [15.24]	.818 [20.78]	.700 [17.78]	.700 [17.78]	.510 [12.95]	.510 [12.95]	.470 [11.94]	.470 [11.94]	C-46-XX
32	PLCC-32-X	PT-1-24-01-51 \ TP-13	08	08	.755 [19.18]	.655 [16.64]	.700 [17.78]	.890 [22.61]	.800 [20.32]	.700 [17.78]	.610 [15.49]	.510 [12.95]	.570 [14.48]	.470 [11.94]	C-46-XX
44	PLCC-44-X	PT-1-24-02-51 \ TP-13	10	10	.855 [21.72]	.855 [21.72]	.800 [20.32]	1.100 [27.94]	.900 [22.86]	.900 [22.86]	.710 [18.03]	.710 [18.03]	.670 [17.02]	.670 [17.02]	C-46-XX
52	PLCC-52-X	PT-1-24-03-51 \ TP-13	12	12	.955 [24.26]	.955 [24.26]	.900 [22.86]	1.242 [31.55]	1.000 [25.40]	1.000 [25.40]	.810 [20.57]	.810 [20.57]	.770 [19.56]	.770 [19.56]	C-46-XX
68	PLCC-68-X	PT-1-24-04-51 \ TP-13	16	16	1.155 [29.34]	1.155 [29.34]	1.100 [27.94]	1.525 [38.74]	1.200 [30.48]	1.200 [30.48]	1.010 [25.65]	1.010 [25.65]	.970 [24.64]	.970 [24.64]	C-46-XX
84	PLCC-84-X	PT-1-24-05-51 \ TP-25	20	20	1.355 [34.42]	1.355 [34.42]	1.300 [33.02]	1.808 [45.92]	1.400 [35.56]	1.400 [35.56]	1.210 [30.73]	1.210 [30.73]	1.170 [29.72]	1.170 [29.72]	C-46-XX

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

MATERIAL:
CELANESE, VECTRA E130
UL RATED 94V-0,
COLOR: BLACK
25% MAXIMUM REGRIND
CONTACT:
BeCu 172 SHM TEMPER

samtec
830 PARK EAST BLVD, NEW ALBANY, INDIANA 47150
PHONE (812) 944-8723 P.O. BOX 1147
CODE 05392
MADE IN:
KOLB 5-18-89
PLCC-0XX-XX-X-XX
SHEET 1 OF 1